

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562870

Luminaire Tested: **SQ4-PC3-0U-125D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562870
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-125D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4918.2 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 43.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562870
CATALOG NUMBER: SQ4-PC3-0U-125D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562870

CATALOG NUMBER: SQ4-PC3-0U-125D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16627	16627	16627
5°	16751	16644	16582
10°	16711	16633	16586
15°	16623	16623	16607
20°	16513	16563	16563
25°	16357	16476	16425
30°	16158	16354	16283
35°	15918	16163	16050
40°	15655	15876	15715
45°	15370	15480	15240
50°	14969	14969	14729
55°	14493	14306	14091
60°	13793	13516	13300
65°	12749	12494	12385
70°	11163	11252	11208
75°	8983	9935	9992
80°	6381	8421	8512
85°	3885	7061	7061



TEST NUMBER: P562870

CATALOG NUMBER: SQ4-PC3-0U-125D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.5	3.5
10°-20°	489.4	10.0
20°-30°	741.2	15.1
30°-40°	888.6	18.1
40°-50°	906.0	18.4
50°-60°	790.9	16.1
60°-70°	566.2	11.5
70°-80°	291.6	5.9
80°-90°	73.7	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1401.1	28.5
0°-40°	2289.7	46.6
0°-60°	3986.6	81.1
0°-90°	4918.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4918.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1802	1802	1802	1802	1802	
5°	1809	1791	1797	1792	1790	172
15°	1740	1726	1740	1740	1739	491
25°	1607	1595	1618	1614	1614	739
35°	1413	1410	1435	1425	1425	884
45°	1178	1175	1186	1171	1168	907
55°	901	890	889	876	876	803
65°	584	571	572	567	567	578
75°	252	263	279	280	280	272
85°	37	56	67	68	67	51
90°	0	0	0	0	0	



TEST NUMBER: P562870

CATALOG NUMBER: SQ4-PC3-0U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1802.1	1802.1	1802.1	1802.1	1802.1
2.5°	1812.7	1797.1	1802.1	1797.9	1791.4
5°	1808.7	1790.8	1797.1	1792.0	1790.4
7.5°	1795.7	1777.8	1786.0	1782.7	1781.0
10°	1783.7	1765.8	1775.4	1772.0	1770.4
12.5°	1767.7	1751.1	1762.0	1758.7	1758.3
15°	1740.3	1725.6	1740.3	1740.3	1738.7
17.5°	1706.0	1692.6	1708.3	1709.3	1708.3
20°	1681.9	1667.2	1686.9	1685.3	1686.9
22.5°	1652.6	1640.5	1661.6	1657.3	1658.9
25°	1606.8	1595.4	1618.5	1613.5	1613.5
27.5°	1552.8	1544.6	1569.8	1564.5	1564.5
30°	1516.7	1508.6	1535.1	1528.4	1528.4
32.5°	1476.7	1471.1	1496.4	1488.4	1488.4
35°	1413.3	1410.0	1435.0	1425.0	1425.0
37.5°	1347.9	1344.9	1367.6	1355.5	1351.5
40°	1299.8	1298.2	1318.2	1304.8	1304.8
42.5°	1251.8	1250.1	1267.5	1251.4	1251.4
45°	1178.0	1174.8	1186.4	1171.3	1168.0
47.5°	1097.6	1094.3	1101.6	1085.2	1083.6
50°	1042.9	1039.6	1042.9	1027.8	1026.2
52.5°	986.8	980.9	981.5	966.4	966.1
55°	901.0	889.6	889.4	876.0	876.0
57.5°	810.3	795.3	796.6	785.2	783.6
60°	747.5	731.2	732.5	722.5	720.8
62.5°	686.1	667.2	671.1	659.7	659.4
65°	584.0	571.0	572.3	567.3	567.3
67.5°	485.9	473.8	482.6	478.5	478.2
70°	413.8	405.6	417.1	417.1	415.5
72.5°	347.1	346.7	361.1	361.1	362.1
75°	252.0	263.4	278.7	280.3	280.3
77.5°	168.2	188.4	205.2	205.9	205.6
80°	120.1	143.0	158.5	161.8	160.2
82.5°	81.4	105.6	118.5	121.8	120.1
85°	36.7	56.3	66.7	68.4	66.7
87.5°	10.7	22.4	26.7	26.6	24.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)