

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563302

Luminaire Tested: **SQ4-PP3-050U-075D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563302
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4866.2 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 36.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563302
CATALOG NUMBER: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563302

CATALOG NUMBER: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	64	61	59	56	54	51	49	47	42
3	83	74	67	61	78	69	63	58	61	56	51	53	49	46	45	42	40	36
4	76	66	58	52	71	62	54	49	54	48	44	47	43	39	40	37	34	31
5	70	58	50	44	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	44	38	60	49	42	37	44	38	33	38	33	30	33	29	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	26	30	26	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	26	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10356	10356	10356
5°	10433	10369	10333
10°	10415	10342	10295
15°	10346	10290	10234
20°	10278	10220	10142
25°	10156	10085	9986
30°	9967	9915	9790
35°	9707	9640	9518
40°	9397	9338	9230
45°	9140	9076	8986
50°	8812	8756	8671
55°	8356	8245	8181
60°	7606	7388	7353
65°	6702	6423	6401
70°	5786	5546	5546
75°	4980	4909	4841
80°	4389	4442	4341
85°	3440	3747	3747



TEST NUMBER: P563302

CATALOG NUMBER: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.1	2.2
10°-20°	303.1	6.2
20°-30°	454.0	9.3
30°-40°	532.5	10.9
40°-50°	534.2	11.0
50°-60°	455.7	9.4
60°-70°	297.2	6.1
70°-80°	149.1	3.1
80°-90°	42.4	0.9
90°-100°	146.4	3.0
100°-110°	397.8	8.2
110°-120°	409.0	8.4
120°-130°	327.0	6.7
130°-140°	257.0	5.3
140°-150°	197.0	4.0
150°-160°	141.7	2.9
160°-170°	86.7	1.8
170°-180°	29.2	0.6
0°-30°	863.2	17.7
0°-40°	1395.7	28.7
0°-60°	2385.6	49.0
0°-90°	2874.3	59.1
90°-120°	953.3	19.6
90°-150°	1734.4	35.6
90°-180°	1992.0	40.9
0°-180°	4866.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1122	1122	1122	1122	1122	
5°	1126	1116	1120	1116	1116	107
15°	1083	1073	1077	1073	1071	306
25°	998	986	991	982	981	459
35°	862	853	856	846	845	538
45°	700	696	696	689	689	539
55°	520	518	513	510	509	462
65°	307	301	294	292	293	306
75°	140	140	138	137	136	152
85°	32	35	35	35	35	38
90°	1	4	7	9	9	3
95°	22	80	255	111	75	23
105°	71	110	438	666	627	75
115°	126	152	350	697	794	124
125°	173	197	317	534	630	154
135°	208	231	308	435	490	161
145°	240	258	304	370	397	151
155°	272	281	302	332	341	125
165°	294	298	303	316	317	83
175°	305	306	304	308	307	29
180°	305	305	305	305	305	

TEST NUMBER: P563302

CATALOG NUMBER: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1122.5	1122.5	1122.5	1122.5	1122.5
2.5°	1129.6	1120.4	1122.5	1120.9	1116.3
5°	1126.5	1115.9	1119.6	1115.7	1115.7
7.5°	1118.8	1107.3	1110.9	1107.0	1106.8
10°	1111.7	1100.2	1103.9	1099.9	1098.9
12.5°	1101.5	1090.0	1094.4	1089.7	1089.5
15°	1083.2	1072.6	1077.3	1073.3	1071.4
17.5°	1062.5	1051.0	1056.6	1051.1	1050.3
20°	1046.8	1035.3	1040.9	1033.0	1033.0
22.5°	1027.9	1016.4	1022.8	1012.6	1012.6
25°	997.6	986.1	990.7	981.8	980.9
27.5°	961.6	950.2	955.1	945.1	944.9
30°	935.6	925.0	930.7	919.9	918.9
32.5°	907.3	897.5	901.6	890.7	889.8
35°	861.8	853.2	855.9	846.1	845.1
37.5°	814.0	805.2	808.3	799.8	799.5
40°	780.2	774.4	775.3	768.3	766.4
42.5°	748.7	742.2	743.0	736.1	735.7
45°	700.5	695.7	695.6	688.7	688.7
47.5°	649.3	645.7	644.6	638.9	638.7
50°	613.9	611.0	610.0	605.0	604.1
52.5°	576.9	575.6	572.2	568.1	567.9
55°	519.5	517.5	512.6	509.6	508.6
57.5°	457.1	453.2	447.6	443.3	444.1
60°	412.2	408.4	400.4	398.5	398.5
62.5°	368.9	364.3	356.3	353.6	355.2
65°	307.0	301.2	294.2	292.2	293.2
67.5°	250.7	245.5	237.9	237.9	237.1
70°	214.5	211.6	205.6	205.6	205.6
72.5°	182.2	180.9	176.5	176.5	175.7
75°	139.7	139.7	137.7	136.7	135.8
77.5°	104.7	105.1	104.1	103.1	101.3
80°	82.6	84.6	83.6	82.6	81.7
82.5°	62.2	64.1	63.9	62.2	62.0
85°	32.5	35.4	35.4	35.4	35.4
87.5°	8.9	12.5	14.0	14.4	15.1
90°	1.0	3.9	6.9	8.8	8.8
92.5°	8.8	40.1	69.6	29.9	25.3
95°	21.6	80.1	255.0	111.0	74.6
97.5°	35.7	88.5	391.0	304.2	213.7
100°	45.1	94.0	432.6	438.5	354.1
102.5°	54.5	99.6	443.6	542.3	467.9
105°	70.6	110.0	437.5	666.1	626.8
107.5°	87.3	122.0	412.2	730.1	741.0
110°	99.1	130.7	393.4	742.7	789.7

TEST NUMBER: P563302

CATALOG NUMBER: SQ4-PP3-050U-075D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.3	139.4	374.5	732.2	803.0
115°	125.6	152.4	350.2	696.7	793.6
117.5°	140.9	166.6	334.7	646.4	755.5
120°	151.1	176.0	327.6	612.6	721.0
122.5°	159.7	184.6	322.9	578.8	683.3
125°	172.6	196.6	316.8	533.9	629.8
127.5°	184.2	208.0	313.5	499.8	582.1
130°	191.3	214.3	311.9	478.4	552.3
132.5°	198.3	221.4	310.4	460.2	525.6
135°	208.0	231.0	308.0	434.8	490.5
137.5°	218.4	239.3	306.8	412.5	459.3
140°	224.6	244.8	306.1	398.2	440.4
142.5°	230.9	249.5	305.3	387.1	422.4
145°	240.3	257.6	304.1	369.5	397.3
147.5°	250.9	265.7	303.1	355.6	377.5
150°	258.0	270.5	303.1	347.6	364.9
152.5°	263.5	274.4	302.3	340.5	354.7
155°	271.7	281.3	302.1	331.8	341.4
157.5°	279.8	287.2	302.1	325.8	333.1
160°	284.5	291.2	302.1	321.9	327.6
162.5°	289.2	294.4	302.9	318.7	322.9
165°	294.3	298.1	303.1	315.9	316.8
167.5°	299.6	301.5	304.1	312.5	313.3
170°	301.2	303.1	304.1	311.0	311.0
172.5°	302.7	303.9	304.1	309.4	309.4
175°	305.1	306.0	304.1	308.0	307.0
177.5°	305.9	305.9	303.5	306.6	305.1
180°	305.1	305.1	305.1	305.1	305.1

(END OF REPORT)