

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562517

Luminaire Tested: **SQ4-PC3-025U-050D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562517  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7005.9 lumens  
Efficiency: N/A  
Efficacy: 101.8 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 68.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562517

CATALOG NUMBER: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P562517

CATALOG NUMBER: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	97	93	90	96	92	88	85	82	79	77	72	70	68	64	62	61	57
2	93	85	79	73	87	80	75	70	72	67	63	63	60	57	56	54	51	47
3	85	75	67	61	79	71	64	59	63	58	53	56	52	48	50	46	44	40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	44	41	38	34
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	65	53	45	39	61	50	43	37	45	39	34	41	35	31	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	41	34	29	38	31	27	34	29	25	30	26	23	21
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5294	5294	5294
5°	5334	5299	5280
10°	5321	5296	5281
15°	5293	5293	5288
20°	5258	5274	5274
25°	5208	5246	5230
30°	5145	5207	5185
35°	5068	5146	5110
40°	4985	5055	5004
45°	4894	4929	4852
50°	4766	4766	4690
55°	4615	4555	4487
60°	4392	4304	4235
65°	4060	3978	3943
70°	3554	3583	3569
75°	2860	3163	3182
80°	2033	2681	2710
85°	1239	2251	2251



TEST NUMBER: P562517

CATALOG NUMBER: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.9	2.3
10°-20°	467.5	6.7
20°-30°	708.0	10.1
30°-40°	848.8	12.1
40°-50°	865.5	12.4
50°-60°	755.5	10.8
60°-70°	540.9	7.7
70°-80°	278.6	4.0
80°-90°	72.4	1.0
90°-100°	173.4	2.5
100°-110°	455.8	6.5
110°-120°	472.7	6.7
120°-130°	379.1	5.4
130°-140°	297.5	4.2
140°-150°	228.3	3.3
150°-160°	164.5	2.3
160°-170°	100.6	1.4
170°-180°	34.0	0.5
0°-30°	1338.4	19.1
0°-40°	2187.2	31.2
0°-60°	3808.2	54.4
0°-90°	4700.0	67.1
90°-120°	1101.9	15.7
90°-150°	2006.9	28.6
90°-180°	2306.0	32.9
0°-180°	7005.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1721	1721	1721	1721	1721	
5°	1728	1711	1717	1712	1710	164
15°	1662	1648	1662	1662	1661	469
25°	1535	1524	1546	1541	1541	706
35°	1350	1347	1371	1361	1361	844
45°	1125	1122	1133	1119	1116	866
55°	861	850	850	837	837	767
65°	558	545	547	542	542	552
75°	241	252	266	268	268	260
85°	35	54	64	65	64	48
90°	2	7	18	9	9	3
95°	23	90	299	154	105	25
105°	82	124	504	765	714	87
115°	146	177	404	805	919	144
125°	203	228	367	621	732	180
135°	242	266	356	501	568	187
145°	280	298	351	427	461	176
155°	317	326	351	386	397	146
165°	342	346	351	365	369	97
175°	356	356	354	358	358	34
180°	356	356	356	356	356	

TEST NUMBER: P562517

CATALOG NUMBER: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1721.4	1721.4	1721.4	1721.4	1721.4
2.5°	1731.6	1716.6	1721.4	1717.4	1711.2
5°	1727.8	1710.6	1716.6	1711.8	1710.2
7.5°	1715.4	1698.2	1706.1	1702.9	1701.3
10°	1703.9	1686.7	1695.9	1692.7	1691.1
12.5°	1688.6	1672.7	1683.2	1680.0	1679.6
15°	1662.4	1648.4	1662.4	1662.4	1660.8
17.5°	1629.6	1616.8	1631.8	1632.8	1631.8
20°	1606.6	1592.6	1611.4	1609.9	1611.4
22.5°	1578.6	1567.1	1587.2	1583.1	1584.7
25°	1534.9	1524.0	1546.1	1541.3	1541.3
27.5°	1483.3	1475.5	1499.5	1494.4	1494.4
30°	1448.9	1441.1	1466.4	1460.0	1460.0
32.5°	1410.6	1405.3	1429.4	1421.8	1421.8
35°	1350.0	1346.9	1370.7	1361.2	1361.2
37.5°	1287.5	1284.7	1306.4	1294.8	1291.1
40°	1241.6	1240.1	1259.2	1246.4	1246.4
42.5°	1195.7	1194.2	1210.7	1195.4	1195.4
45°	1125.3	1122.2	1133.3	1118.8	1115.7
47.5°	1048.5	1045.3	1052.3	1036.6	1035.1
50°	996.2	993.1	996.2	981.8	980.2
52.5°	942.6	937.0	937.5	923.2	922.9
55°	860.7	849.8	849.5	836.8	836.8
57.5°	774.0	759.7	760.9	750.1	748.5
60°	714.1	698.5	699.7	690.1	688.6
62.5°	655.4	637.3	641.1	630.2	629.9
65°	557.9	545.4	546.7	541.9	541.9
67.5°	464.1	452.6	461.0	457.1	456.8
70°	395.3	387.5	398.5	398.4	396.9
72.5°	331.5	331.2	344.9	344.9	345.9
75°	240.7	251.6	266.2	267.8	267.8
77.5°	160.7	180.0	196.0	196.7	196.4
80°	114.8	136.6	151.4	154.6	153.0
82.5°	77.8	100.8	113.2	116.3	114.8
85°	35.1	53.8	63.8	65.3	63.8
87.5°	10.7	22.8	29.2	27.3	24.8
90°	2.3	6.7	18.2	9.1	9.1
92.5°	9.6	46.1	102.2	45.2	29.2
95°	22.8	89.7	298.7	154.0	104.9
97.5°	39.7	98.5	447.0	355.5	261.8
100°	52.5	106.0	492.6	499.2	387.7
102.5°	63.4	113.3	505.4	621.8	526.3
105°	82.1	124.5	504.0	765.1	713.8
107.5°	101.3	140.5	475.3	839.5	852.0
110°	114.0	149.7	451.5	858.7	912.2



TEST NUMBER: P562517

CATALOG NUMBER: SQ4-PC3-025U-050D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	126.8	160.7	429.7	846.6	928.6
115°	146.0	177.2	403.7	805.3	919.1
117.5°	164.7	193.2	385.9	748.1	874.4
120°	175.6	202.4	378.6	709.7	832.4
122.5°	186.5	213.3	373.1	671.4	792.3
125°	203.0	227.5	367.2	620.6	732.0
127.5°	216.2	241.2	362.1	579.6	673.7
130°	223.5	250.2	360.3	553.9	640.8
132.5°	230.8	257.5	358.5	531.8	609.8
135°	241.7	266.3	355.8	501.0	567.9
137.5°	253.1	277.2	355.3	477.9	532.7
140°	262.3	284.6	353.5	459.6	510.8
142.5°	269.6	290.1	353.5	446.6	490.8
145°	280.5	298.3	351.2	427.2	460.7
147.5°	291.5	308.8	351.2	411.1	438.8
150°	298.7	314.4	351.2	401.9	424.2
152.5°	306.0	318.1	351.2	394.5	411.4
155°	317.0	325.9	351.2	385.7	396.8
157.5°	325.2	333.7	351.2	377.8	385.9
160°	330.7	337.4	351.2	374.1	378.6
162.5°	336.1	341.1	351.2	370.5	374.9
165°	342.1	346.5	351.2	365.0	369.4
167.5°	347.6	349.8	353.5	362.6	364.4
170°	351.2	353.4	353.5	362.6	362.6
172.5°	353.0	353.5	353.5	360.7	359.0
175°	355.8	355.8	353.5	358.0	358.0
177.5°	355.8	355.8	353.9	357.5	355.8
180°	355.8	355.8	355.8	355.8	355.8

(END OF REPORT)