

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P562565

Luminaire Tested: **SQ4-PC3-025U-100D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562565  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-025U-100D-930-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11508.3 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 123.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562565  
CATALOG NUMBER: SQ4-PC3-025U-100D-930-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P562565

CATALOG NUMBER: SQ4-PC3-025U-100D-930-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	84	84	84	80
1	105	100	96	92	100	96	92	89	88	85	83	81	79	77	74	72	71	68
2	95	88	81	76	91	84	78	73	77	73	69	71	67	64	65	62	60	57
3	87	77	69	63	83	74	67	61	68	62	58	63	58	54	58	54	51	48
4	80	68	60	53	76	66	58	52	61	54	49	56	51	46	52	47	44	41
5	73	61	52	46	70	59	51	45	54	48	43	50	45	40	46	42	38	36
6	68	55	46	40	64	53	45	39	49	42	37	45	40	35	42	37	34	31
7	63	50	41	35	60	48	40	34	45	38	33	41	36	31	38	34	30	28
8	58	45	37	31	56	44	36	31	41	34	29	38	32	28	35	30	27	25
9	54	41	33	28	52	40	33	28	37	31	26	35	29	25	33	28	24	22
10	51	38	30	25	49	37	30	25	35	28	24	32	27	23	30	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10367	10367	10367
5°	10446	10378	10340
10°	10420	10372	10342
15°	10365	10365	10356
20°	10297	10328	10328
25°	10200	10274	10242
30°	10076	10198	10153
35°	9926	10078	10008
40°	9762	9900	9799
45°	9584	9652	9503
50°	9334	9334	9185
55°	9038	8920	8786
60°	8601	8428	8294
65°	7950	7791	7723
70°	6961	7017	6988
75°	5600	6194	6231
80°	3980	5251	5308
85°	2424	4407	4407



TEST NUMBER: P562565

CATALOG NUMBER: SQ4-PC3-025U-100D-930-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	319.0	2.8
10°-20°	915.6	8.0
20°-30°	1386.5	12.0
30°-40°	1662.2	14.4
40°-50°	1694.9	14.7
50°-60°	1479.5	12.9
60°-70°	1059.2	9.2
70°-80°	545.6	4.7
80°-90°	139.9	1.2
90°-100°	173.4	1.5
100°-110°	455.8	4.0
110°-120°	472.7	4.1
120°-130°	379.1	3.3
130°-140°	297.5	2.6
140°-150°	228.3	2.0
150°-160°	164.5	1.4
160°-170°	100.6	0.9
170°-180°	34.0	0.3
0°-30°	2621.1	22.8
0°-40°	4283.3	37.2
0°-60°	7457.7	64.8
0°-90°	9202.4	80.0
90°-120°	1101.9	9.6
90°-150°	2006.9	17.4
90°-180°	2306.0	20.0
0°-180°	11508.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3371	3371	3371	3371	3371	
5°	3384	3350	3362	3352	3349	321
15°	3256	3228	3256	3256	3252	918
25°	3006	2985	3028	3018	3018	1383
35°	2644	2638	2684	2666	2666	1653
45°	2204	2198	2219	2191	2185	1696
55°	1686	1664	1664	1639	1639	1503
65°	1092	1068	1071	1061	1061	1080
75°	471	493	521	524	524	509
85°	69	105	125	128	125	93
90°	2	7	18	9	9	5
95°	23	90	299	154	105	25
105°	82	124	504	765	714	87
115°	146	177	404	805	919	144
125°	203	228	367	621	732	180
135°	242	266	356	501	568	187
145°	280	298	351	427	461	176
155°	317	326	351	386	397	146
165°	342	346	351	365	369	97
175°	356	356	354	358	358	34
180°	356	356	356	356	356	

TEST NUMBER: P562565

CATALOG NUMBER: SQ4-PC3-025U-100D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3371.1	3371.1	3371.1	3371.1	3371.1
2.5°	3391.1	3361.8	3371.1	3363.4	3351.1
5°	3383.6	3350.0	3361.8	3352.3	3349.3
7.5°	3359.3	3325.7	3341.2	3334.8	3331.8
10°	3336.8	3303.2	3321.2	3314.9	3311.8
12.5°	3306.8	3275.7	3296.2	3290.0	3289.3
15°	3255.6	3228.2	3255.6	3255.6	3252.5
17.5°	3191.3	3166.3	3195.7	3197.5	3195.7
20°	3146.4	3118.9	3155.7	3152.7	3155.7
22.5°	3091.4	3068.9	3108.3	3100.3	3103.3
25°	3005.9	2984.6	3027.8	3018.4	3018.4
27.5°	2904.8	2889.5	2936.6	2926.6	2926.6
30°	2837.4	2822.1	2871.7	2859.2	2859.2
32.5°	2762.4	2752.1	2799.3	2784.3	2784.3
35°	2643.8	2637.7	2684.4	2665.7	2665.7
37.5°	2521.5	2516.0	2558.3	2535.7	2528.3
40°	2431.6	2428.5	2465.9	2440.9	2440.9
42.5°	2341.7	2338.6	2371.0	2341.1	2341.1
45°	2203.7	2197.6	2219.3	2191.1	2185.0
47.5°	2053.3	2047.2	2060.8	2030.1	2027.0
50°	1950.9	1944.8	1950.9	1922.7	1919.7
52.5°	1846.0	1835.0	1836.0	1807.9	1807.3
55°	1685.6	1664.2	1663.7	1638.7	1638.7
57.5°	1515.8	1487.7	1490.2	1468.9	1465.8
60°	1398.4	1367.9	1370.3	1351.5	1348.4
62.5°	1283.5	1248.1	1255.4	1234.2	1233.6
65°	1092.5	1068.1	1070.6	1061.3	1061.3
67.5°	909.0	886.4	902.7	895.2	894.6
70°	774.1	758.8	780.4	780.3	777.2
72.5°	649.3	648.6	675.5	675.5	677.3
75°	471.3	492.7	521.3	524.4	524.4
77.5°	314.6	352.5	383.9	385.2	384.6
80°	224.7	267.5	296.5	302.7	299.7
82.5°	152.3	197.5	221.6	227.8	224.7
85°	68.7	105.3	124.9	127.9	124.9
87.5°	20.4	43.3	53.6	51.7	46.8
90°	2.3	6.7	18.2	9.1	9.1
92.5°	9.6	46.1	102.2	45.2	29.2
95°	22.8	89.7	298.7	154.0	104.9
97.5°	39.7	98.5	447.0	355.5	261.8
100°	52.5	106.0	492.6	499.2	387.7
102.5°	63.4	113.3	505.4	621.8	526.3
105°	82.1	124.5	504.0	765.1	713.8
107.5°	101.3	140.5	475.3	839.5	852.0
110°	114.0	149.7	451.5	858.7	912.2



TEST NUMBER: P562565

CATALOG NUMBER: SQ4-PC3-025U-100D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	126.8	160.7	429.7	846.6	928.6
115°	146.0	177.2	403.7	805.3	919.1
117.5°	164.7	193.2	385.9	748.1	874.4
120°	175.6	202.4	378.6	709.7	832.4
122.5°	186.5	213.3	373.1	671.4	792.3
125°	203.0	227.5	367.2	620.6	732.0
127.5°	216.2	241.2	362.1	579.6	673.7
130°	223.5	250.2	360.3	553.9	640.8
132.5°	230.8	257.5	358.5	531.8	609.8
135°	241.7	266.3	355.8	501.0	567.9
137.5°	253.1	277.2	355.3	477.9	532.7
140°	262.3	284.6	353.5	459.6	510.8
142.5°	269.6	290.1	353.5	446.6	490.8
145°	280.5	298.3	351.2	427.2	460.7
147.5°	291.5	308.8	351.2	411.1	438.8
150°	298.7	314.4	351.2	401.9	424.2
152.5°	306.0	318.1	351.2	394.5	411.4
155°	317.0	325.9	351.2	385.7	396.8
157.5°	325.2	333.7	351.2	377.8	385.9
160°	330.7	337.4	351.2	374.1	378.6
162.5°	336.1	341.1	351.2	370.5	374.9
165°	342.1	346.5	351.2	365.0	369.4
167.5°	347.6	349.8	353.5	362.6	364.4
170°	351.2	353.4	353.5	362.6	362.6
172.5°	353.0	353.5	353.5	360.7	359.0
175°	355.8	355.8	353.5	358.0	358.0
177.5°	355.8	355.8	353.9	357.5	355.8
180°	355.8	355.8	355.8	355.8	355.8

(END OF REPORT)