

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563470

Luminaire Tested: **SQ4-PP3-0U-050D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563470
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-050D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1949.4 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 16.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563470
CATALOG NUMBER: SQ4-PP3-0U-050D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563470

CATALOG NUMBER: SQ4-PP3-OU-050D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93		95	92	90		91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77		84	79	76		81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66		74	69	64		72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56		66	60	56		64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49		60	53	48		58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43		54	48	43		53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38		49	43	38		48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34		45	39	34		44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31		42	35	31		41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28		39	33	28		38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7027	7027	7027
5°	7079	7035	7011
10°	7067	7016	6985
15°	7020	6981	6943
20°	6973	6934	6882
25°	6891	6843	6775
30°	6763	6728	6642
35°	6586	6540	6458
40°	6375	6335	6263
45°	6202	6157	6097
50°	5978	5941	5882
55°	5668	5594	5551
60°	5161	5014	4988
65°	4547	4357	4342
70°	3925	3763	3763
75°	3379	3333	3283
80°	2981	3013	2943
85°	2329	2541	2541



TEST NUMBER: P563470

CATALOG NUMBER: SQ4-PP3-0U-050D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.0	3.7
10°-20°	205.6	10.5
20°-30°	308.0	15.8
30°-40°	361.3	18.5
40°-50°	362.4	18.6
50°-60°	309.2	15.9
60°-70°	201.6	10.3
70°-80°	101.2	5.2
80°-90°	28.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	585.7	30.0
0°-40°	947.0	48.6
0°-60°	1618.6	83.0
0°-90°	1949.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1949.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	762	762	762	762	762	
5°	764	757	760	757	757	73
15°	735	728	731	728	727	207
25°	677	669	672	666	666	311
35°	585	579	581	574	573	365
45°	475	472	472	467	467	366
55°	352	351	348	346	345	313
65°	208	204	200	198	199	208
75°	95	95	94	93	92	103
85°	22	24	24	24	24	27
90°	0	0	0	0	0	



TEST NUMBER: P563470

CATALOG NUMBER: SQ4-PP3-OU-050D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	761.6	761.6	761.6	761.6	761.6
2.5°	766.4	760.2	761.6	760.5	757.4
5°	764.3	757.1	759.6	757.0	757.0
7.5°	759.1	751.3	753.7	751.1	750.9
10°	754.3	746.5	748.9	746.3	745.6
12.5°	747.3	739.5	742.5	739.3	739.2
15°	734.9	727.7	730.9	728.2	726.9
17.5°	720.9	713.1	716.9	713.2	712.6
20°	710.2	702.4	706.2	700.9	700.9
22.5°	697.4	689.6	693.9	687.0	687.0
25°	676.9	669.0	672.2	666.2	665.5
27.5°	652.4	644.7	648.0	641.2	641.1
30°	634.8	627.6	631.5	624.1	623.5
32.5°	615.6	608.9	611.7	604.3	603.7
35°	584.7	578.9	580.7	574.0	573.4
37.5°	552.3	546.3	548.4	542.7	542.4
40°	529.3	525.4	526.0	521.3	520.0
42.5°	508.0	503.5	504.1	499.4	499.2
45°	475.3	472.0	471.9	467.3	467.3
47.5°	440.6	438.1	437.4	433.5	433.3
50°	416.5	414.6	413.9	410.5	409.8
52.5°	391.4	390.5	388.2	385.4	385.3
55°	352.4	351.1	347.8	345.8	345.1
57.5°	310.1	307.5	303.7	300.8	301.3
60°	279.7	277.1	271.7	270.3	270.3
62.5°	250.3	247.2	241.8	239.9	241.0
65°	208.3	204.3	199.6	198.3	198.9
67.5°	170.1	166.6	161.4	161.4	160.9
70°	145.5	143.6	139.5	139.5	139.5
72.5°	123.6	122.7	119.8	119.7	119.2
75°	94.8	94.8	93.5	92.8	92.1
77.5°	71.0	71.3	70.6	69.9	68.8
80°	56.1	57.4	56.7	56.1	55.4
82.5°	42.2	43.5	43.4	42.2	42.1
85°	22.0	24.0	24.0	24.0	24.0
87.5°	5.9	8.0	8.5	8.6	9.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)