

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563518

Luminaire Tested: **SQ4-PP3-0U-100D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563518
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-100D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3817.5 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563518
CATALOG NUMBER: SQ4-PP3-0U-100D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563518

CATALOG NUMBER: SQ4-PP3-OU-100D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93		95	92	90		91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77		84	79	76		81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66		74	69	64		72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56		66	60	56		64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49		60	53	48		58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43		54	48	43		53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38		49	43	38		48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34		45	39	34		44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31		42	35	31		41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28		39	33	28		38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13761	13761	13761
5°	13863	13777	13729
10°	13839	13741	13680
15°	13747	13672	13598
20°	13656	13579	13477
25°	13494	13401	13268
30°	13244	13174	13007
35°	12897	12810	12647
40°	12485	12406	12264
45°	12144	12059	11940
50°	11708	11633	11520
55°	11102	10956	10871
60°	10106	9817	9769
65°	8905	8534	8505
70°	7688	7370	7370
75°	6616	6523	6431
80°	5834	5903	5765
85°	4563	4986	4986



TEST NUMBER: P563518

CATALOG NUMBER: SQ4-PP3-0U-100D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.0	3.7
10°-20°	402.7	10.5
20°-30°	603.2	15.8
30°-40°	707.5	18.5
40°-50°	709.7	18.6
50°-60°	605.5	15.9
60°-70°	394.9	10.3
70°-80°	198.1	5.2
80°-90°	54.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1147.0	30.0
0°-40°	1854.5	48.6
0°-60°	3169.7	83.0
0°-90°	3817.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3817.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1497	1483	1488	1482	1482	142
15°	1439	1425	1431	1426	1424	406
25°	1326	1310	1316	1305	1303	610
35°	1145	1134	1137	1124	1123	715
45°	931	924	924	915	915	717
55°	690	688	681	677	676	613
65°	408	400	391	388	390	407
75°	186	186	183	182	180	201
85°	43	47	47	47	47	52
90°	0	0	0	0	0	



TEST NUMBER: P563518

CATALOG NUMBER: SQ4-PP3-OU-100D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1491.5	1491.5	1491.5	1491.5	1491.5
2.5°	1500.9	1488.7	1491.5	1489.3	1483.2
5°	1496.8	1482.7	1487.6	1482.4	1482.4
7.5°	1486.6	1471.2	1476.1	1470.9	1470.6
10°	1477.2	1461.8	1466.7	1461.4	1460.2
12.5°	1463.6	1448.2	1454.1	1447.9	1447.6
15°	1439.2	1425.2	1431.4	1426.1	1423.6
17.5°	1411.8	1396.5	1404.0	1396.6	1395.6
20°	1390.9	1375.5	1383.0	1372.6	1372.6
22.5°	1365.8	1350.4	1359.0	1345.4	1345.4
25°	1325.5	1310.2	1316.4	1304.6	1303.3
27.5°	1277.7	1262.6	1269.0	1255.7	1255.5
30°	1243.2	1229.1	1236.6	1222.2	1220.9
32.5°	1205.5	1192.5	1197.9	1183.5	1182.2
35°	1145.1	1133.6	1137.3	1124.2	1122.9
37.5°	1081.6	1069.8	1074.0	1062.8	1062.2
40°	1036.6	1029.0	1030.1	1020.9	1018.3
42.5°	994.8	986.1	987.2	978.0	977.5
45°	930.7	924.3	924.2	915.1	915.1
47.5°	862.8	857.9	856.5	848.9	848.6
50°	815.7	811.9	810.5	803.9	802.6
52.5°	766.6	764.8	760.3	754.8	754.5
55°	690.2	687.7	681.1	677.1	675.8
57.5°	607.3	602.2	594.8	589.1	590.1
60°	547.7	542.6	532.0	529.4	529.4
62.5°	490.2	484.1	473.5	469.9	471.9
65°	407.9	400.2	390.9	388.3	389.6
67.5°	333.1	326.2	316.1	316.1	315.0
70°	285.0	281.1	273.2	273.2	273.2
72.5°	242.1	240.3	234.5	234.5	233.5
75°	185.6	185.6	183.0	181.7	180.4
77.5°	139.1	139.6	138.3	136.9	134.6
80°	109.8	112.4	111.1	109.8	108.5
82.5°	82.6	85.2	85.0	82.6	82.4
85°	43.1	47.0	47.1	47.1	47.1
87.5°	11.5	15.6	16.7	16.8	17.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)