

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562613

Luminaire Tested: **SQ4-PC3-050U-050D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562613
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-050D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9456.1 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 79.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562613

CATALOG NUMBER: SQ4-PC3-050U-050D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562613

CATALOG NUMBER: SQ4-PC3-050U-050D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	49	48	47	42
2	89	82	76	70	82	75	70	66	64	60	57	53	51	48	44	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	30
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	34	32	29	25
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	26	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	28	24	30	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5294	5294	5294
5°	5334	5299	5280
10°	5321	5296	5281
15°	5293	5293	5288
20°	5258	5274	5274
25°	5208	5246	5230
30°	5145	5207	5185
35°	5068	5146	5110
40°	4985	5055	5004
45°	4894	4929	4852
50°	4766	4766	4690
55°	4615	4555	4487
60°	4392	4304	4235
65°	4060	3978	3943
70°	3554	3583	3569
75°	2860	3163	3182
80°	2033	2681	2710
85°	1239	2251	2251



TEST NUMBER: P562613

CATALOG NUMBER: SQ4-PC3-050U-050D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.9	1.7
10°-20°	467.5	4.9
20°-30°	708.0	7.5
30°-40°	848.8	9.0
40°-50°	865.5	9.2
50°-60°	755.5	8.0
60°-70°	540.9	5.7
70°-80°	278.6	2.9
80°-90°	73.3	0.8
90°-100°	349.6	3.7
100°-110°	949.7	10.0
110°-120°	976.5	10.3
120°-130°	780.7	8.3
130°-140°	613.5	6.5
140°-150°	470.4	5.0
150°-160°	338.3	3.6
160°-170°	206.9	2.2
170°-180°	69.7	0.7
0°-30°	1338.4	14.2
0°-40°	2187.2	23.1
0°-60°	3808.2	40.3
0°-90°	4700.9	49.7
90°-120°	2275.9	24.1
90°-150°	4140.4	43.8
90°-180°	4755.0	50.3
0°-180°	9456.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1721	1721	1721	1721	1721	
5°	1728	1711	1717	1712	1710	164
15°	1662	1648	1662	1662	1661	469
25°	1535	1524	1546	1541	1541	706
35°	1350	1347	1371	1361	1361	844
45°	1125	1122	1133	1119	1116	866
55°	861	850	850	837	837	767
65°	558	545	547	542	542	552
75°	241	252	266	268	268	260
85°	35	54	64	65	64	48
90°	2	9	16	21	21	5
95°	52	191	609	265	178	55
105°	169	262	1044	1590	1496	179
115°	300	364	836	1663	1894	296
125°	412	469	756	1274	1503	367
135°	496	551	735	1038	1171	384
145°	574	615	726	882	948	360
155°	649	672	721	792	815	299
165°	702	712	724	754	756	198
175°	728	731	726	735	733	69
180°	728	728	728	728	728	

TEST NUMBER: P562613

CATALOG NUMBER: SQ4-PC3-050U-050D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1721.4	1721.4	1721.4	1721.4	1721.4
2.5°	1731.6	1716.6	1721.4	1717.4	1711.2
5°	1727.8	1710.6	1716.6	1711.8	1710.2
7.5°	1715.4	1698.2	1706.1	1702.9	1701.3
10°	1703.9	1686.7	1695.9	1692.7	1691.1
12.5°	1688.6	1672.7	1683.2	1680.0	1679.6
15°	1662.4	1648.4	1662.4	1662.4	1660.8
17.5°	1629.6	1616.8	1631.8	1632.8	1631.8
20°	1606.6	1592.6	1611.4	1609.9	1611.4
22.5°	1578.6	1567.1	1587.2	1583.1	1584.7
25°	1534.9	1524.0	1546.1	1541.3	1541.3
27.5°	1483.3	1475.5	1499.5	1494.4	1494.4
30°	1448.9	1441.1	1466.4	1460.0	1460.0
32.5°	1410.6	1405.3	1429.4	1421.8	1421.8
35°	1350.0	1346.9	1370.7	1361.2	1361.2
37.5°	1287.5	1284.7	1306.4	1294.8	1291.1
40°	1241.6	1240.1	1259.2	1246.4	1246.4
42.5°	1195.7	1194.2	1210.7	1195.4	1195.4
45°	1125.3	1122.2	1133.3	1118.8	1115.7
47.5°	1048.5	1045.3	1052.3	1036.6	1035.1
50°	996.2	993.1	996.2	981.8	980.2
52.5°	942.6	937.0	937.5	923.2	922.9
55°	860.7	849.8	849.5	836.8	836.8
57.5°	774.0	759.7	760.9	750.1	748.5
60°	714.1	698.5	699.7	690.1	688.6
62.5°	655.4	637.3	641.1	630.2	629.9
65°	557.9	545.4	546.7	541.9	541.9
67.5°	464.1	452.6	461.0	457.1	456.8
70°	395.3	387.5	398.5	398.4	396.9
72.5°	331.5	331.2	344.9	344.9	345.9
75°	240.7	251.6	266.2	267.8	267.8
77.5°	160.7	180.0	196.0	196.7	196.4
80°	114.8	136.6	151.4	154.6	153.0
82.5°	77.8	100.8	113.2	116.3	114.8
85°	35.1	53.8	63.8	65.3	63.8
87.5°	10.7	23.3	28.8	29.7	27.2
90°	2.3	9.2	16.4	21.1	21.1
92.5°	21.1	95.7	166.3	71.4	60.4
95°	51.5	191.2	608.9	265.0	178.0
97.5°	85.2	211.2	933.4	726.2	510.0
100°	107.7	224.5	1032.7	1046.9	845.4
102.5°	130.2	237.8	1059.0	1294.7	1117.0
105°	168.6	262.5	1044.4	1590.3	1496.4
107.5°	208.4	291.3	984.0	1742.9	1769.0
110°	236.5	312.1	939.1	1772.9	1885.1



TEST NUMBER: P562613

CATALOG NUMBER: SQ4-PC3-050U-050D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	260.9	332.8	894.1	1748.0	1917.0
115°	299.7	363.9	836.0	1663.2	1894.5
117.5°	336.3	397.6	799.0	1543.1	1803.6
120°	360.6	420.2	782.2	1462.5	1721.2
122.5°	381.2	440.8	770.9	1381.7	1631.3
125°	412.2	469.4	756.4	1274.4	1503.4
127.5°	439.8	496.6	748.4	1193.2	1389.6
130°	456.6	511.6	744.7	1142.1	1318.4
132.5°	473.5	528.5	740.9	1098.6	1254.7
135°	496.5	551.4	735.3	1038.1	1170.9
137.5°	521.3	571.2	732.5	984.7	1096.4
140°	536.3	584.4	730.6	950.7	1051.5
142.5°	551.3	595.7	728.8	924.1	1008.4
145°	573.7	615.0	726.0	882.0	948.4
147.5°	599.0	634.3	723.6	848.9	901.1
150°	615.9	645.7	723.6	829.9	871.1
152.5°	629.0	655.1	721.7	812.9	846.8
155°	648.7	671.6	721.3	792.0	814.9
157.5°	667.9	685.7	721.3	777.9	795.3
160°	679.1	695.1	721.3	768.4	782.2
162.5°	690.4	702.7	723.1	760.8	770.9
165°	702.5	711.7	723.6	754.1	756.4
167.5°	715.2	719.8	726.0	746.1	748.0
170°	718.9	723.5	726.0	742.3	742.3
172.5°	722.7	725.4	726.0	738.6	738.6
175°	728.3	730.6	726.0	735.3	733.0
177.5°	730.2	730.2	724.5	732.0	728.3
180°	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)