

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562685

Luminaire Tested: **SQ4-PC3-050U-125D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562685
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16499.0 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 167
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562685
CATALOG NUMBER: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562685

CATALOG NUMBER: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	91	97	93	90	86	84	81	79	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	43
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	34	30	28
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	35	30	27	25
8	57	44	36	30	54	42	35	30	39	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13230	13230	13230
5°	13330	13244	13195
10°	13298	13236	13198
15°	13228	13228	13215
20°	13141	13180	13180
25°	13017	13111	13071
30°	12858	13014	12957
35°	12667	12861	12772
40°	12457	12633	12506
45°	12231	12318	12127
50°	11911	11911	11721
55°	11533	11384	11213
60°	10976	10756	10584
65°	10146	9943	9855
70°	8883	8954	8919
75°	7147	7904	7952
80°	5079	6702	6773
85°	3091	5621	5621



TEST NUMBER: P562685

CATALOG NUMBER: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	407.1	2.5
10°-20°	1168.4	7.1
20°-30°	1769.3	10.7
30°-40°	2121.2	12.9
40°-50°	2162.9	13.1
50°-60°	1888.1	11.4
60°-70°	1351.7	8.2
70°-80°	696.2	4.2
80°-90°	178.8	1.1
90°-100°	349.6	2.1
100°-110°	949.7	5.8
110°-120°	976.5	5.9
120°-130°	780.7	4.7
130°-140°	613.5	3.7
140°-150°	470.4	2.9
150°-160°	338.3	2.1
160°-170°	206.9	1.3
170°-180°	69.7	0.4
0°-30°	3344.9	20.3
0°-40°	5466.1	33.1
0°-60°	9517.0	57.7
0°-90°	11743.8	71.2
90°-120°	2275.9	13.8
90°-150°	4140.4	25.1
90°-180°	4755.0	28.8
0°-180°	16499.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4302	4302	4302	4302	4302	
5°	4318	4275	4290	4278	4274	410
15°	4155	4120	4155	4154	4151	1171
25°	3836	3809	3864	3852	3852	1765
35°	3374	3366	3426	3402	3402	2110
45°	2812	2804	2832	2796	2788	2165
55°	2151	2124	2123	2091	2091	1917
65°	1394	1363	1366	1354	1354	1379
75°	602	629	665	669	669	650
85°	88	134	159	163	159	119
90°	2	9	16	21	21	7
95°	52	191	609	265	178	55
105°	169	262	1044	1590	1496	179
115°	300	364	836	1663	1894	296
125°	412	469	756	1274	1503	367
135°	496	551	735	1038	1171	384
145°	574	615	726	882	948	360
155°	649	672	721	792	815	299
165°	702	712	724	754	756	198
175°	728	731	726	735	733	69
180°	728	728	728	728	728	

TEST NUMBER: P562685

CATALOG NUMBER: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4302.0	4302.0	4302.0	4302.0	4302.0
2.5°	4327.5	4290.1	4302.0	4292.1	4276.5
5°	4317.9	4275.1	4290.1	4278.0	4274.1
7.5°	4286.9	4244.0	4263.8	4255.7	4251.8
10°	4258.2	4215.3	4238.3	4230.2	4226.3
12.5°	4219.9	4180.2	4206.4	4198.4	4197.6
15°	4154.6	4119.6	4154.6	4154.5	4150.6
17.5°	4072.6	4040.6	4078.1	4080.5	4078.1
20°	4015.2	3980.2	4027.2	4023.3	4027.2
22.5°	3945.1	3916.3	3966.6	3956.3	3960.2
25°	3836.0	3808.7	3863.8	3851.9	3851.9
27.5°	3706.9	3687.4	3747.5	3734.8	3734.8
30°	3620.9	3601.4	3664.7	3648.7	3648.7
32.5°	3525.3	3512.0	3572.3	3553.1	3553.1
35°	3373.9	3366.1	3425.7	3401.8	3401.8
37.5°	3217.7	3210.7	3264.7	3235.9	3226.5
40°	3103.0	3099.1	3146.8	3115.0	3115.0
42.5°	2988.3	2984.4	3025.7	2987.5	2987.5
45°	2812.2	2804.4	2832.2	2796.1	2788.3
47.5°	2620.2	2612.5	2629.8	2590.7	2586.8
50°	2489.6	2481.8	2489.6	2453.6	2449.8
52.5°	2355.7	2341.7	2343.0	2307.1	2306.4
55°	2151.0	2123.7	2123.1	2091.3	2091.3
57.5°	1934.3	1898.5	1901.6	1874.5	1870.6
60°	1784.5	1745.6	1748.7	1724.7	1720.8
62.5°	1637.9	1592.8	1602.1	1575.0	1574.2
65°	1394.2	1363.0	1366.3	1354.3	1354.3
67.5°	1159.9	1131.1	1152.0	1142.4	1141.6
70°	987.9	968.4	995.8	995.7	991.9
72.5°	828.5	827.8	862.0	862.0	864.4
75°	601.5	628.7	665.2	669.2	669.2
77.5°	401.5	449.8	490.0	491.5	490.7
80°	286.8	341.3	378.4	386.3	382.4
82.5°	194.4	252.0	282.8	290.7	286.8
85°	87.6	134.4	159.3	163.2	159.3
87.5°	26.0	55.4	67.0	67.8	61.6
90°	2.3	9.2	16.4	21.1	21.1
92.5°	21.1	95.7	166.3	71.4	60.4
95°	51.5	191.2	608.9	265.0	178.0
97.5°	85.2	211.2	933.4	726.2	510.0
100°	107.7	224.5	1032.7	1046.9	845.4
102.5°	130.2	237.8	1059.0	1294.7	1117.0
105°	168.6	262.5	1044.4	1590.3	1496.4
107.5°	208.4	291.3	984.0	1742.9	1769.0
110°	236.5	312.1	939.1	1772.9	1885.1



TEST NUMBER: P562685

CATALOG NUMBER: SQ4-PC3-050U-125D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	260.9	332.8	894.1	1748.0	1917.0
115°	299.7	363.9	836.0	1663.2	1894.5
117.5°	336.3	397.6	799.0	1543.1	1803.6
120°	360.6	420.2	782.2	1462.5	1721.2
122.5°	381.2	440.8	770.9	1381.7	1631.3
125°	412.2	469.4	756.4	1274.4	1503.4
127.5°	439.8	496.6	748.4	1193.2	1389.6
130°	456.6	511.6	744.7	1142.1	1318.4
132.5°	473.5	528.5	740.9	1098.6	1254.7
135°	496.5	551.4	735.3	1038.1	1170.9
137.5°	521.3	571.2	732.5	984.7	1096.4
140°	536.3	584.4	730.6	950.7	1051.5
142.5°	551.3	595.7	728.8	924.1	1008.4
145°	573.7	615.0	726.0	882.0	948.4
147.5°	599.0	634.3	723.6	848.9	901.1
150°	615.9	645.7	723.6	829.9	871.1
152.5°	629.0	655.1	721.7	812.9	846.8
155°	648.7	671.6	721.3	792.0	814.9
157.5°	667.9	685.7	721.3	777.9	795.3
160°	679.1	695.1	721.3	768.4	782.2
162.5°	690.4	702.7	723.1	760.8	770.9
165°	702.5	711.7	723.6	754.1	756.4
167.5°	715.2	719.8	726.0	746.1	748.0
170°	718.9	723.5	726.0	742.3	742.3
172.5°	722.7	725.4	726.0	738.6	738.6
175°	728.3	730.6	726.0	735.3	733.0
177.5°	730.2	730.2	724.5	732.0	728.3
180°	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)