

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562829

Luminaire Tested: **SQ4-PC3-0U-075D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562829
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-075D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6924.4 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Direct

Input Watts (W): 79.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562829
CATALOG NUMBER: SQ4-PC3-0U-075D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562829

CATALOG NUMBER: SQ4-PC3-0U-075D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85				
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71				
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60				
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51				
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44				
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39				
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34				
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31				
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28				
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7803	7803	7803
5°	7862	7811	7782
10°	7842	7806	7784
15°	7801	7801	7794
20°	7750	7773	7773
25°	7677	7732	7709
30°	7583	7675	7642
35°	7470	7585	7532
40°	7347	7451	7375
45°	7213	7265	7152
50°	7025	7025	6913
55°	6802	6714	6613
60°	6473	6343	6242
65°	5983	5864	5812
70°	5239	5281	5260
75°	4215	4661	4690
80°	2995	3953	3994
85°	1824	3317	3317



TEST NUMBER: P562829

CATALOG NUMBER: SQ4-PC3-0U-075D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.1	3.5
10°-20°	689.1	10.0
20°-30°	1043.5	15.1
30°-40°	1251.0	18.1
40°-50°	1275.6	18.4
50°-60°	1113.5	16.1
60°-70°	797.2	11.5
70°-80°	410.6	5.9
80°-90°	103.8	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1972.7	28.5
0°-40°	3223.7	46.6
0°-60°	5612.8	81.1
0°-90°	6924.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6924.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2537	2537	2537	2537	2537	
5°	2547	2521	2530	2523	2521	242
15°	2450	2430	2450	2450	2448	691
25°	2262	2246	2279	2272	2272	1041
35°	1990	1985	2020	2006	2006	1244
45°	1658	1654	1670	1649	1644	1277
55°	1269	1252	1252	1233	1233	1131
65°	822	804	806	799	799	813
75°	355	371	392	395	395	383
85°	52	79	94	96	94	72
90°	0	0	0	0	0	



TEST NUMBER: P562829

CATALOG NUMBER: SQ4-PC3-0U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2537.2	2537.2	2537.2	2537.2	2537.2
2.5°	2552.2	2530.1	2537.2	2531.3	2522.1
5°	2546.6	2521.3	2530.1	2523.0	2520.7
7.5°	2528.2	2503.0	2514.6	2509.9	2507.6
10°	2511.3	2486.0	2499.6	2494.8	2492.5
12.5°	2488.8	2465.3	2480.8	2476.1	2475.6
15°	2450.2	2429.6	2450.2	2450.2	2447.9
17.5°	2401.8	2383.0	2405.1	2406.5	2405.1
20°	2368.0	2347.3	2375.1	2372.8	2375.1
22.5°	2326.7	2309.7	2339.4	2333.3	2335.6
25°	2262.3	2246.2	2278.7	2271.7	2271.7
27.5°	2186.2	2174.7	2210.1	2202.6	2202.6
30°	2135.4	2124.0	2161.3	2151.9	2151.9
32.5°	2079.1	2071.2	2106.8	2095.5	2095.5
35°	1989.8	1985.2	2020.3	2006.2	2006.2
37.5°	1897.7	1893.6	1925.4	1908.4	1902.9
40°	1830.0	1827.7	1855.9	1837.1	1837.1
42.5°	1762.4	1760.1	1784.5	1761.9	1761.9
45°	1658.5	1654.0	1670.3	1649.0	1644.5
47.5°	1545.3	1540.7	1551.0	1527.9	1525.6
50°	1468.3	1463.7	1468.3	1447.1	1444.8
52.5°	1389.3	1381.1	1381.8	1360.7	1360.2
55°	1268.6	1252.5	1252.1	1233.3	1233.3
57.5°	1140.8	1119.6	1121.5	1105.5	1103.2
60°	1052.4	1029.5	1031.3	1017.2	1014.9
62.5°	966.0	939.4	944.9	928.9	928.4
65°	822.2	803.8	805.8	798.7	798.7
67.5°	684.1	667.1	679.4	673.7	673.3
70°	582.6	571.1	587.3	587.3	585.0
72.5°	488.6	488.2	508.4	508.4	509.8
75°	354.7	370.8	392.3	394.7	394.7
77.5°	236.8	265.3	289.0	289.9	289.4
80°	169.1	201.3	223.2	227.8	225.5
82.5°	114.6	148.6	166.8	171.4	169.1
85°	51.7	79.2	94.0	96.3	94.0
87.5°	15.0	31.6	37.6	37.5	33.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)