

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563710

Luminaire Tested: **SQ4-PP3-125U-100D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563710  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8818.7 lumens  
Efficiency: N/A  
Efficacy: 136.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 64.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563710  
CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P563710

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	67	56	48	42	61	52	45	39	43	38	34	35	32	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13761	13761	13761
5°	13863	13777	13729
10°	13839	13741	13680
15°	13747	13672	13598
20°	13656	13579	13477
25°	13494	13401	13268
30°	13244	13174	13007
35°	12897	12810	12647
40°	12485	12406	12264
45°	12144	12059	11940
50°	11708	11633	11520
55°	11102	10956	10871
60°	10106	9817	9769
65°	8905	8534	8505
70°	7688	7370	7370
75°	6616	6523	6431
80°	5834	5903	5765
85°	4563	4986	4986



TEST NUMBER: P563710

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.0	1.6
10°-20°	402.7	4.6
20°-30°	603.2	6.8
30°-40°	707.5	8.0
40°-50°	709.7	8.0
50°-60°	605.5	6.9
60°-70°	394.9	4.5
70°-80°	198.1	2.2
80°-90°	56.7	0.6
90°-100°	362.3	4.1
100°-110°	975.9	11.1
110°-120°	1024.2	11.6
120°-130°	831.1	9.4
130°-140°	651.8	7.4
140°-150°	500.4	5.7
150°-160°	359.8	4.1
160°-170°	219.8	2.5
170°-180°	74.1	0.8
0°-30°	1147.0	13.0
0°-40°	1854.5	21.0
0°-60°	3169.7	35.9
0°-90°	3819.3	43.3
90°-120°	2362.3	26.8
90°-150°	4345.6	49.3
90°-180°	4999.0	56.7
0°-180°	8818.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1497	1483	1488	1482	1482	142
15°	1439	1425	1431	1426	1424	406
25°	1326	1310	1316	1305	1303	610
35°	1145	1134	1137	1124	1123	715
45°	931	924	924	915	915	717
55°	690	688	681	677	676	613
65°	408	400	391	388	390	407
75°	186	186	183	182	180	201
85°	43	47	47	47	47	51
90°	2	6	12	13	13	5
95°	55	197	594	304	210	58
105°	180	281	1079	1615	1515	190
115°	319	390	899	1736	1964	314
125°	435	500	807	1364	1605	389
135°	524	585	784	1100	1246	404
145°	606	653	774	941	1010	380
155°	688	713	768	844	871	317
165°	746	754	770	801	805	210
175°	775	774	772	782	780	74
180°	774	774	774	774	774	

TEST NUMBER: P563710

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1491.5	1491.5	1491.5	1491.5	1491.5
2.5°	1500.9	1488.7	1491.5	1489.3	1483.2
5°	1496.8	1482.7	1487.6	1482.4	1482.4
7.5°	1486.6	1471.2	1476.1	1470.9	1470.6
10°	1477.2	1461.8	1466.7	1461.4	1460.2
12.5°	1463.6	1448.2	1454.1	1447.9	1447.6
15°	1439.2	1425.2	1431.4	1426.1	1423.6
17.5°	1411.8	1396.5	1404.0	1396.6	1395.6
20°	1390.9	1375.5	1383.0	1372.6	1372.6
22.5°	1365.8	1350.4	1359.0	1345.4	1345.4
25°	1325.5	1310.2	1316.4	1304.6	1303.3
27.5°	1277.7	1262.6	1269.0	1255.7	1255.5
30°	1243.2	1229.1	1236.6	1222.2	1220.9
32.5°	1205.5	1192.5	1197.9	1183.5	1182.2
35°	1145.1	1133.6	1137.3	1124.2	1122.9
37.5°	1081.6	1069.8	1074.0	1062.8	1062.2
40°	1036.6	1029.0	1030.1	1020.9	1018.3
42.5°	994.8	986.1	987.2	978.0	977.5
45°	930.7	924.3	924.2	915.1	915.1
47.5°	862.8	857.9	856.5	848.9	848.6
50°	815.7	811.9	810.5	803.9	802.6
52.5°	766.6	764.8	760.3	754.8	754.5
55°	690.2	687.7	681.1	677.1	675.8
57.5°	607.3	602.2	594.8	589.1	590.1
60°	547.7	542.6	532.0	529.4	529.4
62.5°	490.2	484.1	473.5	469.9	471.9
65°	407.9	400.2	390.9	388.3	389.6
67.5°	333.1	326.2	316.1	316.1	315.0
70°	285.0	281.1	273.2	273.2	273.2
72.5°	242.1	240.3	234.5	234.5	233.5
75°	185.6	185.6	183.0	181.7	180.4
77.5°	139.1	139.6	138.3	136.9	134.6
80°	109.8	112.4	111.1	109.8	108.5
82.5°	82.6	85.2	85.0	82.6	82.4
85°	43.1	47.0	47.1	47.1	47.1
87.5°	11.9	16.8	19.1	19.3	20.3
90°	2.0	5.8	11.8	12.8	12.8
92.5°	24.1	85.0	168.1	80.9	56.2
95°	55.2	197.0	593.9	303.7	210.1
97.5°	88.2	225.6	931.5	778.2	586.8
100°	113.4	236.9	1038.8	1086.9	901.7
102.5°	137.9	252.9	1074.3	1318.1	1166.1
105°	180.5	280.9	1079.3	1614.6	1515.3
107.5°	220.8	310.3	1033.3	1767.0	1792.7
110°	247.6	332.5	991.5	1814.4	1907.9



TEST NUMBER: P563710

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	276.0	354.7	951.2	1803.9	1957.7
115°	318.6	390.0	898.7	1736.5	1964.2
117.5°	357.5	424.5	858.1	1629.0	1882.5
120°	382.8	447.4	837.6	1551.8	1812.2
122.5°	404.9	468.7	822.6	1472.9	1732.5
125°	435.1	499.7	807.0	1363.9	1605.1
127.5°	464.1	527.7	797.1	1267.8	1483.1
130°	481.4	545.1	793.2	1212.8	1401.8
132.5°	498.8	561.7	789.2	1164.3	1337.9
135°	523.8	584.6	784.3	1100.3	1246.0
137.5°	547.7	606.0	781.7	1046.1	1165.7
140°	564.3	620.2	779.4	1012.7	1120.7
142.5°	581.7	633.7	777.8	981.5	1072.5
145°	605.7	653.0	774.4	940.7	1010.2
147.5°	631.8	672.9	771.1	906.5	961.1
150°	649.1	684.8	769.5	885.0	930.3
152.5°	664.9	696.0	768.7	867.4	904.2
155°	687.6	712.7	767.5	844.1	871.1
157.5°	707.5	727.0	767.7	827.7	845.8
160°	720.2	736.6	768.5	818.1	831.6
162.5°	731.2	744.5	769.3	810.2	819.8
165°	745.8	754.5	770.5	801.1	805.0
167.5°	757.6	762.7	771.5	794.2	795.7
170°	765.5	767.5	771.5	790.2	790.2
172.5°	770.3	770.7	772.2	786.3	786.3
175°	775.4	774.4	771.5	782.3	780.3
177.5°	777.6	776.0	772.1	778.3	776.8
180°	774.4	774.4	774.4	774.4	774.4

(END OF REPORT)