

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563830

Luminaire Tested: **SQ4-PP3-150U-125D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-125D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10897.6 lumens
Efficiency: N/A
Efficacy: 131.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 83.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563830
CATALOG NUMBER: SQ4-PP3-150U-125D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563830

CATALOG NUMBER: SQ4-PP3-150U-125D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37	32
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	34	32	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	24
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	33	28	25	26	23	21	18
7	58	45	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	34	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17561	17561	17561
5°	17690	17582	17520
10°	17660	17535	17457
15°	17544	17448	17353
20°	17427	17328	17198
25°	17219	17101	16931
30°	16901	16812	16599
35°	16459	16346	16140
40°	15933	15832	15651
45°	15497	15389	15236
50°	14940	14846	14702
55°	14168	13980	13874
60°	12898	12529	12466
65°	11363	10889	10852
70°	9811	9406	9406
75°	8445	8324	8206
80°	7444	7534	7359
85°	5833	6362	6362



TEST NUMBER: P563830

CATALOG NUMBER: SQ4-PP3-150U-125D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.0	1.7
10°-20°	513.9	4.7
20°-30°	769.8	7.1
30°-40°	902.9	8.3
40°-50°	905.7	8.3
50°-60°	772.7	7.1
60°-70°	503.9	4.6
70°-80°	252.8	2.3
80°-90°	71.9	0.7
90°-100°	434.2	4.0
100°-110°	1174.0	10.8
110°-120°	1234.3	11.3
120°-130°	1002.6	9.2
130°-140°	786.5	7.2
140°-150°	603.6	5.5
150°-160°	434.1	4.0
160°-170°	265.2	2.4
170°-180°	89.4	0.8
0°-30°	1463.7	13.4
0°-40°	2366.6	21.7
0°-60°	4045.0	37.1
0°-90°	4873.6	44.7
90°-120°	2842.6	26.1
90°-150°	5235.3	48.0
90°-180°	6024.0	55.3
0°-180°	10897.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1910	1892	1898	1892	1892	181
15°	1837	1819	1827	1820	1817	518
25°	1692	1672	1680	1665	1663	778
35°	1461	1447	1451	1435	1433	913
45°	1188	1180	1179	1168	1168	915
55°	881	878	869	864	862	783
65°	520	511	499	496	497	519
75°	237	237	234	232	230	257
85°	55	60	60	60	60	65
90°	2	6	13	14	13	7
95°	67	236	722	374	222	71
105°	218	337	1302	1921	1842	230
115°	384	470	1080	2091	2360	379
125°	526	603	974	1643	1930	469
135°	631	705	947	1326	1502	487
145°	733	788	934	1135	1222	459
155°	828	860	926	1019	1052	382
165°	901	910	930	967	972	254
175°	935	934	931	943	941	89
180°	934	934	934	934	934	

TEST NUMBER: P563830

CATALOG NUMBER: SQ4-PP3-150U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1903.4	1903.4	1903.4	1903.4	1903.4
2.5°	1915.4	1899.7	1903.4	1900.5	1892.7
5°	1910.1	1892.1	1898.4	1891.7	1891.7
7.5°	1897.1	1877.5	1883.7	1877.0	1876.7
10°	1885.0	1865.5	1871.7	1865.0	1863.4
12.5°	1867.7	1848.1	1855.7	1847.7	1847.3
15°	1836.7	1818.7	1826.7	1819.9	1816.7
17.5°	1801.6	1782.1	1791.6	1782.3	1781.0
20°	1774.9	1755.4	1764.9	1751.6	1751.6
22.5°	1742.9	1723.3	1734.2	1716.9	1716.9
25°	1691.5	1672.0	1679.9	1664.8	1663.2
27.5°	1630.5	1611.2	1619.5	1602.4	1602.1
30°	1586.4	1568.5	1578.1	1559.7	1558.1
32.5°	1538.4	1521.8	1528.7	1510.3	1508.7
35°	1461.3	1446.6	1451.3	1434.6	1433.0
37.5°	1380.3	1365.2	1370.6	1356.2	1355.6
40°	1322.9	1313.1	1314.5	1302.8	1299.5
42.5°	1269.5	1258.4	1259.8	1248.1	1247.5
45°	1187.7	1179.6	1179.4	1167.7	1167.7
47.5°	1101.0	1094.8	1093.0	1083.3	1083.0
50°	1040.9	1036.1	1034.3	1025.9	1024.3
52.5°	978.2	975.9	970.2	963.2	962.9
55°	880.8	877.5	869.1	864.1	862.5
57.5°	775.0	768.5	759.0	751.7	753.0
60°	699.0	692.4	679.0	675.6	675.6
62.5°	625.6	617.7	604.2	599.6	602.2
65°	520.5	510.7	498.8	495.5	497.1
67.5°	425.1	416.2	403.4	403.3	402.0
70°	363.7	358.8	348.7	348.7	348.7
72.5°	308.9	306.7	299.3	299.2	297.9
75°	236.9	236.9	233.5	231.8	230.2
77.5°	177.5	178.1	176.5	174.8	171.8
80°	140.1	143.4	141.8	140.1	138.5
82.5°	105.4	108.7	108.4	105.4	105.1
85°	55.1	59.9	60.1	60.1	60.1
87.5°	15.1	21.1	24.0	24.2	25.3
90°	2.0	5.9	13.1	14.1	13.1
92.5°	28.6	104.1	205.4	89.2	64.6
95°	67.4	236.5	722.1	373.7	222.3
97.5°	108.2	271.3	1125.6	931.5	684.1
100°	138.8	285.3	1251.1	1304.8	1055.0
102.5°	167.0	304.8	1295.4	1587.8	1401.0
105°	218.2	337.2	1302.4	1921.2	1842.5
107.5°	265.7	374.3	1245.5	2129.1	2155.3
110°	302.7	401.1	1194.8	2185.0	2296.1



TEST NUMBER: P563830

CATALOG NUMBER: SQ4-PP3-150U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	335.7	427.8	1148.1	2173.8	2360.5
115°	384.2	469.7	1080.2	2091.0	2360.5
117.5°	431.7	511.9	1035.3	1964.5	2269.9
120°	460.6	539.3	1008.8	1873.7	2185.5
122.5°	488.0	565.1	992.7	1776.4	2090.5
125°	526.0	602.7	973.6	1642.9	1930.0
127.5°	561.0	636.3	962.3	1533.9	1786.4
130°	580.3	658.0	957.5	1466.5	1694.7
132.5°	600.4	677.3	952.6	1405.8	1615.8
135°	630.6	705.3	947.4	1326.5	1501.6
137.5°	661.0	731.6	943.0	1262.2	1404.8
140°	681.9	747.8	941.4	1220.8	1347.7
142.5°	702.0	764.0	938.1	1183.5	1294.6
145°	733.2	788.2	934.3	1135.4	1222.0
147.5°	761.5	810.3	929.9	1091.9	1158.4
150°	782.5	825.7	928.3	1068.3	1121.4
152.5°	801.8	839.5	927.5	1046.4	1090.0
155°	827.7	860.2	926.3	1018.6	1052.0
157.5°	854.7	877.3	926.5	999.2	1021.2
160°	870.0	888.6	927.3	987.0	1002.7
162.5°	882.0	897.6	928.1	977.2	989.0
165°	901.1	910.0	930.3	966.6	971.5
167.5°	914.2	920.3	930.5	957.5	959.9
170°	922.3	925.2	931.3	953.4	953.4
172.5°	928.7	929.3	931.3	948.6	947.8
175°	935.3	934.3	931.3	943.3	941.4
177.5°	937.5	935.2	931.1	939.1	936.7
180°	934.3	934.3	934.3	934.3	934.3

(END OF REPORT)