

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563237

Luminaire Tested: **SQ4-PP3-025U-100D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563237
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-100D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11421.2 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 123.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563237
CATALOG NUMBER: SQ4-PP3-025U-100D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563237

CATALOG NUMBER: SQ4-PP3-025U-100D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80
1	105	100	96	93	100	96	93	90	88	86	83	81	79	77	74	73	71	68
2	96	88	82	76	91	85	79	74	78	73	69	72	68	65	66	63	60	57
3	88	78	70	64	83	75	68	62	69	63	59	64	59	55	59	55	52	49
4	80	69	61	55	76	66	59	53	61	55	50	57	52	47	52	48	45	42
5	74	62	53	47	70	59	52	46	55	49	44	51	46	41	47	43	39	37
6	68	56	47	41	65	54	46	40	50	43	38	46	41	36	43	38	35	32
7	63	50	42	36	60	49	41	35	45	39	34	42	37	32	39	34	31	29
8	59	46	38	32	56	44	37	32	41	35	30	39	33	29	36	31	28	26
9	55	42	34	29	52	41	33	28	38	32	27	36	30	26	33	29	25	23
10	51	39	31	26	49	38	30	26	35	29	25	33	28	24	31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10951	10951	10951
5°	11031	10963	10925
10°	11012	10934	10886
15°	10940	10880	10820
20°	10867	10806	10724
25°	10738	10664	10558
30°	10539	10484	10351
35°	10263	10193	10064
40°	9935	9872	9760
45°	9664	9596	9501
50°	9317	9257	9168
55°	8835	8718	8651
60°	8043	7812	7774
65°	7085	6790	6768
70°	6117	5864	5864
75°	5265	5191	5118
80°	4642	4699	4587
85°	3634	3963	3963



TEST NUMBER: P563237

CATALOG NUMBER: SQ4-PP3-025U-100D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	336.7	2.9
10°-20°	961.4	8.4
20°-30°	1440.0	12.6
30°-40°	1689.1	14.8
40°-50°	1694.3	14.8
50°-60°	1445.4	12.7
60°-70°	942.7	8.3
70°-80°	472.9	4.1
80°-90°	132.8	1.2
90°-100°	173.4	1.5
100°-110°	455.8	4.0
110°-120°	472.7	4.1
120°-130°	379.1	3.3
130°-140°	297.5	2.6
140°-150°	228.3	2.0
150°-160°	164.5	1.4
160°-170°	100.6	0.9
170°-180°	34.0	0.3
0°-30°	2738.1	24.0
0°-40°	4427.2	38.8
0°-60°	7566.9	66.3
0°-90°	9115.3	79.8
90°-120°	1101.9	9.6
90°-150°	2006.9	17.6
90°-180°	2306.0	20.2
0°-180°	11421.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3561	3561	3561	3561	3561	
5°	3573	3540	3551	3539	3539	339
15°	3436	3402	3417	3404	3398	969
25°	3164	3128	3142	3114	3111	1455
35°	2734	2706	2715	2684	2681	1708
45°	2222	2207	2206	2184	2184	1711
55°	1648	1642	1626	1616	1613	1464
65°	974	955	933	927	930	972
75°	443	443	437	434	431	481
85°	103	112	112	112	112	121
90°	2	7	18	9	9	6
95°	23	90	299	154	105	25
105°	82	124	504	765	714	87
115°	146	177	404	805	919	144
125°	203	228	367	621	732	180
135°	242	266	356	501	568	187
145°	280	298	351	427	461	176
155°	317	326	351	386	397	146
165°	342	346	351	365	369	97
175°	356	356	354	358	358	34
180°	356	356	356	356	356	



TEST NUMBER: P563237

CATALOG NUMBER: SQ4-PP3-025U-100D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3560.7	3560.7	3560.7	3560.7	3560.7
2.5°	3583.2	3553.9	3560.7	3555.4	3540.7
5°	3573.2	3539.6	3551.3	3538.8	3538.8
7.5°	3548.8	3512.2	3523.9	3511.4	3510.8
10°	3526.4	3489.7	3501.4	3488.8	3485.8
12.5°	3493.9	3457.3	3471.4	3456.4	3455.8
15°	3435.9	3402.3	3417.1	3404.5	3398.4
17.5°	3370.3	3333.7	3351.6	3334.1	3331.6
20°	3320.4	3283.8	3301.7	3276.7	3276.7
22.5°	3260.5	3223.9	3244.3	3211.8	3211.8
25°	3164.4	3127.7	3142.5	3114.4	3111.3
27.5°	3050.1	3014.1	3029.5	2997.7	2997.1
30°	2967.8	2934.2	2952.2	2917.8	2914.7
32.5°	2877.9	2846.8	2859.8	2825.4	2822.3
35°	2733.7	2706.2	2715.0	2683.7	2680.7
37.5°	2582.0	2554.0	2563.9	2537.1	2535.9
40°	2474.7	2456.4	2459.1	2437.1	2431.0
42.5°	2374.8	2354.1	2356.7	2334.9	2333.6
45°	2221.9	2206.7	2206.3	2184.5	2184.5
47.5°	2059.6	2048.0	2044.7	2026.6	2025.9
50°	1947.3	1938.1	1934.8	1919.1	1916.1
52.5°	1830.0	1825.7	1815.0	1801.9	1801.3
55°	1647.7	1641.6	1625.9	1616.4	1613.4
57.5°	1449.9	1437.7	1419.9	1406.2	1408.7
60°	1307.6	1295.4	1270.1	1263.9	1263.9
62.5°	1170.3	1155.6	1130.3	1121.7	1126.6
65°	973.6	955.3	933.1	926.9	930.0
67.5°	795.1	778.7	754.6	754.5	752.1
70°	680.3	671.2	652.2	652.2	652.2
72.5°	577.9	573.7	559.8	559.8	557.4
75°	443.1	443.1	436.9	433.7	430.7
77.5°	332.0	333.3	330.2	326.9	321.4
80°	262.1	268.2	265.3	262.1	259.0
82.5°	197.2	203.3	202.8	197.2	196.6
85°	103.0	112.1	112.3	112.3	112.3
87.5°	27.9	38.6	43.6	41.8	44.3
90°	2.3	6.7	18.2	9.1	9.1
92.5°	9.6	46.1	102.2	45.2	29.2
95°	22.8	89.7	298.7	154.0	104.9
97.5°	39.7	98.5	447.0	355.5	261.8
100°	52.5	106.0	492.6	499.2	387.7
102.5°	63.4	113.3	505.4	621.8	526.3
105°	82.1	124.5	504.0	765.1	713.8
107.5°	101.3	140.5	475.3	839.5	852.0
110°	114.0	149.7	451.5	858.7	912.2

TEST NUMBER: P563237

CATALOG NUMBER: SQ4-PP3-025U-100D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	126.8	160.7	429.7	846.6	928.6
115°	146.0	177.2	403.7	805.3	919.1
117.5°	164.7	193.2	385.9	748.1	874.4
120°	175.6	202.4	378.6	709.7	832.4
122.5°	186.5	213.3	373.1	671.4	792.3
125°	203.0	227.5	367.2	620.6	732.0
127.5°	216.2	241.2	362.1	579.6	673.7
130°	223.5	250.2	360.3	553.9	640.8
132.5°	230.8	257.5	358.5	531.8	609.8
135°	241.7	266.3	355.8	501.0	567.9
137.5°	253.1	277.2	355.3	477.9	532.7
140°	262.3	284.6	353.5	459.6	510.8
142.5°	269.6	290.1	353.5	446.6	490.8
145°	280.5	298.3	351.2	427.2	460.7
147.5°	291.5	308.8	351.2	411.1	438.8
150°	298.7	314.4	351.2	401.9	424.2
152.5°	306.0	318.1	351.2	394.5	411.4
155°	317.0	325.9	351.2	385.7	396.8
157.5°	325.2	333.7	351.2	377.8	385.9
160°	330.7	337.4	351.2	374.1	378.6
162.5°	336.1	341.1	351.2	370.5	374.9
165°	342.1	346.5	351.2	365.0	369.4
167.5°	347.6	349.8	353.5	362.6	364.4
170°	351.2	353.4	353.5	362.6	362.6
172.5°	353.0	353.5	353.5	360.7	359.0
175°	355.8	355.8	353.5	358.0	358.0
177.5°	355.8	355.8	353.9	357.5	355.8
180°	355.8	355.8	355.8	355.8	355.8

(END OF REPORT)