

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564358

Luminaire Tested: **SQ4-PR1-125U-075D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564358
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-075D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7857.3 lumens
Efficiency: N/A
Efficacy: 141.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564358
CATALOG NUMBER: SQ4-PR1-125U-075D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564358

CATALOG NUMBER: SQ4-PR1-125U-075D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	87	79	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26
3	79	70	63	57	71	64	58	53	52	48	44	41	38	35	31	29	27	23
4	72	62	54	49	65	56	50	45	46	41	38	36	33	30	28	25	24	19
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	21	17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	45	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10541	10541	10541
5°	10636	10553	10499
10°	10602	10528	10473
15°	10556	10490	10433
20°	10503	10435	10357
25°	10428	10358	10238
30°	10316	10242	10095
35°	10164	10075	9931
40°	9931	9825	9647
45°	9528	9361	9167
50°	8814	8602	8433
55°	7694	7518	7361
60°	6482	6429	6301
65°	5606	5628	5587
70°	5150	5177	5177
75°	4948	4948	4980
80°	4654	4707	4654
85°	3747	4171	4171



TEST NUMBER: P564358

CATALOG NUMBER: SQ4-PR1-125U-075D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.0	1.4
10°-20°	309.1	3.9
20°-30°	466.2	5.9
30°-40°	555.5	7.1
40°-50°	547.7	7.0
50°-60°	418.6	5.3
60°-70°	259.0	3.3
70°-80°	147.1	1.9
80°-90°	46.6	0.6
90°-100°	362.3	4.6
100°-110°	975.9	12.4
110°-120°	1024.2	13.0
120°-130°	831.1	10.6
130°-140°	651.8	8.3
140°-150°	500.4	6.4
150°-160°	359.8	4.6
160°-170°	219.8	2.8
170°-180°	74.1	0.9
0°-30°	883.4	11.2
0°-40°	1438.9	18.3
0°-60°	2405.2	30.6
0°-90°	2857.9	36.4
90°-120°	2362.3	30.1
90°-150°	4345.6	55.3
90°-180°	4999.0	63.6
0°-180°	7857.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1142	1142	1142	1142	1142	
5°	1148	1136	1140	1136	1134	109
15°	1105	1094	1098	1094	1092	312
25°	1024	1012	1018	1007	1006	471
35°	902	892	894	883	882	563
45°	730	721	717	704	703	559
55°	478	471	467	460	458	429
65°	257	255	258	256	256	260
75°	139	139	139	140	140	147
85°	35	37	39	39	39	41
90°	2	6	12	13	13	5
95°	55	197	594	304	210	58
105°	180	281	1079	1615	1515	190
115°	319	390	899	1736	1964	314
125°	435	500	807	1364	1605	389
135°	524	585	784	1100	1246	404
145°	606	653	774	941	1010	380
155°	688	713	768	844	871	317
165°	746	754	770	801	805	210
175°	775	774	772	782	780	74
180°	774	774	774	774	774	

TEST NUMBER: P564358

CATALOG NUMBER: SQ4-PR1-125U-075D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1142.5	1142.5	1142.5	1142.5	1142.5
2.5°	1149.6	1139.6	1142.5	1140.0	1134.6
5°	1148.4	1135.9	1139.5	1135.6	1133.6
7.5°	1139.5	1127.2	1130.9	1126.9	1125.8
10°	1131.7	1120.1	1123.8	1119.8	1117.9
12.5°	1123.0	1110.7	1115.1	1110.4	1108.4
15°	1105.1	1093.6	1098.2	1094.2	1092.3
17.5°	1085.4	1073.1	1077.7	1073.2	1070.7
20°	1069.7	1058.1	1062.8	1055.9	1054.9
22.5°	1052.4	1040.8	1045.5	1036.2	1036.0
25°	1024.4	1011.9	1017.5	1006.7	1005.7
27.5°	991.1	979.6	984.3	973.2	972.1
30°	968.3	956.8	961.4	949.6	947.6
32.5°	942.3	931.6	935.4	923.6	922.5
35°	902.4	891.8	894.5	882.7	881.7
37.5°	856.9	847.3	848.9	835.8	834.9
40°	824.6	815.0	815.8	802.0	801.0
42.5°	789.2	779.6	778.8	765.0	764.0
45°	730.2	720.6	717.4	704.5	702.6
47.5°	662.9	653.2	647.3	636.9	635.5
50°	614.1	604.4	599.3	590.4	587.5
52.5°	561.3	551.7	547.3	539.2	536.3
55°	478.3	470.6	467.4	459.5	457.6
57.5°	399.3	394.1	393.2	385.5	384.8
60°	351.3	348.4	348.4	341.5	341.5
62.5°	310.4	308.3	309.8	305.2	304.5
65°	256.8	254.9	257.8	255.9	255.9
67.5°	214.5	214.5	216.3	215.5	215.5
70°	190.9	190.9	191.9	191.9	191.9
72.5°	169.7	168.9	171.4	171.4	170.6
75°	138.8	138.8	138.8	139.7	139.7
77.5°	108.0	108.2	109.0	108.8	108.0
80°	87.6	88.5	88.6	87.6	87.6
82.5°	67.1	68.1	68.1	67.9	67.1
85°	35.4	37.4	39.4	39.4	39.4
87.5°	10.6	14.5	18.1	18.3	17.5
90°	2.0	5.8	11.8	12.8	12.8
92.5°	24.1	85.0	168.1	80.9	56.2
95°	55.2	197.0	593.9	303.7	210.1
97.5°	88.2	225.6	931.5	778.2	586.8
100°	113.4	236.9	1038.8	1086.9	901.7
102.5°	137.9	252.9	1074.3	1318.1	1166.1
105°	180.5	280.9	1079.3	1614.6	1515.3
107.5°	220.8	310.3	1033.3	1767.0	1792.7
110°	247.6	332.5	991.5	1814.4	1907.9



TEST NUMBER: P564358

CATALOG NUMBER: SQ4-PR1-125U-075D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	276.0	354.7	951.2	1803.9	1957.7
115°	318.6	390.0	898.7	1736.5	1964.2
117.5°	357.5	424.5	858.1	1629.0	1882.5
120°	382.8	447.4	837.6	1551.8	1812.2
122.5°	404.9	468.7	822.6	1472.9	1732.5
125°	435.1	499.7	807.0	1363.9	1605.1
127.5°	464.1	527.7	797.1	1267.8	1483.1
130°	481.4	545.1	793.2	1212.8	1401.8
132.5°	498.8	561.7	789.2	1164.3	1337.9
135°	523.8	584.6	784.3	1100.3	1246.0
137.5°	547.7	606.0	781.7	1046.1	1165.7
140°	564.3	620.2	779.4	1012.7	1120.7
142.5°	581.7	633.7	777.8	981.5	1072.5
145°	605.7	653.0	774.4	940.7	1010.2
147.5°	631.8	672.9	771.1	906.5	961.1
150°	649.1	684.8	769.5	885.0	930.3
152.5°	664.9	696.0	768.7	867.4	904.2
155°	687.6	712.7	767.5	844.1	871.1
157.5°	707.5	727.0	767.7	827.7	845.8
160°	720.2	736.6	768.5	818.1	831.6
162.5°	731.2	744.5	769.3	810.2	819.8
165°	745.8	754.5	770.5	801.1	805.0
167.5°	757.6	762.7	771.5	794.2	795.7
170°	765.5	767.5	771.5	790.2	790.2
172.5°	770.3	770.7	772.2	786.3	786.3
175°	775.4	774.4	771.5	782.3	780.3
177.5°	777.6	776.0	772.1	778.3	776.8
180°	774.4	774.4	774.4	774.4	774.4

(END OF REPORT)