

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563693

Luminaire Tested: **SQ4-PP3-125U-075D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563693
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-075D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18797.9 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 172.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563693
CATALOG NUMBER: SQ4-PP3-125U-075D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563693

CATALOG NUMBER: SQ4-PP3-125U-075D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				37
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37				31	
2	87	79	73	68	78	72	67	63	59	55	52	46	44	41	34	33	32				26	
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	31	29	27				22	
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23				19	
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20				17	
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18				15	
7	56	44	37	31	51	41	34	29	33	28	24	27	23	20	20	18	16				13	
8	52	40	33	27	47	37	30	26	30	25	22	24	21	18	19	16	14				12	
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13				11	
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12				10	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8241	8241	8241
5°	8302	8251	8222
10°	8288	8229	8193
15°	8233	8188	8143
20°	8179	8133	8071
25°	8081	8026	7946
30°	7932	7890	7790
35°	7724	7671	7574
40°	7477	7430	7345
45°	7273	7222	7151
50°	7012	6967	6900
55°	6649	6561	6511
60°	6053	5880	5851
65°	5333	5110	5093
70°	4604	4414	4414
75°	3963	3907	3851
80°	3494	3535	3452
85°	2735	2985	2985



TEST NUMBER: P563693

CATALOG NUMBER: SQ4-PP3-125U-075D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.4	1.3
10°-20°	723.6	3.8
20°-30°	1083.8	5.8
30°-40°	1271.2	6.8
40°-50°	1275.2	6.8
50°-60°	1087.8	5.8
60°-70°	709.5	3.8
70°-80°	355.9	1.9
80°-90°	102.8	0.5
90°-100°	864.9	4.6
100°-110°	2329.7	12.4
110°-120°	2444.9	13.0
120°-130°	1984.0	10.6
130°-140°	1556.0	8.3
140°-150°	1194.6	6.4
150°-160°	858.9	4.6
160°-170°	524.8	2.8
170°-180°	177.0	0.9
0°-30°	2060.7	11.0
0°-40°	3331.9	17.7
0°-60°	5695.0	30.3
0°-90°	6863.2	36.5
90°-120°	5639.5	30.0
90°-150°	10374.1	55.2
90°-180°	11935.0	63.5
0°-180°	18797.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2680	2680	2680	2680	2680	
5°	2689	2664	2673	2663	2663	255
15°	2586	2561	2572	2562	2558	730
25°	2382	2354	2365	2344	2342	1095
35°	2057	2037	2043	2020	2018	1285
45°	1672	1661	1660	1644	1644	1288
55°	1240	1236	1224	1217	1214	1102
65°	733	719	702	698	700	731
75°	334	334	329	326	324	362
85°	78	84	85	85	85	91
90°	5	14	28	31	31	12
95°	132	470	1418	725	502	138
105°	431	670	2576	3855	3617	453
115°	761	931	2146	4146	4689	749
125°	1039	1193	1926	3256	3832	927
135°	1251	1396	1872	2627	2974	965
145°	1446	1559	1849	2246	2412	907
155°	1642	1701	1832	2015	2080	756
165°	1780	1801	1839	1912	1922	502
175°	1851	1849	1842	1868	1863	176
180°	1849	1849	1849	1849	1849	

TEST NUMBER: P563693

CATALOG NUMBER: SQ4-PP3-125U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2679.8	2679.8	2679.8	2679.8	2679.8
2.5°	2696.7	2674.7	2679.8	2675.8	2664.8
5°	2689.2	2664.0	2672.8	2663.4	2663.4
7.5°	2670.9	2643.3	2652.1	2642.7	2642.2
10°	2654.0	2626.4	2635.2	2625.8	2623.5
12.5°	2629.6	2602.0	2612.7	2601.4	2600.9
15°	2585.9	2560.6	2571.8	2562.3	2557.7
17.5°	2536.6	2509.0	2522.5	2509.3	2507.4
20°	2499.0	2471.4	2484.9	2466.1	2466.1
22.5°	2453.9	2426.3	2441.7	2417.2	2417.2
25°	2381.5	2354.0	2365.1	2343.9	2341.6
27.5°	2295.6	2268.5	2280.1	2256.1	2255.7
30°	2233.6	2208.3	2221.8	2195.9	2193.6
32.5°	2165.9	2142.5	2152.3	2126.4	2124.1
35°	2057.4	2036.8	2043.3	2019.8	2017.5
37.5°	1943.3	1922.2	1929.7	1909.4	1908.5
40°	1862.5	1848.7	1850.7	1834.2	1829.6
42.5°	1787.3	1771.7	1773.7	1757.2	1756.3
45°	1672.2	1660.8	1660.5	1644.1	1644.1
47.5°	1550.1	1541.4	1538.8	1525.2	1524.8
50°	1465.6	1458.7	1456.2	1444.4	1442.1
52.5°	1377.3	1374.0	1366.0	1356.1	1355.6
55°	1240.1	1235.5	1223.7	1216.6	1214.3
57.5°	1091.2	1082.0	1068.6	1058.3	1060.2
60°	984.1	974.9	955.9	951.2	951.2
62.5°	880.7	869.7	850.7	844.2	847.9
65°	732.8	719.0	702.2	697.6	699.9
67.5°	598.4	586.0	567.9	567.9	566.0
70°	512.0	505.1	490.9	490.9	490.9
72.5°	435.0	431.8	421.3	421.3	419.5
75°	333.5	333.5	328.8	326.4	324.1
77.5°	249.9	250.8	248.5	246.0	241.9
80°	197.3	201.9	199.6	197.2	194.9
82.5°	148.4	153.0	152.7	148.4	148.0
85°	77.5	84.4	84.6	84.6	84.6
87.5°	21.6	30.8	35.7	36.2	38.1
90°	4.7	13.9	28.3	30.6	30.6
92.5°	57.5	203.0	401.3	193.2	134.2
95°	131.9	470.4	1417.8	725.0	501.6
97.5°	210.5	538.5	2223.7	1857.7	1400.8
100°	270.8	565.6	2479.9	2594.7	2152.5
102.5°	329.2	603.7	2564.7	3146.6	2783.7
105°	431.0	670.5	2576.5	3854.6	3617.4
107.5°	527.1	740.8	2466.7	4218.4	4279.7
110°	591.1	793.8	2366.9	4331.4	4554.7

TEST NUMBER: P563693

CATALOG NUMBER: SQ4-PP3-125U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.0	846.9	2270.8	4306.4	4673.4
115°	760.7	931.1	2145.5	4145.5	4689.0
117.5°	853.5	1013.3	2048.5	3888.8	4494.0
120°	913.8	1068.1	1999.5	3704.5	4326.3
122.5°	966.5	1119.0	1963.7	3516.1	4136.0
125°	1038.6	1192.9	1926.5	3256.0	3831.7
127.5°	1107.8	1259.8	1902.9	3026.7	3540.6
130°	1149.3	1301.3	1893.5	2895.2	3346.6
132.5°	1190.7	1340.9	1884.1	2779.5	3194.0
135°	1250.6	1395.6	1872.3	2626.8	2974.5
137.5°	1307.5	1446.6	1866.2	2497.2	2782.8
140°	1347.1	1480.7	1860.5	2417.5	2675.4
142.5°	1388.6	1512.9	1856.7	2343.1	2560.4
145°	1446.0	1558.9	1848.7	2245.8	2411.6
147.5°	1508.2	1606.3	1840.7	2164.0	2294.3
150°	1549.6	1634.8	1837.0	2112.6	2220.8
152.5°	1587.3	1661.5	1835.1	2070.7	2158.7
155°	1641.5	1701.4	1832.3	2015.1	2079.5
157.5°	1689.1	1735.6	1832.7	1976.0	2019.2
160°	1719.2	1758.4	1834.6	1953.1	1985.3
162.5°	1745.6	1777.4	1836.5	1934.0	1957.1
165°	1780.4	1801.2	1839.3	1912.5	1921.7
167.5°	1808.7	1820.7	1841.7	1895.9	1899.6
170°	1827.5	1832.2	1841.7	1886.4	1886.4
172.5°	1838.9	1839.8	1843.6	1877.0	1877.0
175°	1851.1	1848.8	1841.7	1867.5	1862.9
177.5°	1856.3	1852.6	1843.1	1858.1	1854.4
180°	1848.7	1848.7	1848.7	1848.7	1848.7

(END OF REPORT)