

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563741

Luminaire Tested: **SQ4-PP3-125U-125D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563741
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23569.0 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 233.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563741
CATALOG NUMBER: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563741

CATALOG NUMBER: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30				
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23				
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13974	13974	13974
5°	14077	13991	13942
10°	14053	13953	13891
15°	13960	13884	13808
20°	13868	13790	13685
25°	13703	13608	13473
30°	13449	13378	13209
35°	13097	13008	12843
40°	12678	12598	12455
45°	12332	12246	12124
50°	11889	11813	11699
55°	11274	11125	11039
60°	10263	9969	9921
65°	9042	8665	8636
70°	7807	7484	7484
75°	6720	6624	6531
80°	5924	5995	5853
85°	4637	5060	5060



TEST NUMBER: P563741

CATALOG NUMBER: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	429.7	1.8
10°-20°	1226.9	5.2
20°-30°	1837.7	7.8
30°-40°	2155.5	9.1
40°-50°	2162.2	9.2
50°-60°	1844.5	7.8
60°-70°	1202.9	5.1
70°-80°	603.5	2.6
80°-90°	171.4	0.7
90°-100°	864.9	3.7
100°-110°	2329.7	9.9
110°-120°	2444.9	10.4
120°-130°	1984.0	8.4
130°-140°	1556.0	6.6
140°-150°	1194.6	5.1
150°-160°	858.9	3.6
160°-170°	524.8	2.2
170°-180°	177.0	0.8
0°-30°	3494.2	14.8
0°-40°	5649.7	24.0
0°-60°	9656.4	41.0
0°-90°	11634.2	49.4
90°-120°	5639.5	23.9
90°-150°	10374.1	44.0
90°-180°	11935.0	50.6
0°-180°	23569.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4544	4544	4544	4544	4544	
5°	4560	4517	4532	4516	4516	433
15°	4385	4342	4361	4345	4337	1237
25°	4038	3991	4010	3974	3970	1857
35°	3489	3454	3465	3425	3421	2179
45°	2836	2816	2816	2788	2788	2183
55°	2103	2095	2075	2063	2059	1869
65°	1242	1219	1191	1183	1187	1240
75°	566	566	558	554	550	613
85°	131	143	143	143	143	155
90°	5	14	28	31	31	14
95°	132	470	1418	725	502	138
105°	431	670	2576	3855	3617	453
115°	761	931	2146	4146	4689	749
125°	1039	1193	1926	3256	3832	927
135°	1251	1396	1872	2627	2974	965
145°	1446	1559	1849	2246	2412	907
155°	1642	1701	1832	2015	2080	756
165°	1780	1801	1839	1912	1922	502
175°	1851	1849	1842	1868	1863	176
180°	1849	1849	1849	1849	1849	

TEST NUMBER: P563741

CATALOG NUMBER: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4543.9	4543.9	4543.9	4543.9	4543.9
2.5°	4572.6	4535.2	4543.9	4537.1	4518.4
5°	4559.8	4517.0	4532.0	4516.0	4516.0
7.5°	4528.8	4482.1	4496.9	4481.0	4480.2
10°	4500.1	4453.4	4468.2	4452.2	4448.3
12.5°	4458.7	4412.0	4430.0	4410.9	4410.1
15°	4384.6	4341.8	4360.7	4344.6	4336.8
17.5°	4301.0	4254.3	4277.1	4254.7	4251.6
20°	4237.3	4190.5	4213.4	4181.5	4181.5
22.5°	4160.8	4114.1	4140.1	4098.7	4098.7
25°	4038.1	3991.4	4010.3	3974.3	3970.4
27.5°	3892.4	3846.4	3866.1	3825.5	3824.7
30°	3787.3	3744.4	3767.3	3723.5	3719.6
32.5°	3672.6	3632.8	3649.5	3605.6	3601.7
35°	3488.6	3453.5	3464.7	3424.8	3420.9
37.5°	3295.0	3259.2	3271.9	3237.7	3236.1
40°	3158.0	3134.7	3138.1	3110.1	3102.3
42.5°	3030.6	3004.1	3007.5	2979.6	2978.0
45°	2835.5	2816.0	2815.6	2787.7	2787.7
47.5°	2628.4	2613.6	2609.3	2586.1	2585.4
50°	2485.0	2473.3	2469.1	2449.1	2445.2
52.5°	2335.3	2329.8	2316.2	2299.4	2298.6
55°	2102.7	2094.9	2074.8	2062.8	2058.9
57.5°	1850.2	1834.6	1812.0	1794.5	1797.7
60°	1668.6	1653.0	1620.8	1612.9	1612.9
62.5°	1493.4	1474.7	1442.4	1431.4	1437.6
65°	1242.5	1219.1	1190.7	1182.9	1186.8
67.5°	1014.7	993.7	962.9	962.9	959.8
70°	868.2	856.5	832.3	832.3	832.3
72.5°	737.5	732.1	714.4	714.4	711.3
75°	565.5	565.5	557.5	553.5	549.6
77.5°	423.7	425.3	421.3	417.2	410.2
80°	334.5	342.3	338.5	334.4	330.5
82.5°	251.7	259.5	258.9	251.7	250.9
85°	131.4	143.1	143.4	143.4	143.4
87.5°	36.0	50.3	56.6	57.2	60.3
90°	4.7	13.9	28.3	30.6	30.6
92.5°	57.5	203.0	401.3	193.2	134.2
95°	131.9	470.4	1417.8	725.0	501.6
97.5°	210.5	538.5	2223.7	1857.7	1400.8
100°	270.8	565.6	2479.9	2594.7	2152.5
102.5°	329.2	603.7	2564.7	3146.6	2783.7
105°	431.0	670.5	2576.5	3854.6	3617.4
107.5°	527.1	740.8	2466.7	4218.4	4279.7
110°	591.1	793.8	2366.9	4331.4	4554.7



TEST NUMBER: P563741

CATALOG NUMBER: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.0	846.9	2270.8	4306.4	4673.4
115°	760.7	931.1	2145.5	4145.5	4689.0
117.5°	853.5	1013.3	2048.5	3888.8	4494.0
120°	913.8	1068.1	1999.5	3704.5	4326.3
122.5°	966.5	1119.0	1963.7	3516.1	4136.0
125°	1038.6	1192.9	1926.5	3256.0	3831.7
127.5°	1107.8	1259.8	1902.9	3026.7	3540.6
130°	1149.3	1301.3	1893.5	2895.2	3346.6
132.5°	1190.7	1340.9	1884.1	2779.5	3194.0
135°	1250.6	1395.6	1872.3	2626.8	2974.5
137.5°	1307.5	1446.6	1866.2	2497.2	2782.8
140°	1347.1	1480.7	1860.5	2417.5	2675.4
142.5°	1388.6	1512.9	1856.7	2343.1	2560.4
145°	1446.0	1558.9	1848.7	2245.8	2411.6
147.5°	1508.2	1606.3	1840.7	2164.0	2294.3
150°	1549.6	1634.8	1837.0	2112.6	2220.8
152.5°	1587.3	1661.5	1835.1	2070.7	2158.7
155°	1641.5	1701.4	1832.3	2015.1	2079.5
157.5°	1689.1	1735.6	1832.7	1976.0	2019.2
160°	1719.2	1758.4	1834.6	1953.1	1985.3
162.5°	1745.6	1777.4	1836.5	1934.0	1957.1
165°	1780.4	1801.2	1839.3	1912.5	1921.7
167.5°	1808.7	1820.7	1841.7	1895.9	1899.6
170°	1827.5	1832.2	1841.7	1886.4	1886.4
172.5°	1838.9	1839.8	1843.6	1877.0	1877.0
175°	1851.1	1848.8	1841.7	1867.5	1862.9
177.5°	1856.3	1852.6	1843.1	1858.1	1854.4
180°	1848.7	1848.7	1848.7	1848.7	1848.7

(END OF REPORT)