

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564293

Luminaire Tested: **SQ4-PR1-100U-100D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564293
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-100U-100D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18650.6 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 182.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564293
CATALOG NUMBER: SQ4-PR1-100U-100D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P564293

CATALOG NUMBER: SQ4-PR1-100U-100D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41				
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	42	40	35				
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	39	36	34	30				
4	75	64	56	50	69	59	53	47	51	45	41	42	39	35	35	32	30	26				
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23				
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20				
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	28	34	28	25	29	24	21	24	21	18	16				
9	51	38	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14				
10	47	35	28	23	44	33	27	22	29	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11145	11145	11145
5°	11246	11159	11101
10°	11210	11132	11073
15°	11160	11091	11032
20°	11105	11033	10951
25°	11026	10952	10825
30°	10907	10830	10674
35°	10746	10653	10500
40°	10501	10388	10200
45°	10073	9897	9693
50°	9319	9095	8916
55°	8134	7950	7783
60°	6854	6797	6662
65°	5929	5951	5906
70°	5445	5473	5473
75°	5229	5229	5266
80°	4920	4975	4920
85°	3966	4407	4407



TEST NUMBER: P564293

CATALOG NUMBER: SQ4-PR1-100U-100D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	342.7	1.8
10°-20°	980.5	5.3
20°-30°	1478.9	7.9
30°-40°	1762.1	9.4
40°-50°	1737.3	9.3
50°-60°	1327.7	7.1
60°-70°	821.7	4.4
70°-80°	466.7	2.5
80°-90°	145.0	0.8
90°-100°	691.1	3.7
100°-110°	1907.8	10.2
110°-120°	1967.5	10.5
120°-130°	1581.1	8.5
130°-140°	1242.6	6.7
140°-150°	953.0	5.1
150°-160°	684.9	3.7
160°-170°	418.9	2.2
170°-180°	141.2	0.8
0°-30°	2802.1	15.0
0°-40°	4564.2	24.5
0°-60°	7629.2	40.9
0°-90°	9062.6	48.6
90°-120°	4566.4	24.5
90°-150°	8343.0	44.7
90°-180°	9588.0	51.4
0°-180°	18650.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3624	3624	3624	3624	3624	
5°	3643	3603	3615	3602	3596	346
15°	3505	3469	3484	3471	3465	989
25°	3249	3210	3228	3193	3190	1495
35°	2862	2829	2837	2800	2797	1786
45°	2316	2286	2276	2235	2229	1774
55°	1517	1493	1483	1458	1452	1359
65°	815	809	818	812	812	825
75°	440	440	440	443	443	465
85°	112	118	125	125	125	131
90°	5	9	19	21	24	12
95°	102	374	1254	515	335	109
105°	340	525	2099	3204	3017	362
115°	609	736	1690	3347	3806	599
125°	836	951	1532	2593	3043	744
135°	1006	1114	1490	2100	2368	778
145°	1166	1247	1471	1788	1924	730
155°	1315	1359	1459	1604	1655	606
165°	1424	1442	1466	1523	1535	401
175°	1476	1478	1469	1490	1485	140
180°	1476	1476	1476	1476	1476	

TEST NUMBER: P564293

CATALOG NUMBER: SQ4-PR1-100U-100D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3624.0	3624.0	3624.0	3624.0	3624.0
2.5°	3646.4	3614.7	3624.0	3616.1	3599.0
5°	3642.7	3603.0	3614.6	3602.0	3595.9
7.5°	3614.6	3575.5	3587.1	3574.5	3570.9
10°	3589.6	3553.0	3564.6	3552.0	3545.9
12.5°	3562.1	3523.1	3537.2	3522.1	3515.9
15°	3505.3	3468.7	3483.5	3470.9	3464.8
17.5°	3442.9	3403.8	3418.6	3404.0	3396.1
20°	3393.0	3356.3	3371.1	3349.2	3346.1
22.5°	3338.0	3301.4	3316.2	3286.8	3286.2
25°	3249.4	3209.7	3227.5	3193.1	3190.1
27.5°	3143.9	3107.3	3122.0	3087.0	3083.3
30°	3071.5	3034.8	3049.6	3012.0	3005.9
32.5°	2989.1	2954.9	2967.2	2929.7	2926.0
35°	2862.3	2828.8	2837.4	2799.8	2796.8
37.5°	2718.1	2687.6	2692.5	2651.3	2648.2
40°	2615.7	2585.2	2587.6	2543.9	2540.8
42.5°	2503.4	2472.8	2470.3	2426.5	2423.5
45°	2316.1	2285.6	2275.5	2234.8	2228.7
47.5°	2102.6	2072.1	2053.3	2020.1	2015.8
50°	1947.8	1917.2	1900.9	1872.6	1863.5
52.5°	1780.4	1749.9	1736.1	1710.3	1701.2
55°	1517.0	1492.6	1482.7	1457.6	1451.5
57.5°	1266.7	1250.2	1247.3	1222.9	1220.5
60°	1114.3	1105.2	1105.0	1083.1	1083.1
62.5°	984.5	977.8	982.6	968.2	965.8
65°	814.7	808.6	817.8	811.6	811.6
67.5°	680.5	680.5	686.1	683.6	683.6
70°	605.6	605.6	608.7	608.7	608.7
72.5°	538.1	535.7	543.7	543.7	541.3
75°	440.1	440.1	440.1	443.2	443.2
77.5°	342.7	343.3	345.9	345.2	342.7
80°	277.8	280.9	280.9	277.8	277.8
82.5°	212.9	215.9	216.0	215.3	212.9
85°	112.4	118.5	124.9	124.9	124.9
87.5°	33.4	44.1	53.7	54.1	52.2
90°	4.7	9.3	18.9	21.3	23.6
92.5°	42.5	176.4	315.4	115.1	89.7
95°	101.5	373.9	1253.7	515.3	335.3
97.5°	168.1	418.8	1857.2	1429.9	1035.6
100°	217.2	445.8	2080.1	2094.8	1702.3
102.5°	264.4	476.4	2123.5	2588.2	2216.1
105°	340.0	524.7	2099.0	3204.4	3017.4
107.5°	420.3	584.6	1981.9	3501.6	3569.9
110°	476.9	624.7	1891.2	3565.5	3787.1



TEST NUMBER: P564293

CATALOG NUMBER: SQ4-PR1-100U-100D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	527.9	670.1	1806.2	3515.0	3841.9
115°	609.1	736.1	1690.5	3346.6	3806.0
117.5°	680.0	806.5	1614.5	3109.6	3632.2
120°	727.2	851.9	1584.3	2949.1	3475.5
122.5°	772.5	891.7	1559.7	2799.3	3297.9
125°	835.8	951.2	1532.3	2593.2	3043.4
127.5°	889.6	1005.1	1516.3	2419.0	2807.3
130°	925.5	1041.0	1508.7	2312.4	2665.6
132.5°	959.5	1069.4	1501.2	2222.9	2542.8
135°	1005.8	1114.3	1489.8	2100.3	2368.1
137.5°	1057.7	1156.6	1484.2	1997.4	2226.0
140°	1086.1	1183.0	1480.4	1928.8	2129.7
142.5°	1118.2	1207.8	1476.6	1867.8	2044.7
145°	1166.4	1247.2	1470.9	1788.0	1924.3
147.5°	1212.6	1283.3	1465.7	1720.8	1826.5
150°	1246.6	1304.3	1463.8	1680.6	1766.1
152.5°	1273.1	1327.1	1462.0	1646.3	1717.0
155°	1315.1	1359.0	1459.1	1604.3	1655.1
157.5°	1353.8	1387.5	1459.6	1573.7	1608.3
160°	1376.5	1406.5	1461.5	1556.5	1581.9
162.5°	1395.4	1421.7	1463.4	1541.3	1561.1
165°	1423.7	1442.2	1466.2	1523.1	1534.7
167.5°	1445.4	1456.5	1468.6	1512.1	1515.8
170°	1456.8	1466.0	1468.6	1506.3	1506.3
172.5°	1466.2	1471.7	1468.6	1498.7	1496.9
175°	1475.7	1478.0	1468.6	1489.7	1485.1
177.5°	1479.4	1477.6	1468.1	1481.2	1477.5
180°	1475.7	1475.7	1475.7	1475.7	1475.7

(END OF REPORT)