

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564413

Luminaire Tested: **SQ4-PR1-125U-125D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564413
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-125D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23500.2 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 233.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564413
CATALOG NUMBER: SQ4-PR1-125U-125D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P564413

CATALOG NUMBER: SQ4-PR1-125U-125D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49				49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47				42	
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40				36	
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35				31	
4	75	64	56	51	69	60	53	47	51	46	41	43	39	36	35	32	30				26	
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26				23	
6	63	51	43	38	58	48	41	36	41	36	31	35	30	27	29	26	23				20	
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21				18	
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19				16	
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17				15	
10	47	35	28	23	44	33	27	22	29	23	20	25	20	18	21	18	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14222	14222	14222
5°	14351	14240	14166
10°	14305	14206	14131
15°	14242	14154	14078
20°	14171	14079	13975
25°	14071	13976	13814
30°	13919	13820	13622
35°	13714	13594	13400
40°	13401	13257	13017
45°	12855	12629	12370
50°	11892	11606	11377
55°	10380	10145	9931
60°	8746	8673	8502
65°	7565	7594	7537
70°	6949	6984	6984
75°	6673	6673	6721
80°	6278	6349	6278
85°	5060	5621	5621



TEST NUMBER: P564413

CATALOG NUMBER: SQ4-PR1-125U-125D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	437.3	1.9
10°-20°	1251.2	5.3
20°-30°	1887.3	8.0
30°-40°	2248.7	9.6
40°-50°	2217.0	9.4
50°-60°	1694.3	7.2
60°-70°	1048.5	4.5
70°-80°	595.5	2.5
80°-90°	185.5	0.8
90°-100°	864.9	3.7
100°-110°	2329.7	9.9
110°-120°	2444.9	10.4
120°-130°	1984.0	8.4
130°-140°	1556.0	6.6
140°-150°	1194.6	5.1
150°-160°	858.9	3.7
160°-170°	524.8	2.2
170°-180°	177.0	0.8
0°-30°	3575.8	15.2
0°-40°	5824.5	24.8
0°-60°	9735.9	41.4
0°-90°	11565.4	49.2
90°-120°	5639.5	24.0
90°-150°	10374.1	44.1
90°-180°	11935.0	50.8
0°-180°	23500.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4625	4625	4625	4625	4625	
5°	4648	4598	4613	4597	4589	441
15°	4473	4426	4445	4429	4422	1262
25°	4147	4096	4119	4075	4071	1908
35°	3653	3610	3621	3573	3569	2280
45°	2956	2917	2904	2852	2844	2264
55°	1936	1905	1892	1860	1852	1735
65°	1040	1032	1044	1036	1036	1053
75°	562	562	562	566	566	593
85°	143	151	159	159	159	167
90°	5	14	28	31	31	15
95°	132	470	1418	725	502	138
105°	431	670	2576	3855	3617	453
115°	761	931	2146	4146	4689	749
125°	1039	1193	1926	3256	3832	927
135°	1251	1396	1872	2627	2974	965
145°	1446	1559	1849	2246	2412	907
155°	1642	1701	1832	2015	2080	756
165°	1780	1801	1839	1912	1922	502
175°	1851	1849	1842	1868	1863	176
180°	1849	1849	1849	1849	1849	

TEST NUMBER: P564413

CATALOG NUMBER: SQ4-PR1-125U-125D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4624.6	4624.6	4624.6	4624.6	4624.6
2.5°	4653.3	4612.8	4624.6	4614.6	4592.8
5°	4648.5	4597.9	4612.7	4596.6	4588.8
7.5°	4612.7	4562.8	4577.6	4561.6	4556.9
10°	4580.8	4534.1	4549.0	4532.9	4525.1
12.5°	4545.8	4495.9	4513.9	4494.6	4486.8
15°	4473.3	4426.5	4445.4	4429.3	4421.5
17.5°	4393.6	4343.8	4362.5	4344.0	4333.9
20°	4329.9	4283.1	4302.0	4274.0	4270.1
22.5°	4259.8	4213.0	4231.9	4194.4	4193.6
25°	4146.6	4096.0	4118.8	4074.9	4071.0
27.5°	4012.0	3965.3	3984.1	3939.4	3934.7
30°	3919.6	3872.9	3891.7	3843.7	3835.9
32.5°	3814.4	3770.8	3786.6	3738.6	3734.0
35°	3652.7	3609.9	3620.8	3573.0	3569.1
37.5°	3468.7	3429.7	3436.0	3383.4	3379.5
40°	3338.0	3299.1	3302.2	3246.3	3242.4
42.5°	3194.6	3155.7	3152.4	3096.6	3092.7
45°	2955.6	2916.7	2903.8	2851.9	2844.1
47.5°	2683.2	2644.2	2620.2	2577.9	2572.4
50°	2485.6	2446.6	2425.8	2389.7	2378.0
52.5°	2272.1	2233.1	2215.5	2182.6	2170.9
55°	1935.9	1904.7	1892.1	1860.0	1852.2
57.5°	1616.4	1595.4	1591.7	1560.6	1557.5
60°	1422.0	1410.4	1410.1	1382.2	1382.2
62.5°	1256.3	1247.8	1254.0	1235.6	1232.4
65°	1039.6	1031.9	1043.6	1035.7	1035.7
67.5°	868.4	868.4	875.5	872.3	872.3
70°	772.8	772.8	776.7	776.7	776.7
72.5°	686.7	683.6	693.9	693.8	690.7
75°	561.6	561.6	561.6	565.6	565.6
77.5°	437.4	438.1	441.4	440.5	437.4
80°	354.5	358.4	358.5	354.5	354.5
82.5°	271.7	275.6	275.6	274.8	271.7
85°	143.4	151.2	159.3	159.3	159.3
87.5°	42.4	56.7	69.4	69.8	66.7
90°	4.7	13.9	28.3	30.6	30.6
92.5°	57.5	203.0	401.3	193.2	134.2
95°	131.9	470.4	1417.8	725.0	501.6
97.5°	210.5	538.5	2223.7	1857.7	1400.8
100°	270.8	565.6	2479.9	2594.7	2152.5
102.5°	329.2	603.7	2564.7	3146.6	2783.7
105°	431.0	670.5	2576.5	3854.6	3617.4
107.5°	527.1	740.8	2466.7	4218.4	4279.7
110°	591.1	793.8	2366.9	4331.4	4554.7

TEST NUMBER: P564413

CATALOG NUMBER: SQ4-PR1-125U-125D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.0	846.9	2270.8	4306.4	4673.4
115°	760.7	931.1	2145.5	4145.5	4689.0
117.5°	853.5	1013.3	2048.5	3888.8	4494.0
120°	913.8	1068.1	1999.5	3704.5	4326.3
122.5°	966.5	1119.0	1963.7	3516.1	4136.0
125°	1038.6	1192.9	1926.5	3256.0	3831.7
127.5°	1107.8	1259.8	1902.9	3026.7	3540.6
130°	1149.3	1301.3	1893.5	2895.2	3346.6
132.5°	1190.7	1340.9	1884.1	2779.5	3194.0
135°	1250.6	1395.6	1872.3	2626.8	2974.5
137.5°	1307.5	1446.6	1866.2	2497.2	2782.8
140°	1347.1	1480.7	1860.5	2417.5	2675.4
142.5°	1388.6	1512.9	1856.7	2343.1	2560.4
145°	1446.0	1558.9	1848.7	2245.8	2411.6
147.5°	1508.2	1606.3	1840.7	2164.0	2294.3
150°	1549.6	1634.8	1837.0	2112.6	2220.8
152.5°	1587.3	1661.5	1835.1	2070.7	2158.7
155°	1641.5	1701.4	1832.3	2015.1	2079.5
157.5°	1689.1	1735.6	1832.7	1976.0	2019.2
160°	1719.2	1758.4	1834.6	1953.1	1985.3
162.5°	1745.6	1777.4	1836.5	1934.0	1957.1
165°	1780.4	1801.2	1839.3	1912.5	1921.7
167.5°	1808.7	1820.7	1841.7	1895.9	1899.6
170°	1827.5	1832.2	1841.7	1886.4	1886.4
172.5°	1838.9	1839.8	1843.6	1877.0	1877.0
175°	1851.1	1848.8	1841.7	1867.5	1862.9
177.5°	1856.3	1852.6	1843.1	1858.1	1854.4
180°	1848.7	1848.7	1848.7	1848.7	1848.7

(END OF REPORT)