

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519624

Luminaire Tested: **SQ4-WB-150U-125D-835-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519624  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-150U-125D-835-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10130.9 lumens  
Efficiency: N/A  
Efficacy: 121.9 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 83.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519624  
CATALOG NUMBER: SQ4-WB-150U-125D-835-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P519624

CATALOG NUMBER: SQ4-WB-150U-125D-835-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	97	93	89	86	88	85	82	79	70	68	66	56	55	53	43	43	42	36
2	89	82	76	72	81	75	70	66	62	59	56	50	48	46	39	38	37	32
3	82	73	66	61	74	67	61	57	56	52	48	45	43	40	36	34	32	28
4	75	65	58	52	68	60	54	49	50	46	42	41	38	35	33	31	29	25
5	69	59	51	46	63	54	48	43	45	41	37	37	34	31	30	28	26	22
6	64	53	45	40	59	49	42	38	41	36	33	34	31	28	28	25	23	20
7	59	48	41	35	54	45	38	33	38	33	29	31	28	25	25	23	21	18
8	55	44	37	32	51	41	34	30	35	30	26	29	25	23	24	21	19	17
9	52	40	33	28	47	37	31	27	32	27	24	27	23	21	22	19	18	15
10	48	37	30	26	44	34	28	24	30	25	22	25	21	19	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25990	25990	25990
5°	25666	25575	25724
10°	24250	24470	25036
15°	22385	22905	23933
20°	20328	21093	22489
25°	18233	19227	20951
30°	16303	17369	19358
35°	14257	15286	17472
40°	11999	12952	15126
45°	9903	10758	12629
50°	8268	9013	10521
55°	7018	7734	8689
60°	5999	6706	6934
65°	4777	5639	4480
70°	4235	4402	2735
75°	3921	3568	1675
80°	3613	3284	1445
85°	3271	3006	1175



TEST NUMBER: P519624

CATALOG NUMBER: SQ4-WB-150U-125D-835-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	258.4	2.6
10°-20°	672.1	6.6
20°-30°	870.5	8.6
30°-40°	852.5	8.4
40°-50°	652.5	6.4
50°-60°	434.8	4.3
60°-70°	237.3	2.3
70°-80°	98.9	1.0
80°-90°	30.0	0.3
90°-100°	434.2	4.3
100°-110°	1174.0	11.6
110°-120°	1234.3	12.2
120°-130°	1002.6	9.9
130°-140°	786.5	7.8
140°-150°	603.6	6.0
150°-160°	434.1	4.3
160°-170°	265.2	2.6
170°-180°	89.4	0.9
0°-30°	1801.0	17.8
0°-40°	2653.5	26.2
0°-60°	3740.8	36.9
0°-90°	4106.9	40.5
90°-120°	2842.6	28.1
90°-150°	5235.3	51.7
90°-180°	6024.0	59.5
0°-180°	10130.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2817	2817	2817	2817	2817	
5°	2771	2744	2761	2768	2778	258
15°	2344	2335	2398	2463	2506	654
25°	1791	1796	1889	1971	2058	824
35°	1266	1272	1357	1449	1551	787
45°	759	774	824	887	968	592
55°	436	454	481	499	540	396
65°	219	237	258	226	205	227
75°	110	110	100	69	47	117
85°	31	31	28	18	11	34
90°	2	6	13	14	13	6
95°	67	236	722	374	222	71
105°	218	337	1302	1921	1842	230
115°	384	470	1080	2091	2360	379
125°	526	603	974	1643	1930	469
135°	631	705	947	1326	1502	487
145°	733	788	934	1135	1222	459
155°	828	860	926	1019	1052	382
165°	901	910	930	967	972	254
175°	935	934	931	943	941	89
180°	934	934	934	934	934	

TEST NUMBER: P519624

CATALOG NUMBER: SQ4-WB-150U-125D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2817.0	2817.0	2817.0	2817.0	2817.0
2.5°	2824.0	2798.8	2805.2	2805.0	2797.3
5°	2771.3	2743.5	2761.4	2767.8	2777.5
7.5°	2668.5	2647.4	2680.1	2704.3	2723.8
10°	2588.4	2570.2	2611.9	2647.0	2672.4
12.5°	2495.4	2480.2	2531.8	2579.0	2612.1
15°	2343.6	2335.2	2398.0	2463.3	2505.6
17.5°	2181.2	2177.1	2249.2	2325.3	2379.5
20°	2070.4	2069.2	2148.3	2227.6	2290.5
22.5°	1958.7	1961.4	2044.5	2127.0	2198.5
25°	1791.1	1795.9	1888.7	1971.1	2058.1
27.5°	1636.1	1638.3	1734.2	1821.1	1914.0
30°	1530.3	1536.3	1630.4	1720.4	1817.1
32.5°	1424.5	1431.5	1523.6	1616.6	1715.2
35°	1265.8	1271.8	1357.2	1448.6	1551.3
37.5°	1102.1	1110.3	1186.2	1272.5	1373.5
40°	996.3	1008.4	1075.4	1156.8	1255.9
42.5°	894.4	909.4	971.6	1048.8	1138.2
45°	759.0	773.5	824.5	886.9	967.9
47.5°	642.3	659.0	698.1	751.9	821.0
50°	576.0	591.7	627.9	667.7	733.0
52.5°	517.7	533.4	565.6	596.3	651.9
55°	436.3	454.5	480.8	499.1	540.2
57.5°	369.6	387.0	407.9	416.1	441.0
60°	325.1	344.4	363.4	362.5	375.8
62.5°	284.5	301.0	319.9	306.8	307.5
65°	218.8	236.9	258.3	225.7	205.2
67.5°	176.8	180.6	202.7	157.4	133.0
70°	157.0	157.0	163.2	121.9	101.4
72.5°	138.2	138.2	132.5	99.1	77.6
75°	110.0	110.0	100.1	68.7	47.0
77.5°	84.8	83.8	76.6	51.3	34.1
80°	68.0	68.0	61.8	40.5	27.2
82.5°	53.2	53.2	48.0	31.6	20.3
85°	30.9	30.9	28.4	18.4	11.1
87.5°	11.3	12.1	12.5	8.7	7.6
90°	2.0	5.9	13.1	14.1	13.1
92.5°	28.6	104.1	205.4	89.2	64.6
95°	67.4	236.5	722.1	373.7	222.3
97.5°	108.2	271.3	1125.6	931.5	684.1
100°	138.8	285.3	1251.1	1304.8	1055.0
102.5°	167.0	304.8	1295.4	1587.8	1401.0
105°	218.2	337.2	1302.4	1921.2	1842.5
107.5°	265.7	374.3	1245.5	2129.1	2155.3
110°	302.7	401.1	1194.8	2185.0	2296.1

TEST NUMBER: P519624

CATALOG NUMBER: SQ4-WB-150U-125D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	335.7	427.8	1148.1	2173.8	2360.5
115°	384.2	469.7	1080.2	2091.0	2360.5
117.5°	431.7	511.9	1035.3	1964.5	2269.9
120°	460.6	539.3	1008.8	1873.7	2185.5
122.5°	488.0	565.1	992.7	1776.4	2090.5
125°	526.0	602.7	973.6	1642.9	1930.0
127.5°	561.0	636.3	962.3	1533.9	1786.4
130°	580.3	658.0	957.5	1466.5	1694.7
132.5°	600.4	677.3	952.6	1405.8	1615.8
135°	630.6	705.3	947.4	1326.5	1501.6
137.5°	661.0	731.6	943.0	1262.2	1404.8
140°	681.9	747.8	941.4	1220.8	1347.7
142.5°	702.0	764.0	938.1	1183.5	1294.6
145°	733.2	788.2	934.3	1135.4	1222.0
147.5°	761.5	810.3	929.9	1091.9	1158.4
150°	782.5	825.7	928.3	1068.3	1121.4
152.5°	801.8	839.5	927.5	1046.4	1090.0
155°	827.7	860.2	926.3	1018.6	1052.0
157.5°	854.7	877.3	926.5	999.2	1021.2
160°	870.0	888.6	927.3	987.0	1002.7
162.5°	882.0	897.6	928.1	977.2	989.0
165°	901.1	910.0	930.3	966.6	971.5
167.5°	914.2	920.3	930.5	957.5	959.9
170°	922.3	925.2	931.3	953.4	953.4
172.5°	928.7	929.3	931.3	948.6	947.8
175°	935.3	934.3	931.3	943.3	941.4
177.5°	937.5	935.2	931.1	939.1	936.7
180°	934.3	934.3	934.3	934.3	934.3

(END OF REPORT)