

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519649

Luminaire Tested: **SQ4-025U-0D-835-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519649
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-025U-0D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1448.9 lumens
Efficiency: N/A
Efficacy: 176.7 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519649
CATALOG NUMBER: SQ4-025U-0D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519649

CATALOG NUMBER: SQ4-025U-0D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	1009	13246	4651
100°	1169	10963	8629
105°	1226	7526	10659
110°	1288	5102	10308
115°	1335	3691	8405
120°	1357	2927	6434
125°	1367	2474	4933
130°	1343	2166	3853
135°	1321	1944	3104
140°	1323	1783	2577
145°	1324	1657	2174
150°	1333	1567	1893
155°	1352	1498	1692
160°	1360	1445	1557
165°	1368	1405	1478
170°	1378	1387	1423
175°	1380	1371	1389



TEST NUMBER: P519649

CATALOG NUMBER: SQ4-025U-0D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	108.9	7.5
100°-110°	286.4	19.8
110°-120°	297.0	20.5
120°-130°	238.2	16.4
130°-140°	186.9	12.9
140°-150°	143.5	9.9
150°-160°	103.3	7.1
160°-170°	63.2	4.4
170°-180°	21.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	692.3	47.8
90°-150°	1261.0	87.0
90°-180°	1449.0	100.0
0°-180°	1448.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	4	12	6	6	
95°	14	56	188	97	66	17
105°	52	78	317	481	448	55
115°	92	111	254	506	578	91
125°	128	143	231	390	460	113
135°	152	167	224	315	357	118
145°	176	188	221	268	290	110
155°	199	205	221	242	249	92
165°	215	218	221	229	232	61
175°	224	224	222	225	225	21
180°	224	224	224	224	224	



TEST NUMBER: P519649

CATALOG NUMBER: SQ4-025U-0D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.4	4.2	11.5	5.7	5.7
92.5°	6.0	29.0	64.2	28.4	18.3
95°	14.3	56.4	187.7	96.7	65.9
97.5°	24.9	61.9	280.9	223.3	164.5
100°	33.0	66.6	309.5	313.7	243.6
102.5°	39.8	71.2	317.5	390.7	330.7
105°	51.6	78.2	316.7	480.7	448.5
107.5°	63.6	88.3	298.6	527.5	535.3
110°	71.6	94.1	283.7	539.5	573.2
112.5°	79.7	101.0	270.0	531.9	583.5
115°	91.7	111.3	253.6	506.0	577.5
117.5°	103.5	121.4	242.5	470.1	549.4
120°	110.3	127.1	237.9	446.0	523.0
122.5°	117.2	134.0	234.4	421.9	497.8
125°	127.5	142.9	230.7	389.9	460.0
127.5°	135.8	151.5	227.5	364.2	423.3
130°	140.4	157.2	226.4	348.0	402.7
132.5°	145.0	161.8	225.3	334.1	383.2
135°	151.9	167.3	223.5	314.8	356.8
137.5°	159.1	174.2	223.3	300.3	334.7
140°	164.8	178.8	222.1	288.8	321.0
142.5°	169.4	182.3	222.1	280.6	308.4
145°	176.3	187.5	220.7	268.4	289.5
147.5°	183.1	194.1	220.7	258.3	275.7
150°	187.7	197.5	220.7	252.5	266.5
152.5°	192.3	199.9	220.7	247.9	258.5
155°	199.2	204.8	220.7	242.3	249.3
157.5°	204.3	209.7	220.7	237.4	242.5
160°	207.8	212.0	220.7	235.1	237.9
162.5°	211.2	214.3	220.7	232.8	235.6
165°	214.9	217.7	220.7	229.3	232.1
167.5°	218.4	219.8	222.1	227.9	229.0
170°	220.7	222.1	222.1	227.8	227.8
172.5°	221.8	222.1	222.1	226.7	225.5
175°	223.5	223.5	222.1	225.0	225.0
177.5°	223.5	223.5	222.4	224.7	223.5
180°	223.5	223.5	223.5	223.5	223.5

(END OF REPORT)