

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519697

Luminaire Tested: **SQ4-075U-0D-835-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519697
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4490.7 lumens
Efficiency: N/A
Efficacy: 162.7 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 27.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519697
CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519697

CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	3416	40572	11073
100°	3585	34443	28365
105°	3800	23423	33285
110°	3983	15957	31968
115°	4120	11505	25999
120°	4203	9112	20063
125°	4183	7691	15240
130°	4126	6737	11957
135°	4095	6060	9658
140°	4086	5559	8008
145°	4086	5154	6762
150°	4125	4854	5864
155°	4181	4629	5245
160°	4215	4464	4838
165°	4240	4361	4567
170°	4250	4287	4397
175°	4256	4238	4283



TEST NUMBER: P519697

CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	325.1	7.2
100°-110°	894.5	19.9
110°-120°	923.3	20.6
120°-130°	739.7	16.5
130°-140°	581.0	12.9
140°-150°	445.2	9.9
150°-160°	320.1	7.1
160°-170°	195.7	4.4
170°-180°	66.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2142.9	47.7
90°-150°	3908.8	87.0
90°-180°	4491.0	100.0
0°-180°	4490.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	6	10	13	13	
95°	48	178	575	246	157	54
105°	160	246	986	1501	1401	169
115°	283	345	790	1574	1786	279
125°	390	445	717	1213	1421	348
135°	471	522	697	981	1110	363
145°	544	581	686	836	900	341
155°	616	636	682	751	773	283
165°	666	674	685	713	717	188
175°	689	691	686	695	694	65
180°	689	689	689	689	689	



TEST NUMBER: P519697

CATALOG NUMBER: SQ4-075U-0D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.5	5.8	10.3	13.2	13.2
92.5°	20.2	86.5	149.9	57.6	47.2
95°	48.4	177.5	574.9	245.8	156.9
97.5°	78.9	196.8	877.3	676.0	477.0
100°	101.2	208.8	972.4	981.5	800.8
102.5°	122.3	223.0	997.0	1217.7	1051.9
105°	159.9	245.9	985.6	1501.0	1400.6
107.5°	195.7	274.2	929.6	1639.8	1669.6
110°	221.5	293.2	887.3	1674.3	1777.6
112.5°	244.9	314.3	845.1	1652.1	1809.3
115°	283.1	344.7	790.5	1574.1	1786.4
117.5°	319.4	376.2	755.9	1464.8	1704.8
120°	341.7	396.2	740.7	1382.8	1630.9
122.5°	361.7	416.2	730.1	1311.0	1546.4
125°	390.1	444.6	717.2	1213.2	1421.2
127.5°	417.1	469.0	708.7	1131.7	1314.1
130°	431.2	484.3	704.0	1083.2	1249.6
132.5°	447.6	500.7	700.5	1040.6	1190.9
135°	470.8	522.4	696.7	981.2	1110.3
137.5°	492.5	540.4	693.4	933.2	1039.6
140°	508.9	553.4	692.3	901.2	997.3
142.5°	523.0	564.0	689.9	872.8	955.1
145°	544.1	581.4	686.4	836.0	900.5
147.5°	566.7	598.8	684.6	803.4	855.1
150°	580.8	609.5	683.5	785.6	825.7
152.5°	593.7	620.1	682.3	770.2	803.4
155°	616.0	636.1	682.0	751.4	772.9
157.5°	632.1	648.5	682.0	736.0	750.9
160°	643.9	656.8	682.0	727.7	739.2
162.5°	653.2	663.9	683.2	720.6	729.8
165°	665.9	674.5	684.9	712.9	717.2
167.5°	674.7	681.3	686.4	706.4	707.5
170°	680.5	684.8	686.4	704.0	704.0
172.5°	685.2	687.2	686.4	700.4	699.3
175°	689.3	690.8	686.4	695.2	693.7
177.5°	690.5	690.5	685.8	692.8	690.5
180°	689.3	689.3	689.3	689.3	689.3

(END OF REPORT)