

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564653

Luminaire Tested: **SQ4-PW1-050U-075D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564653
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-050U-075D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11542.0 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 105.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564653

CATALOG NUMBER: SQ4-PW1-050U-075D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P564653

CATALOG NUMBER: SQ4-PW1-050U-075D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	56	55	50
2	91	84	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	74	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	54	48	43	46	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	32	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	23
7	60	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	30	52	40	33	28	36	30	26	31	27	23	27	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8200	8200	8200
5°	8253	8188	8152
10°	8187	8121	8077
15°	8100	8011	7981
20°	8004	7881	7865
25°	7892	7748	7725
30°	7725	7608	7558
35°	7506	7400	7356
40°	7271	7159	7130
45°	6989	6897	6866
50°	6699	6643	6598
55°	6386	6386	6286
60°	5996	6112	5896
65°	5488	5761	5351
70°	4838	5303	4711
75°	4132	4746	4020
80°	3204	3994	3245
85°	2071	3066	2735



TEST NUMBER: P564653

CATALOG NUMBER: SQ4-PW1-050U-075D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.1	2.2
10°-20°	708.9	6.1
20°-30°	1051.5	9.1
30°-40°	1230.3	10.7
40°-50°	1224.8	10.6
50°-60°	1057.7	9.2
60°-70°	761.4	6.6
70°-80°	399.3	3.5
80°-90°	101.8	0.9
90°-100°	349.6	3.0
100°-110°	949.7	8.2
110°-120°	976.5	8.5
120°-130°	780.7	6.8
130°-140°	613.5	5.3
140°-150°	470.4	4.1
150°-160°	338.3	2.9
160°-170°	206.9	1.8
170°-180°	69.7	0.6
0°-30°	2011.4	17.4
0°-40°	3241.8	28.1
0°-60°	5524.3	47.9
0°-90°	6786.7	58.8
90°-120°	2275.9	19.7
90°-150°	4140.4	35.9
90°-180°	4755.0	41.2
0°-180°	11542.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2666	2666	2666	2666	2666	
5°	2673	2644	2652	2645	2640	253
15°	2544	2512	2516	2511	2507	717
25°	2326	2287	2283	2270	2276	1069
35°	1999	1972	1971	1952	1959	1250
45°	1607	1593	1586	1581	1579	1240
55°	1191	1189	1191	1175	1172	1063
65°	754	777	792	761	735	747
75°	348	380	399	373	338	373
85°	59	77	87	82	78	78
90°	2	9	16	21	21	6
95°	52	191	609	265	178	55
105°	169	262	1044	1590	1496	179
115°	300	364	836	1663	1894	296
125°	412	469	756	1274	1503	367
135°	496	551	735	1038	1171	384
145°	574	615	726	882	948	360
155°	649	672	721	792	815	299
165°	702	712	724	754	756	198
175°	728	731	726	735	733	69
180°	728	728	728	728	728	

TEST NUMBER: P564653

CATALOG NUMBER: SQ4-PW1-050U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2666.4	2666.4	2666.4	2666.4	2666.4
2.5°	2681.4	2659.3	2666.4	2660.4	2647.6
5°	2673.4	2643.5	2652.3	2645.1	2640.5
7.5°	2646.2	2618.6	2625.0	2617.4	2614.7
10°	2621.7	2594.2	2600.6	2591.1	2586.5
12.5°	2593.5	2564.1	2570.5	2561.1	2558.3
15°	2544.2	2512.0	2516.0	2511.2	2506.6
17.5°	2486.9	2454.3	2454.9	2447.4	2446.5
20°	2445.5	2411.1	2407.9	2398.7	2403.3
22.5°	2400.4	2364.1	2361.0	2348.0	2354.4
25°	2325.7	2286.7	2283.4	2269.5	2276.4
27.5°	2239.3	2200.7	2200.7	2181.2	2188.5
30°	2175.4	2138.6	2142.5	2119.2	2128.4
32.5°	2107.7	2074.6	2076.7	2053.4	2062.6
35°	1999.2	1971.6	1971.0	1952.4	1959.2
37.5°	1888.3	1864.0	1860.1	1849.3	1851.2
40°	1811.2	1790.6	1783.1	1776.0	1776.0
42.5°	1730.4	1711.6	1704.1	1698.9	1697.1
45°	1606.9	1593.1	1585.7	1581.0	1578.7
47.5°	1484.7	1471.8	1465.4	1462.1	1459.8
50°	1400.1	1390.9	1388.4	1381.3	1379.0
52.5°	1315.6	1310.0	1307.6	1298.6	1296.3
55°	1191.1	1188.8	1191.1	1174.6	1172.3
57.5°	1061.4	1065.1	1072.7	1050.4	1044.9
60°	974.9	984.1	993.7	967.7	958.5
62.5°	886.6	901.3	914.8	884.9	872.0
65°	754.1	777.1	791.7	760.6	735.3
67.5°	626.3	654.8	672.3	638.8	610.3
70°	538.0	570.1	589.7	556.0	523.9
72.5°	460.9	496.8	512.6	480.9	448.7
75°	347.7	379.8	399.4	372.7	338.3
77.5°	246.7	277.0	293.2	270.0	241.5
80°	180.9	213.0	225.5	206.2	183.2
82.5°	128.3	154.9	163.5	151.9	136.3
85°	58.7	77.1	86.9	82.1	77.5
87.5°	15.5	29.7	39.0	40.0	41.8
90°	2.3	9.2	16.4	21.1	21.1
92.5°	21.1	95.7	166.3	71.4	60.4
95°	51.5	191.2	608.9	265.0	178.0
97.5°	85.2	211.2	933.4	726.2	510.0
100°	107.7	224.5	1032.7	1046.9	845.4
102.5°	130.2	237.8	1059.0	1294.7	1117.0
105°	168.6	262.5	1044.4	1590.3	1496.4
107.5°	208.4	291.3	984.0	1742.9	1769.0
110°	236.5	312.1	939.1	1772.9	1885.1

TEST NUMBER: P564653

CATALOG NUMBER: SQ4-PW1-050U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	260.9	332.8	894.1	1748.0	1917.0
115°	299.7	363.9	836.0	1663.2	1894.5
117.5°	336.3	397.6	799.0	1543.1	1803.6
120°	360.6	420.2	782.2	1462.5	1721.2
122.5°	381.2	440.8	770.9	1381.7	1631.3
125°	412.2	469.4	756.4	1274.4	1503.4
127.5°	439.8	496.6	748.4	1193.2	1389.6
130°	456.6	511.6	744.7	1142.1	1318.4
132.5°	473.5	528.5	740.9	1098.6	1254.7
135°	496.5	551.4	735.3	1038.1	1170.9
137.5°	521.3	571.2	732.5	984.7	1096.4
140°	536.3	584.4	730.6	950.7	1051.5
142.5°	551.3	595.7	728.8	924.1	1008.4
145°	573.7	615.0	726.0	882.0	948.4
147.5°	599.0	634.3	723.6	848.9	901.1
150°	615.9	645.7	723.6	829.9	871.1
152.5°	629.0	655.1	721.7	812.9	846.8
155°	648.7	671.6	721.3	792.0	814.9
157.5°	667.9	685.7	721.3	777.9	795.3
160°	679.1	695.1	721.3	768.4	782.2
162.5°	690.4	702.7	723.1	760.8	770.9
165°	702.5	711.7	723.6	754.1	756.4
167.5°	715.2	719.8	726.0	746.1	748.0
170°	718.9	723.5	726.0	742.3	742.3
172.5°	722.7	725.4	726.0	738.6	738.6
175°	728.3	730.6	726.0	735.3	733.0
177.5°	730.2	730.2	724.5	732.0	728.3
180°	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)