

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519103

Luminaire Tested: **SQ4-WB-050U-075D-930-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519103
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-050U-075D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10710.5 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 105.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519103
CATALOG NUMBER: SQ4-WB-050U-075D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519103

CATALOG NUMBER: SQ4-WB-050U-075D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	100	96	93	90	93	90	87	84	78	76	74	66	65	64	56	55	54	49
2	92	86	80	76	86	80	75	71	70	66	63	60	57	55	51	49	48	43
3	85	77	70	65	79	72	66	61	63	58	55	54	51	48	46	44	42	38
4	79	69	62	56	73	65	58	53	57	52	48	49	46	43	42	40	38	34
5	73	62	55	49	68	58	52	47	51	46	42	45	41	38	39	36	34	31
6	68	56	49	43	63	53	46	41	47	42	38	41	37	34	36	33	30	28
7	63	51	44	39	59	49	42	37	43	38	34	38	34	31	33	30	28	25
8	59	47	40	35	55	45	38	33	40	34	31	35	31	28	31	28	25	23
9	55	43	36	31	51	41	35	30	37	32	28	33	29	26	29	26	23	21
10	52	40	33	29	48	38	32	28	34	29	26	30	26	23	27	24	21	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12563	12563	12563
5°	12406	12362	12433
10°	11721	11827	12102
15°	10820	11071	11568
20°	9826	10195	10870
25°	8813	9294	10127
30°	7880	8396	9357
35°	6891	7389	8445
40°	5800	6260	7311
45°	4786	5200	6104
50°	3996	4356	5085
55°	3392	3738	4200
60°	2899	3241	3352
65°	2309	2726	2165
70°	2047	2127	1322
75°	1895	1725	809
80°	1746	1587	698
85°	1581	1454	568



TEST NUMBER: P519103

CATALOG NUMBER: SQ4-WB-050U-075D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	374.7	3.5
10°-20°	974.6	9.1
20°-30°	1262.3	11.8
30°-40°	1236.1	11.5
40°-50°	946.2	8.8
50°-60°	630.5	5.9
60°-70°	344.1	3.2
70°-80°	143.4	1.3
80°-90°	43.4	0.4
90°-100°	349.6	3.3
100°-110°	949.7	8.9
110°-120°	976.5	9.1
120°-130°	780.7	7.3
130°-140°	613.5	5.7
140°-150°	470.4	4.4
150°-160°	338.3	3.2
160°-170°	206.9	1.9
170°-180°	69.7	0.7
0°-30°	2611.6	24.4
0°-40°	3847.7	35.9
0°-60°	5424.4	50.6
0°-90°	5955.2	55.6
90°-120°	2275.9	21.2
90°-150°	4140.4	38.7
90°-180°	4755.0	44.4
0°-180°	10710.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4085	4085	4085	4085	4085	
5°	4019	3978	4004	4014	4028	374
15°	3398	3386	3477	3572	3633	949
25°	2597	2604	2739	2858	2984	1194
35°	1835	1844	1968	2100	2250	1141
45°	1100	1122	1196	1286	1404	858
55°	633	659	697	724	783	574
65°	317	344	375	327	298	330
75°	160	160	145	100	68	170
85°	45	45	41	27	16	49
90°	2	9	16	21	21	6
95°	52	191	609	265	178	55
105°	169	262	1044	1590	1496	179
115°	300	364	836	1663	1894	296
125°	412	469	756	1274	1503	367
135°	496	551	735	1038	1171	384
145°	574	615	726	882	948	360
155°	649	672	721	792	815	299
165°	702	712	724	754	756	198
175°	728	731	726	735	733	69
180°	728	728	728	728	728	

TEST NUMBER: P519103

CATALOG NUMBER: SQ4-WB-050U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4084.9	4084.9	4084.9	4084.9	4084.9
2.5°	4094.9	4058.5	4067.7	4067.4	4056.2
5°	4018.6	3978.3	4004.2	4013.5	4027.5
7.5°	3869.4	3838.9	3886.3	3921.3	3949.7
10°	3753.3	3727.0	3787.3	3838.4	3875.2
12.5°	3618.5	3596.4	3671.2	3739.7	3787.7
15°	3398.4	3386.1	3477.3	3571.9	3633.2
17.5°	3162.9	3156.9	3261.5	3371.9	3450.4
20°	3002.3	3000.5	3115.2	3230.2	3321.3
22.5°	2840.2	2844.1	2964.6	3084.2	3188.0
25°	2597.2	2604.2	2738.8	2858.2	2984.3
27.5°	2372.4	2375.6	2514.7	2640.8	2775.4
30°	2219.0	2227.8	2364.2	2494.6	2634.8
32.5°	2065.6	2075.7	2209.3	2344.1	2487.1
35°	1835.4	1844.2	1968.1	2100.5	2249.5
37.5°	1598.1	1610.0	1720.0	1845.2	1991.7
40°	1444.7	1462.2	1559.4	1677.4	1821.1
42.5°	1297.0	1318.7	1408.8	1520.8	1650.4
45°	1100.5	1121.6	1195.5	1286.0	1403.5
47.5°	931.3	955.5	1012.3	1090.3	1190.5
50°	835.3	858.0	910.5	968.3	1062.9
52.5°	750.7	773.4	820.2	864.7	945.3
55°	632.7	659.0	697.2	723.7	783.3
57.5°	535.9	561.2	591.5	603.4	639.5
60°	471.4	499.4	527.0	525.6	544.9
62.5°	412.6	436.4	463.9	444.9	445.9
65°	317.3	343.5	374.6	327.3	297.5
67.5°	256.3	261.9	294.0	228.3	192.9
70°	227.6	227.6	236.6	176.8	147.0
72.5°	200.4	200.4	192.1	143.8	112.6
75°	159.5	159.5	145.2	99.7	68.1
77.5°	123.0	121.6	111.1	74.4	49.5
80°	98.6	98.6	89.6	58.7	39.4
82.5°	77.1	77.1	69.5	45.9	29.4
85°	44.8	44.8	41.2	26.6	16.1
87.5°	16.2	17.6	17.6	12.8	11.4
90°	2.3	9.2	16.4	21.1	21.1
92.5°	21.1	95.7	166.3	71.4	60.4
95°	51.5	191.2	608.9	265.0	178.0
97.5°	85.2	211.2	933.4	726.2	510.0
100°	107.7	224.5	1032.7	1046.9	845.4
102.5°	130.2	237.8	1059.0	1294.7	1117.0
105°	168.6	262.5	1044.4	1590.3	1496.4
107.5°	208.4	291.3	984.0	1742.9	1769.0
110°	236.5	312.1	939.1	1772.9	1885.1

TEST NUMBER: P519103

CATALOG NUMBER: SQ4-WB-050U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	260.9	332.8	894.1	1748.0	1917.0
115°	299.7	363.9	836.0	1663.2	1894.5
117.5°	336.3	397.6	799.0	1543.1	1803.6
120°	360.6	420.2	782.2	1462.5	1721.2
122.5°	381.2	440.8	770.9	1381.7	1631.3
125°	412.2	469.4	756.4	1274.4	1503.4
127.5°	439.8	496.6	748.4	1193.2	1389.6
130°	456.6	511.6	744.7	1142.1	1318.4
132.5°	473.5	528.5	740.9	1098.6	1254.7
135°	496.5	551.4	735.3	1038.1	1170.9
137.5°	521.3	571.2	732.5	984.7	1096.4
140°	536.3	584.4	730.6	950.7	1051.5
142.5°	551.3	595.7	728.8	924.1	1008.4
145°	573.7	615.0	726.0	882.0	948.4
147.5°	599.0	634.3	723.6	848.9	901.1
150°	615.9	645.7	723.6	829.9	871.1
152.5°	629.0	655.1	721.7	812.9	846.8
155°	648.7	671.6	721.3	792.0	814.9
157.5°	667.9	685.7	721.3	777.9	795.3
160°	679.1	695.1	721.3	768.4	782.2
162.5°	690.4	702.7	723.1	760.8	770.9
165°	702.5	711.7	723.6	754.1	756.4
167.5°	715.2	719.8	726.0	746.1	748.0
170°	718.9	723.5	726.0	742.3	742.3
172.5°	722.7	725.4	726.0	738.6	738.6
175°	728.3	730.6	726.0	735.3	733.0
177.5°	730.2	730.2	724.5	732.0	728.3
180°	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)