

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519487

Luminaire Tested: **SQ4-WB-125U-075D-930-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519487
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-075D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17891.5 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 172.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519487
CATALOG NUMBER: SQ4-WB-125U-075D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519487

CATALOG NUMBER: SQ4-WB-125U-075D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	95	91	87	84	85	82	79	77	66	64	62	51	50	49	37	36	36	30
2	87	80	75	70	78	73	68	64	59	55	53	46	44	42	34	32	31	26
3	80	71	65	59	72	65	59	54	52	48	45	41	38	36	31	29	28	23
4	73	63	56	51	66	58	52	47	47	43	39	37	34	32	28	26	25	21
5	68	57	49	44	61	52	45	41	42	38	34	34	31	28	26	24	22	18
6	62	51	44	38	56	47	40	36	39	34	30	31	27	25	23	21	20	17
7	58	46	39	34	52	43	36	32	35	30	27	28	25	22	22	19	18	15
8	54	42	35	30	49	39	33	28	32	27	24	26	23	20	20	18	16	14
9	50	39	32	27	45	36	29	25	30	25	22	24	21	18	19	16	15	13
10	47	36	29	24	43	33	27	23	27	23	20	22	19	17	17	15	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12563	12563	12563
5°	12406	12362	12433
10°	11721	11827	12102
15°	10820	11071	11568
20°	9826	10195	10870
25°	8813	9294	10127
30°	7880	8396	9357
35°	6891	7389	8445
40°	5800	6260	7311
45°	4786	5200	6104
50°	3996	4356	5085
55°	3392	3738	4200
60°	2899	3241	3352
65°	2309	2726	2165
70°	2047	2127	1322
75°	1895	1725	809
80°	1746	1587	698
85°	1581	1454	568



TEST NUMBER: P519487

CATALOG NUMBER: SQ4-WB-125U-075D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	374.7	2.1
10°-20°	974.6	5.4
20°-30°	1262.3	7.1
30°-40°	1236.1	6.9
40°-50°	946.2	5.3
50°-60°	630.5	3.5
60°-70°	344.1	1.9
70°-80°	143.4	0.8
80°-90°	44.9	0.3
90°-100°	864.9	4.8
100°-110°	2329.7	13.0
110°-120°	2444.9	13.7
120°-130°	1984.0	11.1
130°-140°	1556.0	8.7
140°-150°	1194.6	6.7
150°-160°	858.9	4.8
160°-170°	524.8	2.9
170°-180°	177.0	1.0
0°-30°	2611.6	14.6
0°-40°	3847.7	21.5
0°-60°	5424.4	30.3
0°-90°	5956.8	33.3
90°-120°	5639.5	31.5
90°-150°	10374.1	58.0
90°-180°	11935.0	66.7
0°-180°	17891.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4085	4085	4085	4085	4085	
5°	4019	3978	4004	4014	4028	374
15°	3398	3386	3477	3572	3633	949
25°	2597	2604	2739	2858	2984	1194
35°	1835	1844	1968	2100	2250	1141
45°	1100	1122	1196	1286	1404	858
55°	633	659	697	724	783	574
65°	317	344	375	327	298	330
75°	160	160	145	100	68	170
85°	45	45	41	27	16	49
90°	5	14	28	31	31	11
95°	132	470	1418	725	502	138
105°	431	670	2576	3855	3617	453
115°	761	931	2146	4146	4689	749
125°	1039	1193	1926	3256	3832	927
135°	1251	1396	1872	2627	2974	965
145°	1446	1559	1849	2246	2412	907
155°	1642	1701	1832	2015	2080	756
165°	1780	1801	1839	1912	1922	502
175°	1851	1849	1842	1868	1863	176
180°	1849	1849	1849	1849	1849	

TEST NUMBER: P519487

CATALOG NUMBER: SQ4-WB-125U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4084.9	4084.9	4084.9	4084.9	4084.9
2.5°	4094.9	4058.5	4067.7	4067.4	4056.2
5°	4018.6	3978.3	4004.2	4013.5	4027.5
7.5°	3869.4	3838.9	3886.3	3921.3	3949.7
10°	3753.3	3727.0	3787.3	3838.4	3875.2
12.5°	3618.5	3596.4	3671.2	3739.7	3787.7
15°	3398.4	3386.1	3477.3	3571.9	3633.2
17.5°	3162.9	3156.9	3261.5	3371.9	3450.4
20°	3002.3	3000.5	3115.2	3230.2	3321.3
22.5°	2840.2	2844.1	2964.6	3084.2	3188.0
25°	2597.2	2604.2	2738.8	2858.2	2984.3
27.5°	2372.4	2375.6	2514.7	2640.8	2775.4
30°	2219.0	2227.8	2364.2	2494.6	2634.8
32.5°	2065.6	2075.7	2209.3	2344.1	2487.1
35°	1835.4	1844.2	1968.1	2100.5	2249.5
37.5°	1598.1	1610.0	1720.0	1845.2	1991.7
40°	1444.7	1462.2	1559.4	1677.4	1821.1
42.5°	1297.0	1318.7	1408.8	1520.8	1650.4
45°	1100.5	1121.6	1195.5	1286.0	1403.5
47.5°	931.3	955.5	1012.3	1090.3	1190.5
50°	835.3	858.0	910.5	968.3	1062.9
52.5°	750.7	773.4	820.2	864.7	945.3
55°	632.7	659.0	697.2	723.7	783.3
57.5°	535.9	561.2	591.5	603.4	639.5
60°	471.4	499.4	527.0	525.6	544.9
62.5°	412.6	436.4	463.9	444.9	445.9
65°	317.3	343.5	374.6	327.3	297.5
67.5°	256.3	261.9	294.0	228.3	192.9
70°	227.6	227.6	236.6	176.8	147.0
72.5°	200.4	200.4	192.1	143.8	112.6
75°	159.5	159.5	145.2	99.7	68.1
77.5°	123.0	121.6	111.1	74.4	49.5
80°	98.6	98.6	89.6	58.7	39.4
82.5°	77.1	77.1	69.5	45.9	29.4
85°	44.8	44.8	41.2	26.6	16.1
87.5°	16.7	18.6	20.0	14.7	13.3
90°	4.7	13.9	28.3	30.6	30.6
92.5°	57.5	203.0	401.3	193.2	134.2
95°	131.9	470.4	1417.8	725.0	501.6
97.5°	210.5	538.5	2223.7	1857.7	1400.8
100°	270.8	565.6	2479.9	2594.7	2152.5
102.5°	329.2	603.7	2564.7	3146.6	2783.7
105°	431.0	670.5	2576.5	3854.6	3617.4
107.5°	527.1	740.8	2466.7	4218.4	4279.7
110°	591.1	793.8	2366.9	4331.4	4554.7

TEST NUMBER: P519487

CATALOG NUMBER: SQ4-WB-125U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.0	846.9	2270.8	4306.4	4673.4
115°	760.7	931.1	2145.5	4145.5	4689.0
117.5°	853.5	1013.3	2048.5	3888.8	4494.0
120°	913.8	1068.1	1999.5	3704.5	4326.3
122.5°	966.5	1119.0	1963.7	3516.1	4136.0
125°	1038.6	1192.9	1926.5	3256.0	3831.7
127.5°	1107.8	1259.8	1902.9	3026.7	3540.6
130°	1149.3	1301.3	1893.5	2895.2	3346.6
132.5°	1190.7	1340.9	1884.1	2779.5	3194.0
135°	1250.6	1395.6	1872.3	2626.8	2974.5
137.5°	1307.5	1446.6	1866.2	2497.2	2782.8
140°	1347.1	1480.7	1860.5	2417.5	2675.4
142.5°	1388.6	1512.9	1856.7	2343.1	2560.4
145°	1446.0	1558.9	1848.7	2245.8	2411.6
147.5°	1508.2	1606.3	1840.7	2164.0	2294.3
150°	1549.6	1634.8	1837.0	2112.6	2220.8
152.5°	1587.3	1661.5	1835.1	2070.7	2158.7
155°	1641.5	1701.4	1832.3	2015.1	2079.5
157.5°	1689.1	1735.6	1832.7	1976.0	2019.2
160°	1719.2	1758.4	1834.6	1953.1	1985.3
162.5°	1745.6	1777.4	1836.5	1934.0	1957.1
165°	1780.4	1801.2	1839.3	1912.5	1921.7
167.5°	1808.7	1820.7	1841.7	1895.9	1899.6
170°	1827.5	1832.2	1841.7	1886.4	1886.4
172.5°	1838.9	1839.8	1843.6	1877.0	1877.0
175°	1851.1	1848.8	1841.7	1867.5	1862.9
177.5°	1856.3	1852.6	1843.1	1858.1	1854.4
180°	1848.7	1848.7	1848.7	1848.7	1848.7

(END OF REPORT)