

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562967

Luminaire Tested: **SQ4-PC3-100U-125D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562967
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-125D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13403.7 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 107.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562967
CATALOG NUMBER: SQ4-PC3-100U-125D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562967

CATALOG NUMBER: SQ4-PC3-100U-125D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51	47				
2	90	83	76	71	83	77	72	67	66	62	59	56	54	51	47	45	43	39				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33				
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32	28				
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24				
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21				
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	26	22	19	17				
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15				
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16626	16626	16626
5°	16751	16643	16582
10°	16711	16633	16585
15°	16623	16623	16607
20°	16514	16563	16563
25°	16358	16477	16426
30°	16159	16354	16283
35°	15918	16163	16049
40°	15655	15876	15715
45°	15370	15479	15240
50°	14969	14969	14729
55°	14493	14305	14091
60°	13794	13517	13300
65°	12749	12495	12385
70°	11163	11252	11207
75°	8981	9934	9993
80°	6383	8423	8512
85°	3889	7064	7064



TEST NUMBER: P562967

CATALOG NUMBER: SQ4-PC3-100U-125D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.8	1.9
10°-20°	734.1	5.5
20°-30°	1111.7	8.3
30°-40°	1332.8	9.9
40°-50°	1359.0	10.1
50°-60°	1186.3	8.9
60°-70°	849.3	6.3
70°-80°	437.5	3.3
80°-90°	112.5	0.8
90°-100°	434.2	3.2
100°-110°	1198.7	8.9
110°-120°	1236.3	9.2
120°-130°	993.5	7.4
130°-140°	780.8	5.8
140°-150°	598.8	4.5
150°-160°	430.4	3.2
160°-170°	263.2	2.0
170°-180°	88.7	0.7
0°-30°	2101.7	15.7
0°-40°	3434.5	25.6
0°-60°	5979.9	44.6
0°-90°	7379.2	55.1
90°-120°	2869.2	21.4
90°-150°	5242.2	39.1
90°-180°	6024.0	44.9
0°-180°	13403.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2703	2703	2703	2703	2703	
5°	2713	2686	2696	2688	2686	258
15°	2610	2588	2610	2610	2608	736
25°	2410	2393	2428	2420	2420	1109
35°	2120	2115	2152	2137	2137	1326
45°	1767	1762	1780	1757	1752	1360
55°	1352	1334	1334	1314	1314	1205
65°	876	856	858	851	851	866
75°	378	395	418	420	420	408
85°	55	84	100	103	100	75
90°	3	6	12	13	15	7
95°	64	235	788	324	211	68
105°	214	330	1319	2013	1896	227
115°	383	462	1062	2103	2391	376
125°	525	598	963	1629	1912	467
135°	632	700	936	1320	1488	489
145°	733	784	924	1124	1209	459
155°	826	854	917	1008	1040	381
165°	895	906	921	957	964	252
175°	927	929	923	936	933	88
180°	927	927	927	927	927	

TEST NUMBER: P562967

CATALOG NUMBER: SQ4-PC3-100U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2703.1	2703.1	2703.1	2703.1	2703.1
2.5°	2719.1	2695.6	2703.1	2696.9	2687.1
5°	2713.1	2686.2	2695.6	2688.0	2685.6
7.5°	2693.6	2666.7	2679.1	2674.0	2671.6
10°	2675.6	2648.6	2663.1	2658.0	2655.5
12.5°	2651.5	2626.6	2643.0	2638.0	2637.5
15°	2610.5	2588.5	2610.5	2610.4	2608.0
17.5°	2558.9	2538.9	2562.4	2563.9	2562.4
20°	2522.9	2500.9	2530.4	2528.0	2530.4
22.5°	2478.8	2460.7	2492.4	2485.9	2488.4
25°	2410.3	2393.1	2427.8	2420.3	2420.3
27.5°	2329.2	2316.9	2354.7	2346.7	2346.7
30°	2275.1	2262.9	2302.6	2292.6	2292.6
32.5°	2215.0	2206.7	2244.6	2232.6	2232.6
35°	2119.9	2115.0	2152.5	2137.4	2137.4
37.5°	2021.8	2017.4	2051.4	2033.2	2027.3
40°	1949.7	1947.3	1977.3	1957.2	1957.2
42.5°	1877.7	1875.2	1901.2	1877.2	1877.2
45°	1767.0	1762.1	1779.5	1756.9	1752.0
47.5°	1646.4	1641.5	1652.4	1627.8	1625.4
50°	1564.3	1559.4	1564.3	1541.7	1539.3
52.5°	1480.2	1471.4	1472.2	1449.6	1449.2
55°	1351.5	1334.4	1334.0	1314.0	1314.0
57.5°	1215.4	1192.9	1194.9	1177.8	1175.3
60°	1121.3	1096.8	1098.8	1083.7	1081.2
62.5°	1029.2	1000.8	1006.7	989.6	989.1
65°	876.0	856.4	858.5	851.0	851.0
67.5°	728.8	710.7	723.8	717.8	717.3
70°	620.7	608.5	625.7	625.7	623.2
72.5°	520.6	520.1	541.6	541.7	543.1
75°	377.9	395.1	418.0	420.5	420.5
77.5°	252.3	282.6	307.9	308.8	308.4
80°	180.2	214.5	237.8	242.7	240.3
82.5°	122.1	158.4	177.7	182.7	180.2
85°	55.1	84.4	100.1	102.6	100.1
87.5°	16.6	34.8	42.4	42.6	39.0
90°	3.0	5.9	11.9	13.4	14.8
92.5°	26.7	110.8	198.2	72.3	56.4
95°	63.8	235.0	787.8	323.8	210.7
97.5°	105.6	263.2	1166.9	898.4	650.7
100°	136.5	280.1	1307.0	1316.2	1069.6
102.5°	166.2	299.3	1334.3	1626.3	1392.4
105°	213.6	329.7	1318.9	2013.4	1895.9
107.5°	264.1	367.3	1245.3	2200.2	2243.1
110°	299.7	392.5	1188.3	2240.3	2379.6



TEST NUMBER: P562967

CATALOG NUMBER: SQ4-PC3-100U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.7	421.1	1134.9	2208.6	2414.0
115°	382.7	462.5	1062.2	2102.8	2391.4
117.5°	427.3	506.7	1014.4	1953.8	2282.3
120°	456.9	535.3	995.4	1853.0	2183.7
122.5°	485.4	560.3	980.0	1758.9	2072.2
125°	525.2	597.7	962.8	1629.4	1912.3
127.5°	559.0	631.5	952.7	1519.9	1763.9
130°	581.5	654.1	948.0	1453.0	1674.9
132.5°	602.9	672.0	943.2	1396.7	1597.8
135°	632.0	700.2	936.1	1319.7	1488.0
137.5°	664.6	726.7	932.5	1255.1	1398.7
140°	682.4	743.3	930.2	1211.9	1338.1
142.5°	702.6	758.9	927.8	1173.6	1284.7
145°	732.9	783.6	924.2	1123.5	1209.1
147.5°	761.9	806.3	921.0	1081.2	1147.7
150°	783.3	819.6	919.8	1056.0	1109.7
152.5°	799.9	833.9	918.6	1034.4	1078.8
155°	826.3	853.9	916.8	1008.0	1040.0
157.5°	850.7	871.8	917.1	988.8	1010.6
160°	864.9	883.8	918.3	978.0	994.0
162.5°	876.8	893.3	919.5	968.4	980.9
165°	894.6	906.2	921.3	957.0	964.3
167.5°	908.2	915.2	922.8	950.1	952.4
170°	915.3	921.1	922.8	946.5	946.5
172.5°	921.3	924.7	922.8	941.7	940.6
175°	927.2	928.7	922.8	936.0	933.1
177.5°	929.6	928.4	922.5	930.7	928.4
180°	927.2	927.2	927.2	927.2	927.2

(END OF REPORT)