

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563039

Luminaire Tested: **SQ4-PC3-125U-100D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563039  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-125U-100D-835-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 13282.7 lumens  
Efficiency: N/A  
Efficacy: 129.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 102.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563039  
CATALOG NUMBER: SQ4-PC3-125U-100D-835-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563039

CATALOG NUMBER: SQ4-PC3-125U-100D-835-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				44
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42				37	
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36				31	
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30				26	
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26				22	
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23				19	
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20				17	
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18				15	
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16				13	
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14				12	
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13				11	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13029	13029	13029
5°	13127	13042	12994
10°	13095	13034	12997
15°	13026	13026	13014
20°	12941	12979	12979
25°	12818	12912	12872
30°	12662	12815	12759
35°	12474	12665	12576
40°	12267	12441	12315
45°	12045	12130	11942
50°	11730	11730	11542
55°	11357	11210	11042
60°	10809	10592	10423
65°	9991	9791	9705
70°	8747	8817	8783
75°	7039	7783	7831
80°	5001	6599	6670
85°	3042	5540	5540



TEST NUMBER: P563039

CATALOG NUMBER: SQ4-PC3-125U-100D-835-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	200.5	1.5
10°-20°	575.3	4.3
20°-30°	871.2	6.6
30°-40°	1044.4	7.9
40°-50°	1065.0	8.0
50°-60°	929.6	7.0
60°-70°	665.5	5.0
70°-80°	342.8	2.6
80°-90°	89.4	0.7
90°-100°	543.4	4.1
100°-110°	1463.8	11.0
110°-120°	1536.2	11.6
120°-130°	1246.6	9.4
130°-140°	977.7	7.4
140°-150°	750.6	5.7
150°-160°	539.7	4.1
160°-170°	329.7	2.5
170°-180°	111.2	0.8
0°-30°	1646.9	12.4
0°-40°	2691.3	20.3
0°-60°	4685.9	35.3
0°-90°	5783.7	43.5
90°-120°	3543.5	26.7
90°-150°	6518.4	49.1
90°-180°	7499.0	56.5
0°-180°	13282.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2118	2118	2118	2118	2118	
5°	2126	2105	2112	2106	2104	202
15°	2046	2028	2046	2046	2044	577
25°	1889	1875	1902	1897	1897	869
35°	1661	1657	1687	1675	1675	1039
45°	1385	1381	1394	1377	1373	1066
55°	1059	1046	1045	1030	1030	944
65°	686	671	673	667	667	679
75°	296	310	328	330	330	320
85°	43	66	78	80	78	59
90°	3	9	18	19	19	8
95°	83	296	891	456	315	87
105°	271	421	1619	2422	2273	285
115°	478	585	1348	2605	2946	470
125°	653	750	1210	2046	2408	583
135°	786	877	1176	1650	1869	607
145°	909	980	1162	1411	1515	570
155°	1031	1069	1151	1266	1307	475
165°	1119	1132	1156	1202	1208	315
175°	1163	1162	1157	1173	1170	110
180°	1162	1162	1162	1162	1162	

TEST NUMBER: P563039

CATALOG NUMBER: SQ4-PC3-125U-100D-835-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2118.2	2118.2	2118.2	2118.2	2118.2
2.5°	2130.7	2112.3	2118.2	2113.3	2105.6
5°	2126.0	2104.9	2112.3	2106.4	2104.5
7.5°	2110.7	2089.6	2099.4	2095.4	2093.5
10°	2096.6	2075.5	2086.8	2082.8	2080.9
12.5°	2077.8	2058.2	2071.1	2067.2	2066.8
15°	2045.6	2028.4	2045.6	2045.6	2043.7
17.5°	2005.2	1989.5	2008.0	2009.1	2008.0
20°	1977.0	1959.7	1982.9	1980.9	1982.9
22.5°	1942.5	1928.3	1953.1	1948.0	1949.9
25°	1888.7	1875.3	1902.5	1896.6	1896.6
27.5°	1825.2	1815.6	1845.2	1838.9	1838.9
30°	1782.8	1773.2	1804.4	1796.5	1796.5
32.5°	1735.7	1729.2	1758.9	1749.5	1749.5
35°	1661.2	1657.4	1686.7	1674.9	1674.9
37.5°	1584.3	1580.9	1607.5	1593.2	1588.6
40°	1527.8	1525.9	1549.4	1533.7	1533.7
42.5°	1471.4	1469.4	1489.8	1471.0	1471.0
45°	1384.7	1380.8	1394.5	1376.7	1372.9
47.5°	1290.1	1286.3	1294.8	1275.6	1273.7
50°	1225.8	1222.0	1225.8	1208.1	1206.2
52.5°	1159.9	1153.0	1153.6	1136.0	1135.6
55°	1059.1	1045.7	1045.4	1029.7	1029.7
57.5°	952.4	934.8	936.3	922.9	921.0
60°	878.7	859.5	861.0	849.2	847.3
62.5°	806.5	784.2	788.8	775.5	775.1
65°	686.5	671.1	672.7	666.8	666.8
67.5°	571.1	556.9	567.2	562.5	562.1
70°	486.4	476.8	490.3	490.3	488.4
72.5°	407.9	407.6	424.4	424.4	425.6
75°	296.2	309.6	327.5	329.5	329.5
77.5°	197.7	221.5	241.2	242.0	241.6
80°	141.2	168.1	186.3	190.2	188.3
82.5°	95.7	124.1	139.3	143.1	141.2
85°	43.1	66.2	78.5	80.4	78.5
87.5°	13.1	28.1	34.9	35.2	32.1
90°	3.0	8.7	17.8	19.2	19.2
92.5°	36.1	127.6	252.2	121.4	84.3
95°	82.9	295.6	890.8	455.5	315.2
97.5°	132.3	338.3	1397.2	1167.2	880.2
100°	170.2	355.4	1558.2	1630.3	1352.5
102.5°	206.9	379.3	1611.5	1977.1	1749.1
105°	270.8	421.3	1618.9	2422.0	2272.9
107.5°	331.2	465.4	1549.9	2650.6	2689.1
110°	371.4	498.8	1487.2	2721.5	2861.9



TEST NUMBER: P563039

CATALOG NUMBER: SQ4-PC3-125U-100D-835-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	414.0	532.1	1426.8	2705.8	2936.5
115°	478.0	585.0	1348.1	2604.8	2946.2
117.5°	536.3	636.7	1287.1	2443.5	2823.7
120°	574.2	671.1	1256.3	2327.7	2718.4
122.5°	607.3	703.1	1233.8	2209.3	2598.8
125°	652.6	749.5	1210.5	2045.9	2407.6
127.5°	696.1	791.6	1195.7	1901.8	2224.7
130°	722.1	817.6	1189.7	1819.2	2102.8
132.5°	748.2	842.5	1183.8	1746.4	2006.9
135°	785.8	876.9	1176.4	1650.5	1869.0
137.5°	821.6	909.0	1172.6	1569.1	1748.5
140°	846.4	930.4	1169.0	1519.0	1681.0
142.5°	872.5	950.6	1166.7	1472.2	1608.8
145°	908.6	979.5	1161.6	1411.1	1515.3
147.5°	947.7	1009.3	1156.6	1359.7	1441.6
150°	973.7	1027.2	1154.2	1327.4	1395.4
152.5°	997.4	1044.0	1153.0	1301.1	1356.4
155°	1031.4	1069.0	1151.3	1266.1	1306.6
157.5°	1061.3	1090.5	1151.6	1241.6	1268.8
160°	1080.2	1104.8	1152.7	1227.2	1247.5
162.5°	1096.8	1116.8	1153.9	1215.2	1229.7
165°	1118.7	1131.7	1155.7	1201.7	1207.5
167.5°	1136.5	1144.0	1157.2	1191.3	1193.6
170°	1148.3	1151.2	1157.2	1185.3	1185.3
172.5°	1155.4	1156.0	1158.4	1179.4	1179.4
175°	1163.1	1161.7	1157.2	1173.4	1170.5
177.5°	1166.4	1164.0	1158.1	1167.5	1165.2
180°	1161.6	1161.6	1161.6	1161.6	1161.6

(END OF REPORT)