

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563591

Luminaire Tested: **SQ4-PP3-100U-075D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563591
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-075D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10336.1 lumens
Efficiency: N/A
Efficacy: 132.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 78
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563591
CATALOG NUMBER: SQ4-PP3-100U-075D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563591

CATALOG NUMBER: SQ4-PP3-100U-075D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	45	43	40	38	34	32	30	26
4	73	63	55	49	67	57	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	32	52	42	35	30	35	29	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10357	10357	10357
5°	10433	10369	10333
10°	10415	10342	10295
15°	10346	10290	10234
20°	10278	10220	10142
25°	10156	10086	9985
30°	9967	9916	9789
35°	9707	9640	9519
40°	9397	9337	9230
45°	9140	9076	8986
50°	8812	8756	8670
55°	8356	8245	8182
60°	7606	7388	7353
65°	6701	6421	6401
70°	5785	5546	5546
75°	4981	4910	4841
80°	4392	4442	4339
85°	3437	3747	3747



TEST NUMBER: P563591

CATALOG NUMBER: SQ4-PP3-100U-075D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	1.5
10°-20°	454.6	4.4
20°-30°	681.0	6.6
30°-40°	798.8	7.7
40°-50°	801.2	7.8
50°-60°	683.5	6.6
60°-70°	445.8	4.3
70°-80°	223.6	2.2
80°-90°	63.8	0.6
90°-100°	434.2	4.2
100°-110°	1198.7	11.6
110°-120°	1236.3	12.0
120°-130°	993.5	9.6
130°-140°	780.8	7.6
140°-150°	598.8	5.8
150°-160°	430.4	4.2
160°-170°	263.2	2.5
170°-180°	88.7	0.9
0°-30°	1294.8	12.5
0°-40°	2093.6	20.3
0°-60°	3578.4	34.6
0°-90°	4311.6	41.7
90°-120°	2869.2	27.8
90°-150°	5242.2	50.7
90°-180°	6024.0	58.3
0°-180°	10336.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1684	1684	1684	1684	1684	
5°	1690	1674	1679	1674	1674	160
15°	1625	1609	1616	1610	1607	458
25°	1496	1479	1486	1473	1471	688
35°	1293	1280	1284	1269	1268	808
45°	1051	1044	1043	1033	1033	809
55°	779	776	769	764	763	692
65°	460	452	441	438	440	459
75°	210	210	207	205	204	227
85°	49	53	53	53	53	57
90°	3	6	12	13	15	6
95°	64	235	788	324	211	68
105°	214	330	1319	2013	1896	227
115°	383	462	1062	2103	2391	376
125°	525	598	963	1629	1912	467
135°	632	700	936	1320	1488	489
145°	733	784	924	1124	1209	459
155°	826	854	917	1008	1040	381
165°	895	906	921	957	964	252
175°	927	929	923	936	933	88
180°	927	927	927	927	927	

TEST NUMBER: P563591

CATALOG NUMBER: SQ4-PP3-100U-075D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1683.8	1683.8	1683.8	1683.8	1683.8
2.5°	1694.4	1680.6	1683.8	1681.3	1674.4
5°	1689.7	1673.9	1679.4	1673.5	1673.5
7.5°	1678.2	1660.9	1666.4	1660.5	1660.2
10°	1667.6	1650.3	1655.8	1649.8	1648.4
12.5°	1652.2	1634.9	1641.6	1634.5	1634.2
15°	1624.8	1608.9	1615.9	1610.0	1607.1
17.5°	1593.8	1576.5	1584.9	1576.7	1575.5
20°	1570.2	1552.9	1561.3	1549.5	1549.5
22.5°	1541.9	1524.5	1534.2	1518.8	1518.8
25°	1496.4	1479.1	1486.1	1472.8	1471.3
27.5°	1442.4	1425.4	1432.7	1417.6	1417.3
30°	1403.4	1387.6	1396.1	1379.8	1378.3
32.5°	1360.9	1346.2	1352.4	1336.1	1334.7
35°	1292.8	1279.8	1283.9	1269.1	1267.7
37.5°	1221.0	1207.8	1212.5	1199.8	1199.2
40°	1170.3	1161.6	1162.9	1152.5	1149.6
42.5°	1123.0	1113.2	1114.5	1104.1	1103.6
45°	1050.7	1043.5	1043.4	1033.0	1033.0
47.5°	974.0	968.5	966.9	958.3	958.1
50°	920.9	916.5	915.0	907.5	906.1
52.5°	865.4	863.4	858.3	852.1	851.8
55°	779.2	776.3	768.9	764.4	763.0
57.5°	685.6	679.9	671.5	665.0	666.2
60°	618.3	612.6	600.6	597.7	597.7
62.5°	553.4	546.5	534.5	530.4	532.7
65°	460.4	451.8	441.2	438.3	439.8
67.5°	376.0	368.2	356.8	356.8	355.7
70°	321.7	317.4	308.4	308.4	308.4
72.5°	273.3	271.3	264.7	264.7	263.6
75°	209.6	209.6	206.6	205.1	203.7
77.5°	157.0	157.6	156.1	154.6	152.0
80°	124.0	126.8	125.4	123.9	122.5
82.5°	93.3	96.2	95.9	93.3	93.0
85°	48.7	53.0	53.1	53.1	53.1
87.5°	13.6	18.8	21.3	21.6	23.0
90°	3.0	5.9	11.9	13.4	14.8
92.5°	26.7	110.8	198.2	72.3	56.4
95°	63.8	235.0	787.8	323.8	210.7
97.5°	105.6	263.2	1166.9	898.4	650.7
100°	136.5	280.1	1307.0	1316.2	1069.6
102.5°	166.2	299.3	1334.3	1626.3	1392.4
105°	213.6	329.7	1318.9	2013.4	1895.9
107.5°	264.1	367.3	1245.3	2200.2	2243.1
110°	299.7	392.5	1188.3	2240.3	2379.6



TEST NUMBER: P563591

CATALOG NUMBER: SQ4-PP3-100U-075D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.7	421.1	1134.9	2208.6	2414.0
115°	382.7	462.5	1062.2	2102.8	2391.4
117.5°	427.3	506.7	1014.4	1953.8	2282.3
120°	456.9	535.3	995.4	1853.0	2183.7
122.5°	485.4	560.3	980.0	1758.9	2072.2
125°	525.2	597.7	962.8	1629.4	1912.3
127.5°	559.0	631.5	952.7	1519.9	1763.9
130°	581.5	654.1	948.0	1453.0	1674.9
132.5°	602.9	672.0	943.2	1396.7	1597.8
135°	632.0	700.2	936.1	1319.7	1488.0
137.5°	664.6	726.7	932.5	1255.1	1398.7
140°	682.4	743.3	930.2	1211.9	1338.1
142.5°	702.6	758.9	927.8	1173.6	1284.7
145°	732.9	783.6	924.2	1123.5	1209.1
147.5°	761.9	806.3	921.0	1081.2	1147.7
150°	783.3	819.6	919.8	1056.0	1109.7
152.5°	799.9	833.9	918.6	1034.4	1078.8
155°	826.3	853.9	916.8	1008.0	1040.0
157.5°	850.7	871.8	917.1	988.8	1010.6
160°	864.9	883.8	918.3	978.0	994.0
162.5°	876.8	893.3	919.5	968.4	980.9
165°	894.6	906.2	921.3	957.0	964.3
167.5°	908.2	915.2	922.8	950.1	952.4
170°	915.3	921.1	922.8	946.5	946.5
172.5°	921.3	924.7	922.8	941.7	940.6
175°	927.2	928.7	922.8	936.0	933.1
177.5°	929.6	928.4	922.5	930.7	928.4
180°	927.2	927.2	927.2	927.2	927.2

(END OF REPORT)