

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563639

Luminaire Tested: **SQ4-PP3-100U-125D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563639
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-125D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13333.9 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 107.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563639
CATALOG NUMBER: SQ4-PP3-100U-125D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563639

CATALOG NUMBER: SQ4-PP3-100U-125D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	29	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	23	20	24	21	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17561	17561	17561
5°	17690	17582	17520
10°	17660	17535	17457
15°	17543	17448	17352
20°	17427	17329	17198
25°	17220	17101	16931
30°	16901	16813	16599
35°	16459	16347	16140
40°	15933	15832	15652
45°	15497	15389	15236
50°	14941	14845	14702
55°	14168	13980	13873
60°	12898	12528	12466
65°	11362	10889	10853
70°	9810	9405	9405
75°	8444	8325	8206
80°	7446	7534	7357
85°	5829	6359	6359



TEST NUMBER: P563639

CATALOG NUMBER: SQ4-PP3-100U-125D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.0	2.0
10°-20°	770.9	5.8
20°-30°	1154.7	8.7
30°-40°	1354.4	10.2
40°-50°	1358.6	10.2
50°-60°	1159.0	8.7
60°-70°	755.9	5.7
70°-80°	379.2	2.8
80°-90°	106.9	0.8
90°-100°	434.2	3.3
100°-110°	1198.7	9.0
110°-120°	1236.3	9.3
120°-130°	993.5	7.5
130°-140°	780.8	5.9
140°-150°	598.8	4.5
150°-160°	430.4	3.2
160°-170°	263.2	2.0
170°-180°	88.7	0.7
0°-30°	2195.5	16.5
0°-40°	3549.9	26.6
0°-60°	6067.5	45.5
0°-90°	7309.4	54.8
90°-120°	2869.2	21.5
90°-150°	5242.2	39.3
90°-180°	6024.0	45.2
0°-180°	13333.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2855	2855	2855	2855	2855	
5°	2865	2838	2848	2838	2838	272
15°	2755	2728	2740	2730	2725	777
25°	2537	2508	2520	2497	2495	1167
35°	2192	2170	2177	2152	2150	1369
45°	1782	1769	1769	1752	1752	1372
55°	1321	1316	1304	1296	1294	1174
65°	781	766	748	743	746	779
75°	355	355	350	348	345	385
85°	83	90	90	90	90	97
90°	3	6	12	13	15	8
95°	64	235	788	324	211	68
105°	214	330	1319	2013	1896	227
115°	383	462	1062	2103	2391	376
125°	525	598	963	1629	1912	467
135°	632	700	936	1320	1488	489
145°	733	784	924	1124	1209	459
155°	826	854	917	1008	1040	381
165°	895	906	921	957	964	252
175°	927	929	923	936	933	88
180°	927	927	927	927	927	

TEST NUMBER: P563639

CATALOG NUMBER: SQ4-PP3-100U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2855.1	2855.1	2855.1	2855.1	2855.1
2.5°	2873.1	2849.6	2855.1	2850.8	2839.1
5°	2865.1	2838.2	2847.6	2837.6	2837.6
7.5°	2845.6	2816.2	2825.6	2815.5	2815.1
10°	2827.6	2798.2	2807.6	2797.5	2795.0
12.5°	2801.5	2772.2	2783.5	2771.5	2771.0
15°	2755.0	2728.1	2740.0	2729.9	2725.0
17.5°	2702.5	2673.1	2687.4	2673.4	2671.4
20°	2662.4	2633.1	2647.4	2627.4	2627.4
22.5°	2614.4	2585.0	2601.4	2575.3	2575.3
25°	2537.3	2507.9	2519.8	2497.2	2494.8
27.5°	2445.7	2416.9	2429.2	2403.7	2403.2
30°	2379.7	2352.7	2367.2	2339.6	2337.1
32.5°	2307.6	2282.6	2293.1	2265.5	2263.1
35°	2192.0	2170.0	2177.0	2151.9	2149.5
37.5°	2070.4	2047.9	2055.9	2034.3	2033.3
40°	1984.3	1969.6	1971.8	1954.2	1949.3
42.5°	1904.2	1887.6	1889.7	1872.2	1871.2
45°	1781.6	1769.4	1769.1	1751.6	1751.6
47.5°	1651.5	1642.2	1639.5	1625.0	1624.5
50°	1561.4	1554.1	1551.4	1538.8	1536.4
52.5°	1467.3	1463.9	1455.3	1444.8	1444.3
55°	1321.2	1316.3	1303.7	1296.1	1293.7
57.5°	1162.6	1152.8	1138.5	1127.6	1129.5
60°	1048.5	1038.7	1018.4	1013.4	1013.4
62.5°	938.4	926.6	906.3	899.4	903.3
65°	780.7	766.0	748.2	743.2	745.7
67.5°	637.6	624.4	605.1	605.0	603.0
70°	545.5	538.2	523.0	523.0	523.0
72.5°	463.4	460.0	448.9	448.9	446.9
75°	355.3	355.3	350.3	347.8	345.3
77.5°	266.2	267.2	264.7	262.1	257.7
80°	210.2	215.1	212.7	210.1	207.7
82.5°	158.1	163.0	162.6	158.1	157.6
85°	82.6	89.9	90.1	90.1	90.1
87.5°	22.6	31.0	34.4	34.8	37.0
90°	3.0	5.9	11.9	13.4	14.8
92.5°	26.7	110.8	198.2	72.3	56.4
95°	63.8	235.0	787.8	323.8	210.7
97.5°	105.6	263.2	1166.9	898.4	650.7
100°	136.5	280.1	1307.0	1316.2	1069.6
102.5°	166.2	299.3	1334.3	1626.3	1392.4
105°	213.6	329.7	1318.9	2013.4	1895.9
107.5°	264.1	367.3	1245.3	2200.2	2243.1
110°	299.7	392.5	1188.3	2240.3	2379.6

TEST NUMBER: P563639

CATALOG NUMBER: SQ4-PP3-100U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.7	421.1	1134.9	2208.6	2414.0
115°	382.7	462.5	1062.2	2102.8	2391.4
117.5°	427.3	506.7	1014.4	1953.8	2282.3
120°	456.9	535.3	995.4	1853.0	2183.7
122.5°	485.4	560.3	980.0	1758.9	2072.2
125°	525.2	597.7	962.8	1629.4	1912.3
127.5°	559.0	631.5	952.7	1519.9	1763.9
130°	581.5	654.1	948.0	1453.0	1674.9
132.5°	602.9	672.0	943.2	1396.7	1597.8
135°	632.0	700.2	936.1	1319.7	1488.0
137.5°	664.6	726.7	932.5	1255.1	1398.7
140°	682.4	743.3	930.2	1211.9	1338.1
142.5°	702.6	758.9	927.8	1173.6	1284.7
145°	732.9	783.6	924.2	1123.5	1209.1
147.5°	761.9	806.3	921.0	1081.2	1147.7
150°	783.3	819.6	919.8	1056.0	1109.7
152.5°	799.9	833.9	918.6	1034.4	1078.8
155°	826.3	853.9	916.8	1008.0	1040.0
157.5°	850.7	871.8	917.1	988.8	1010.6
160°	864.9	883.8	918.3	978.0	994.0
162.5°	876.8	893.3	919.5	968.4	980.9
165°	894.6	906.2	921.3	957.0	964.3
167.5°	908.2	915.2	922.8	950.1	952.4
170°	915.3	921.1	922.8	946.5	946.5
172.5°	921.3	924.7	922.8	941.7	940.6
175°	927.2	928.7	922.8	936.0	933.1
177.5°	929.6	928.4	922.5	930.7	928.4
180°	927.2	927.2	927.2	927.2	927.2

(END OF REPORT)