

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938514

Luminaire Tested: SQ4-FB-150U-125D-835-1D-UNV-STD-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938514
REPORT IS A COMBINATION OF REPORTS P933632 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-125D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10099.1 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 83.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938514
CATALOG NUMBER: SQ4-FB-150U-125D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P938514

CATALOG NUMBER: SQ4-FB-150U-125D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47	40
1	95	91	87	83	86	83	79	76	68	65	63	54	52	51	41	40	39	39	39	39	33
2	86	79	72	67	78	72	66	62	59	55	51	47	44	42	36	34	32	32	32	32	27
3	78	69	61	55	71	63	56	51	51	47	43	41	37	35	31	29	27	27	27	27	22
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	27	25	23	23	23	23	19
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	22	19	19	19	19	16
6	60	48	39	34	54	44	36	31	36	30	26	29	25	21	22	19	17	17	17	17	14
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15	15	15	15	12
8	51	39	31	25	46	35	28	24	29	24	20	23	19	16	18	15	13	13	13	13	10
9	47	35	27	22	43	32	25	21	27	21	18	21	17	15	17	14	11	11	11	11	9
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10	10	10	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4883	4883	4883
5°	4765	5640	6564
10°	4317	8214	10882
15°	3665	10725	13139
20°	2981	12419	13391
25°	2484	12987	13119
30°	2091	13058	13094
35°	1846	12831	13432
40°	1606	12539	13782
45°	1452	12322	13837
50°	1329	12124	13608
55°	1268	11839	13004
60°	1295	11304	12052
65°	1340	10497	10743
70°	1417	9136	9077
75°	1554	7430	7083
80°	1661	5135	4773
85°	1399	2709	2443

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13837 cd/sqm



TEST NUMBER: P938514

CATALOG NUMBER: SQ4-FB-150U-125D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.1	0.7
10°-20°	301.7	3.0
20°-30°	527.7	5.2
30°-40°	679.3	6.7
40°-50°	758.8	7.5
50°-60°	726.7	7.2
60°-70°	575.9	5.7
70°-80°	338.7	3.4
80°-90°	97.6	1.0
90°-100°	453.0	4.5
100°-110°	1191.0	11.8
110°-120°	1234.9	12.2
120°-130°	990.5	9.8
130°-140°	777.2	7.7
140°-150°	596.6	5.9
150°-160°	429.6	4.3
160°-170°	262.9	2.6
170°-180°	88.8	0.9
0°-30°	897.5	8.9
0°-40°	1576.8	15.6
0°-60°	3062.3	30.3
0°-90°	4074.6	40.3
90°-120°	2878.9	28.5
90°-150°	5243.2	51.9
90°-180°	6024.0	59.6
0°-180°	10099.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	526	526	526	526	526	
5°	513	550	619	700	726	47
15°	384	709	1195	1448	1494	107
25°	245	804	1423	1486	1487	113
35°	166	768	1340	1416	1472	104
45°	113	612	1184	1357	1418	88
55°	81	389	1005	1168	1200	74
65°	64	206	746	839	851	64
75°	47	127	410	450	452	50
85°	17	39	102	112	113	18
90°	6	18	47	24	24	6
95°	60	234	780	402	274	66
105°	215	325	1317	1999	1865	227
115°	381	463	1055	2104	2401	376
125°	530	594	959	1621	1912	471
135°	632	695	929	1308	1484	489
145°	733	780	918	1116	1204	459
155°	828	851	918	1007	1037	381
165°	894	906	918	954	966	252
175°	929	929	924	936	936	88
180°	929	929	929	929	929	



TEST NUMBER: P938514
 CATALOG NUMBER: SQ4-FB-150U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	526.2	526.2	526.2	526.2	526.2	526.2	526.2	526.2	526.2	526.2	526.2
2.5°	526.2	526.2	529.6	531.3	534.7	536.4	539.8	543.2	553.3	555.0	558.4
5°	512.7	519.5	541.5	549.9	573.6	605.8	619.3	641.3	687.0	700.5	709.0
7.5°	492.4	507.6	561.8	575.3	634.5	719.1	754.7	802.1	874.8	910.3	939.1
10°	460.2	492.4	588.8	621.0	717.4	846.0	912.0	978.0	1088.0	1137.1	1155.7
12.5°	424.7	477.2	617.6	661.6	800.4	988.2	1067.7	1140.5	1265.7	1331.7	1341.8
15°	384.1	455.2	644.7	709.0	888.3	1106.6	1194.6	1284.3	1401.1	1448.4	1460.3
17.5°	348.6	438.3	670.1	737.8	956.0	1213.2	1302.9	1377.4	1472.1	1504.3	1512.7
20°	304.6	411.2	687.0	775.0	1027.1	1291.1	1377.4	1434.9	1499.2	1519.5	1522.9
22.5°	272.4	382.4	697.1	788.5	1074.5	1338.4	1411.2	1456.9	1500.9	1507.7	1509.3
25°	245.4	350.3	695.5	803.7	1115.1	1367.2	1423.1	1456.9	1482.3	1485.7	1485.7
27.5°	220.0	314.7	688.7	807.1	1145.5	1374.0	1418.0	1441.7	1453.5	1460.3	1460.3
30°	198.0	280.9	671.8	800.4	1159.1	1367.2	1402.7	1414.6	1426.4	1436.6	1441.7
32.5°	181.1	248.7	646.4	786.8	1160.8	1350.3	1375.7	1382.4	1399.4	1423.1	1431.5
35°	165.8	216.6	617.6	768.2	1150.6	1323.2	1340.1	1346.9	1380.7	1416.3	1428.1
37.5°	150.6	192.9	580.4	736.1	1135.4	1291.1	1302.9	1314.8	1367.2	1409.5	1423.1
40°	135.4	172.6	536.4	700.5	1111.7	1252.1	1262.3	1280.9	1350.3	1399.4	1412.9
42.5°	123.5	155.7	489.0	663.3	1081.2	1208.2	1223.4	1250.5	1330.0	1382.4	1397.7
45°	113.4	138.8	438.3	612.5	1042.3	1162.5	1184.5	1221.7	1306.3	1357.1	1370.6
47.5°	103.2	126.9	385.8	560.1	1000.0	1116.8	1145.5	1187.9	1274.1	1323.2	1335.1
50°	94.8	115.1	333.3	504.2	954.3	1067.7	1101.6	1145.5	1233.5	1279.2	1294.5
52.5°	88.0	104.9	284.3	448.4	901.9	1016.9	1055.9	1101.6	1184.5	1228.5	1238.6
55°	81.2	96.4	242.0	389.2	847.7	962.8	1005.1	1049.1	1130.3	1167.5	1174.3
57.5°	77.8	89.7	206.4	333.3	790.2	901.9	949.3	989.9	1066.0	1094.8	1101.6
60°	72.8	84.6	179.4	286.0	727.6	844.4	885.0	925.6	989.9	1013.6	1018.6
62.5°	67.7	81.2	159.1	240.3	663.3	776.7	817.3	854.5	908.7	925.6	932.3
65°	64.3	77.8	143.8	206.4	597.3	705.6	746.2	778.4	822.4	839.3	842.7
67.5°	60.9	74.5	132.0	177.7	531.3	634.5	665.0	695.5	729.3	746.2	747.9
70°	55.8	71.1	121.8	157.4	463.6	553.3	578.7	610.8	637.9	646.4	651.5
72.5°	52.5	66.0	115.1	142.1	394.3	475.5	499.2	517.8	541.5	549.9	549.9
75°	47.4	59.2	108.3	126.9	323.2	389.2	409.5	428.1	446.7	450.1	445.0
77.5°	42.3	52.5	93.1	106.6	252.1	308.0	324.9	335.0	350.3	353.6	355.3
80°	35.5	45.7	72.8	82.9	182.7	226.7	238.6	247.0	260.6	260.6	264.0
82.5°	27.1	35.5	52.5	59.2	123.5	155.7	165.8	170.9	179.4	179.4	179.4
85°	16.9	22.0	33.8	38.9	74.5	94.8	101.5	103.2	110.0	111.7	111.7
87.5°	8.5	11.8	22.0	23.7	38.9	49.1	49.1	52.5	52.5	50.8	49.1
90°	6.2	11.2	16.2	17.5	27.5	40.8	47.4	42.1	31.6	23.7	23.7
92.5°	24.9	67.3	109.8	120.4	169.2	234.3	266.9	233.9	168.0	118.5	113.8
95°	59.9	137.5	215.1	234.5	416.4	659.0	780.3	696.3	528.3	402.3	388.0
97.5°	103.5	172.0	240.5	257.6	560.9	965.4	1167.6	1114.5	1008.3	928.7	901.5
100°	137.2	199.3	261.4	276.9	613.5	1062.3	1286.7	1290.6	1298.4	1304.2	1271.8
102.5°	165.9	223.9	281.8	296.3	637.7	1092.8	1320.4	1388.0	1523.3	1624.8	1597.1
105°	214.6	263.7	312.7	325.0	655.5	1096.2	1316.6	1468.2	1771.5	1999.0	1984.1
107.5°	264.5	310.2	356.0	367.4	658.9	1047.5	1241.8	1453.3	1876.3	2193.6	2197.2
110°	298.1	339.4	380.8	391.1	653.9	1004.2	1179.4	1415.9	1888.8	2243.5	2259.0



TEST NUMBER: P938514

CATALOG NUMBER: SQ4-FB-150U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	331.2	370.6	410.0	419.8	654.1	966.5	1122.7	1364.7	1848.7	2211.7	2235.5
115°	381.1	417.4	453.7	462.8	660.1	923.2	1054.7	1287.8	1754.1	2103.8	2136.9
117.5°	430.4	463.4	496.4	504.6	672.4	896.1	1007.9	1218.3	1639.1	1954.7	1991.4
120°	459.0	490.1	521.1	528.9	682.3	886.9	989.2	1181.4	1565.9	1854.3	1889.9
122.5°	487.1	518.4	549.8	557.6	696.7	882.2	974.9	1148.0	1494.2	1753.9	1789.0
125°	530.2	558.7	587.3	594.4	716.0	878.2	959.3	1106.3	1400.4	1621.0	1653.4
127.5°	565.1	593.9	622.7	629.9	735.3	875.9	946.2	1072.5	1325.0	1514.4	1541.7
130°	583.8	614.8	645.8	653.6	749.5	877.3	941.2	1053.6	1278.4	1447.0	1472.2
132.5°	603.1	634.2	665.2	673.0	760.9	878.2	936.8	1037.4	1238.7	1389.6	1412.2
135°	631.8	660.1	688.3	695.4	773.4	877.3	929.3	1013.6	1182.1	1308.5	1328.0
137.5°	661.1	689.1	717.1	724.1	792.1	882.8	928.1	999.3	1141.8	1248.7	1264.6
140°	685.5	711.3	737.1	743.5	803.6	883.7	923.7	985.2	1108.3	1200.6	1215.5
142.5°	704.2	728.0	751.8	757.8	813.1	886.8	923.7	977.8	1085.9	1167.0	1179.8
145°	732.9	753.7	774.4	779.6	825.6	886.9	917.5	961.7	1050.1	1116.4	1126.1
147.5°	761.5	781.8	802.0	807.1	843.9	893.0	917.5	952.3	1021.8	1074.0	1082.0
150°	780.3	798.6	816.8	821.4	853.4	896.1	917.5	946.9	1005.6	1049.7	1056.2
152.5°	799.6	813.5	827.3	830.8	859.7	898.2	917.5	942.6	992.8	1030.4	1035.3
155°	828.3	838.6	848.8	851.4	873.4	902.8	917.5	937.5	977.4	1007.3	1010.6
157.5°	849.5	859.5	869.4	871.9	887.1	907.4	917.5	933.0	964.0	987.3	989.6
160°	863.8	871.6	879.4	881.3	893.4	909.5	917.5	930.8	957.4	977.3	978.6
162.5°	878.2	884.0	889.8	891.3	900.0	911.7	917.5	928.7	951.2	968.0	969.2
165°	893.8	899.0	904.3	905.6	909.6	914.9	917.5	925.5	941.6	953.6	954.9
167.5°	908.1	910.6	913.1	913.7	917.0	921.5	923.7	929.0	939.5	947.4	948.0
170°	917.5	920.0	922.5	923.1	923.3	923.6	923.7	929.0	939.5	947.4	947.4
172.5°	922.5	923.0	923.6	923.7	923.7	923.7	923.7	927.9	936.2	942.4	941.9
175°	929.3	929.3	929.3	929.3	927.4	924.9	923.7	926.3	931.6	935.6	935.6
177.5°	929.3	929.3	929.3	929.3	927.9	926.0	925.0	927.1	931.2	934.3	933.7
180°	929.3	929.3	929.3	929.3	929.3	929.3	929.3	929.3	929.3	929.3	929.3



TEST NUMBER: P938514

CATALOG NUMBER: SQ4-FB-150U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	526.2	526.2
2.5°	561.8	558.4
5°	722.5	725.9
7.5°	973.0	971.3
10°	1209.8	1225.1
12.5°	1382.4	1385.8
15°	1487.4	1494.1
17.5°	1528.0	1529.7
20°	1529.7	1526.3
22.5°	1511.0	1507.7
25°	1489.0	1487.4
27.5°	1468.7	1470.4
30°	1460.3	1465.4
32.5°	1460.3	1468.7
35°	1463.7	1472.1
37.5°	1462.0	1472.1
40°	1455.2	1467.0
42.5°	1436.6	1445.0
45°	1407.8	1418.0
47.5°	1370.6	1377.4
50°	1323.2	1330.0
52.5°	1264.0	1265.7
55°	1192.9	1199.7
57.5°	1116.8	1118.5
60°	1032.2	1037.3
62.5°	942.5	942.5
65°	847.7	851.1
67.5°	749.6	758.1
70°	649.8	651.5
72.5°	551.6	551.6
75°	450.1	451.8
77.5°	353.6	353.6
80°	262.3	264.0
82.5°	181.1	184.4
85°	113.4	113.4
87.5°	52.5	47.4
90°	23.7	23.7
92.5°	94.9	76.1
95°	330.9	273.8
97.5°	792.9	684.2
100°	1142.4	1012.9
102.5°	1486.2	1375.3
105°	1924.5	1864.9
107.5°	2211.6	2226.0
110°	2321.1	2383.2



TEST NUMBER: P938514

CATALOG NUMBER: SQ4-FB-150U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2330.9	2426.2
115°	2269.1	2401.3
117.5°	2138.0	2284.6
120°	2032.4	2174.9
122.5°	1929.6	2070.1
125°	1782.8	1912.3
127.5°	1650.9	1760.1
130°	1573.1	1674.0
132.5°	1502.5	1592.9
135°	1405.9	1483.8
137.5°	1328.4	1392.1
140°	1275.1	1334.7
142.5°	1231.1	1282.3
145°	1165.0	1203.8
147.5°	1114.2	1146.4
150°	1082.3	1108.3
152.5°	1055.0	1074.6
155°	1023.6	1036.6
157.5°	998.7	1007.9
160°	983.9	989.2
162.5°	974.2	979.2
165°	960.2	965.5
167.5°	950.2	952.4
170°	947.4	947.4
172.5°	940.0	938.1
175°	935.6	935.6
177.5°	931.5	929.3
180°	929.3	929.3



TEST NUMBER: P938514
 CATALOG NUMBER: SQ4-FB-150U-125D-835-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.55	6.36	6.58	7.40	8.80	18.69	19.50	19.72	20.54	21.94
	3H	6.25	6.98	7.29	8.03	9.45	20.51	21.23	21.55	22.28	23.70
	4H	6.55	7.24	7.60	8.29	9.72	21.14	21.83	22.19	22.88	24.31
	6H	6.80	7.43	7.86	8.49	9.93	21.56	22.19	22.62	23.25	24.69
	8H	6.86	7.47	7.93	8.54	9.97	21.67	22.27	22.73	23.35	24.78
	12H	6.88	7.45	7.95	8.52	9.98	21.73	22.30	22.80	23.37	24.83
4H	2H	12.73	13.42	13.79	14.47	15.90	18.96	19.65	20.01	20.70	22.13
	3H	14.30	14.88	15.36	15.95	17.39	20.98	21.56	22.05	22.64	24.08
	4H	14.39	14.92	15.46	15.99	17.45	21.74	22.27	22.81	23.34	24.80
	6H	14.40	14.86	15.48	15.95	17.40	22.26	22.72	23.34	23.81	25.27
	8H	14.37	14.80	15.46	15.89	17.36	22.41	22.84	23.50	23.93	25.40
	12H	14.33	14.72	15.43	15.81	17.29	22.50	22.88	23.60	23.98	25.46
8H	4H	15.82	16.25	16.90	17.33	18.80	21.79	22.22	22.88	23.31	24.78
	6H	16.06	16.41	17.17	17.54	19.01	22.41	22.76	23.51	23.89	25.36
	8H	16.08	16.39	17.19	17.50	18.99	22.62	22.93	23.73	24.04	25.53
	12H	16.04	16.32	17.16	17.42	18.95	22.75	23.03	23.87	24.13	25.66
12H	4H	15.96	16.34	17.06	17.44	18.92	21.74	22.13	22.84	23.23	24.71
	6H	16.32	16.63	17.43	17.74	19.22	22.39	22.70	23.50	23.81	25.30
	8H	16.38	16.65	17.50	17.76	19.29	22.61	22.88	23.73	23.99	25.52