

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562654

Luminaire Tested: **SQ4-PC3-050U-100D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562654
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-100D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5847.0 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562654
CATALOG NUMBER: SQ4-PC3-050U-100D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562654

CATALOG NUMBER: SQ4-PC3-050U-100D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	90	95	91	88	85	81	78	76	72	70	68	63	61	60	56
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	55	53	51	47
3	84	75	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	39
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	36	39	35	32	29
6	65	53	44	38	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	32	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	36	29	24	46	35	28	23	32	26	22	28	23	20	26	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13028	13028	13028
5°	13127	13042	12994
10°	13094	13034	12997
15°	13026	13026	13013
20°	12941	12979	12979
25°	12818	12911	12872
30°	12662	12815	12760
35°	12474	12665	12576
40°	12268	12440	12315
45°	12044	12131	11943
50°	11730	11730	11542
55°	11358	11210	11043
60°	10809	10592	10424
65°	9990	9791	9706
70°	8748	8818	8783
75°	7037	7785	7832
80°	5000	6599	6668
85°	3049	5536	5536



TEST NUMBER: P562654

CATALOG NUMBER: SQ4-PC3-050U-100D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.6	2.3
10°-20°	383.5	6.6
20°-30°	580.8	9.9
30°-40°	696.3	11.9
40°-50°	710.0	12.1
50°-60°	619.8	10.6
60°-70°	443.7	7.6
70°-80°	228.5	3.9
80°-90°	58.9	1.0
90°-100°	146.4	2.5
100°-110°	397.8	6.8
110°-120°	409.0	7.0
120°-130°	327.0	5.6
130°-140°	257.0	4.4
140°-150°	197.0	3.4
150°-160°	141.7	2.4
160°-170°	86.7	1.5
170°-180°	29.2	0.5
0°-30°	1097.9	18.8
0°-40°	1794.2	30.7
0°-60°	3123.9	53.4
0°-90°	3855.1	65.9
90°-120°	953.3	16.3
90°-150°	1734.4	29.7
90°-180°	1992.0	34.1
0°-180°	5847.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1412	1412	1412	1412	1412	
5°	1417	1403	1408	1404	1403	135
15°	1364	1352	1364	1364	1362	385
25°	1259	1250	1268	1264	1264	579
35°	1108	1105	1124	1117	1117	693
45°	923	921	930	918	915	711
55°	706	697	697	686	686	629
65°	458	447	448	445	445	453
75°	197	206	218	220	220	213
85°	29	44	52	54	52	39
90°	1	4	7	9	9	3
95°	22	80	255	111	75	23
105°	71	110	438	666	627	75
115°	126	152	350	697	794	124
125°	173	197	317	534	630	154
135°	208	231	308	435	490	161
145°	240	258	304	370	397	151
155°	272	281	302	332	341	125
165°	294	298	303	316	317	83
175°	305	306	304	308	307	29
180°	305	305	305	305	305	

TEST NUMBER: P562654

CATALOG NUMBER: SQ4-PC3-050U-100D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1412.1	1412.1	1412.1	1412.1	1412.1
2.5°	1420.5	1408.2	1412.1	1408.9	1403.8
5°	1417.4	1403.3	1408.2	1404.3	1403.0
7.5°	1407.2	1393.1	1399.6	1396.9	1395.7
10°	1397.7	1383.7	1391.2	1388.6	1387.3
12.5°	1385.2	1372.2	1380.7	1378.1	1377.9
15°	1363.7	1352.2	1363.7	1363.7	1362.4
17.5°	1336.8	1326.3	1338.6	1339.4	1338.6
20°	1318.0	1306.5	1321.9	1320.6	1321.9
22.5°	1295.0	1285.5	1302.0	1298.7	1299.9
25°	1259.1	1250.2	1268.3	1264.4	1264.4
27.5°	1216.8	1210.4	1230.1	1225.9	1225.9
30°	1188.5	1182.1	1202.9	1197.7	1197.7
32.5°	1157.2	1152.8	1172.6	1166.3	1166.3
35°	1107.5	1104.9	1124.5	1116.6	1116.6
37.5°	1056.2	1053.9	1071.6	1062.2	1059.1
40°	1018.6	1017.3	1032.9	1022.5	1022.5
42.5°	980.9	979.6	993.2	980.6	980.6
45°	923.1	920.6	929.7	917.8	915.3
47.5°	860.1	857.5	863.2	850.4	849.1
50°	817.2	814.6	817.2	805.4	804.1
52.5°	773.3	768.7	769.1	757.3	757.1
55°	706.1	697.1	696.9	686.5	686.5
57.5°	634.9	623.2	624.2	615.3	614.0
60°	585.8	573.0	574.0	566.1	564.9
62.5°	537.7	522.8	525.9	517.0	516.7
65°	457.6	447.4	448.5	444.6	444.6
67.5°	380.8	371.3	378.1	375.0	374.7
70°	324.3	317.9	326.9	326.9	325.6
72.5°	272.0	271.7	282.9	283.0	283.7
75°	197.4	206.4	218.4	219.7	219.7
77.5°	131.8	147.7	160.8	161.3	161.1
80°	94.1	112.0	124.2	126.8	125.5
82.5°	63.8	82.7	92.8	95.4	94.1
85°	28.8	44.1	52.3	53.6	52.3
87.5°	8.6	18.3	22.3	22.6	20.6
90°	1.0	3.9	6.9	8.8	8.8
92.5°	8.8	40.1	69.6	29.9	25.3
95°	21.6	80.1	255.0	111.0	74.6
97.5°	35.7	88.5	391.0	304.2	213.7
100°	45.1	94.0	432.6	438.5	354.1
102.5°	54.5	99.6	443.6	542.3	467.9
105°	70.6	110.0	437.5	666.1	626.8
107.5°	87.3	122.0	412.2	730.1	741.0
110°	99.1	130.7	393.4	742.7	789.7



TEST NUMBER: P562654

CATALOG NUMBER: SQ4-PC3-050U-100D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.3	139.4	374.5	732.2	803.0
115°	125.6	152.4	350.2	696.7	793.6
117.5°	140.9	166.6	334.7	646.4	755.5
120°	151.1	176.0	327.6	612.6	721.0
122.5°	159.7	184.6	322.9	578.8	683.3
125°	172.6	196.6	316.8	533.9	629.8
127.5°	184.2	208.0	313.5	499.8	582.1
130°	191.3	214.3	311.9	478.4	552.3
132.5°	198.3	221.4	310.4	460.2	525.6
135°	208.0	231.0	308.0	434.8	490.5
137.5°	218.4	239.3	306.8	412.5	459.3
140°	224.6	244.8	306.1	398.2	440.4
142.5°	230.9	249.5	305.3	387.1	422.4
145°	240.3	257.6	304.1	369.5	397.3
147.5°	250.9	265.7	303.1	355.6	377.5
150°	258.0	270.5	303.1	347.6	364.9
152.5°	263.5	274.4	302.3	340.5	354.7
155°	271.7	281.3	302.1	331.8	341.4
157.5°	279.8	287.2	302.1	325.8	333.1
160°	284.5	291.2	302.1	321.9	327.6
162.5°	289.2	294.4	302.9	318.7	322.9
165°	294.3	298.1	303.1	315.9	316.8
167.5°	299.6	301.5	304.1	312.5	313.3
170°	301.2	303.1	304.1	311.0	311.0
172.5°	302.7	303.9	304.1	309.4	309.4
175°	305.1	306.0	304.1	308.0	307.0
177.5°	305.9	305.9	303.5	306.6	305.1
180°	305.1	305.1	305.1	305.1	305.1

(END OF REPORT)