

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564023

Luminaire Tested: **SQ4-PR1-050U-125D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564023
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10253.9 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 87.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564023
CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564023

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	75	75	75	71	
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	64	64	64	60	
2	94	87	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55	55	55	55	51	
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	47	47	47	44	
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	41	41	41	38	
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	36	36	36	33	
6	67	55	47	41	63	52	45	39	48	41	37	43	38	34	39	35	32	32	32	32	29	
7	62	50	42	36	59	48	40	35	43	37	33	40	34	30	36	32	28	28	28	28	26	
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	25	25	25	25	23	
9	54	41	34	29	51	40	33	28	37	30	26	33	28	25	31	26	23	23	23	23	21	
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	21	21	21	19	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17873	17873	17873
5°	18034	17895	17802
10°	17977	17852	17758
15°	17898	17786	17691
20°	17808	17693	17562
25°	17683	17564	17360
30°	17492	17367	17119
35°	17233	17083	16839
40°	16841	16660	16358
45°	16154	15871	15544
50°	14945	14585	14298
55°	13044	12749	12480
60°	10991	10899	10684
65°	9507	9543	9470
70°	8733	8778	8778
75°	8387	8387	8446
80°	7892	7980	7892
85°	6359	7064	7064



TEST NUMBER: P564023

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.8	2.7
10°-20°	786.2	7.7
20°-30°	1185.8	11.6
30°-40°	1412.9	13.8
40°-50°	1393.0	13.6
50°-60°	1064.6	10.4
60°-70°	658.8	6.4
70°-80°	374.2	3.6
80°-90°	115.6	1.1
90°-100°	219.7	2.1
100°-110°	596.8	5.8
110°-120°	613.6	6.0
120°-130°	490.6	4.8
130°-140°	385.5	3.8
140°-150°	295.6	2.9
150°-160°	212.5	2.1
160°-170°	130.0	1.3
170°-180°	43.8	0.4
0°-30°	2246.8	21.9
0°-40°	3659.7	35.7
0°-60°	6117.4	59.7
0°-90°	7266.0	70.9
90°-120°	1430.0	13.9
90°-150°	2601.6	25.4
90°-180°	2988.0	29.1
0°-180°	10253.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2906	2906	2906	2906	2906	
5°	2921	2889	2898	2888	2883	277
15°	2811	2781	2793	2783	2778	793
25°	2606	2574	2588	2560	2558	1199
35°	2295	2268	2275	2245	2243	1432
45°	1857	1833	1825	1792	1787	1423
55°	1216	1197	1189	1169	1164	1090
65°	653	648	656	651	651	662
75°	353	353	353	355	355	373
85°	90	95	100	100	100	105
90°	2	6	10	13	13	6
95°	32	120	383	166	112	34
105°	106	165	656	999	940	113
115°	188	229	525	1045	1190	186
125°	259	295	475	801	945	231
135°	312	346	462	652	736	241
145°	360	386	456	554	596	226
155°	408	422	453	498	512	188
165°	441	447	455	474	475	125
175°	458	459	456	462	461	43
180°	458	458	458	458	458	

TEST NUMBER: P564023

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2905.8	2905.8	2905.8	2905.8	2905.8
2.5°	2923.8	2898.4	2905.8	2899.5	2885.8
5°	2920.8	2889.0	2898.3	2888.2	2883.3
7.5°	2898.3	2867.0	2876.3	2866.2	2863.3
10°	2878.3	2848.9	2858.3	2848.1	2843.3
12.5°	2856.3	2824.9	2836.2	2824.1	2819.2
15°	2810.7	2781.3	2793.2	2783.1	2778.2
17.5°	2760.7	2729.3	2741.1	2729.5	2723.1
20°	2720.6	2691.2	2703.1	2685.5	2683.1
22.5°	2676.6	2647.2	2659.0	2635.5	2635.0
25°	2605.5	2573.7	2588.0	2560.4	2557.9
27.5°	2520.9	2491.5	2503.4	2475.3	2472.3
30°	2462.8	2433.4	2445.3	2415.2	2410.3
32.5°	2396.7	2369.3	2379.2	2349.1	2346.2
35°	2295.1	2268.2	2275.1	2245.0	2242.6
37.5°	2179.5	2155.0	2159.0	2125.9	2123.4
40°	2097.4	2072.9	2074.9	2039.8	2037.3
42.5°	2007.3	1982.8	1980.8	1945.7	1943.2
45°	1857.1	1832.7	1824.6	1791.9	1787.0
47.5°	1685.9	1661.5	1646.4	1619.8	1616.3
50°	1561.8	1537.3	1524.2	1501.6	1494.2
52.5°	1427.6	1403.2	1392.1	1371.4	1364.1
55°	1216.4	1196.8	1188.9	1168.7	1163.8
57.5°	1015.7	1002.4	1000.1	980.6	978.6
60°	893.5	886.2	886.0	868.5	868.5
62.5°	789.4	784.0	787.9	776.3	774.4
65°	653.2	648.4	655.7	650.7	650.7
67.5°	545.6	545.6	550.1	548.1	548.1
70°	485.6	485.6	488.1	488.1	488.1
72.5°	431.5	429.5	436.0	436.0	434.0
75°	352.9	352.9	352.9	355.4	355.4
77.5°	274.8	275.3	277.3	276.8	274.8
80°	222.8	225.2	225.3	222.8	222.8
82.5°	170.7	173.1	173.2	172.7	170.7
85°	90.1	95.0	100.1	100.1	100.1
87.5°	26.3	35.0	42.1	42.6	40.7
90°	1.5	5.8	10.3	13.2	13.2
92.5°	13.2	60.1	104.5	44.9	38.0
95°	32.4	120.1	382.6	166.5	111.8
97.5°	53.6	132.7	586.5	456.3	320.5
100°	67.7	141.1	648.9	657.8	531.2
102.5°	81.8	149.4	665.4	813.5	701.9
105°	105.9	164.9	656.3	999.2	940.2
107.5°	131.0	183.0	618.3	1095.1	1111.5
110°	148.6	196.1	590.0	1114.0	1184.5

TEST NUMBER: P564023

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	163.9	209.1	561.8	1098.3	1204.5
115°	188.3	228.6	525.3	1045.1	1190.4
117.5°	211.3	249.9	502.0	969.6	1133.3
120°	226.6	264.0	491.5	918.9	1081.5
122.5°	239.5	277.0	484.4	868.2	1025.0
125°	259.0	294.9	475.3	800.8	944.7
127.5°	276.3	312.0	470.3	749.7	873.1
130°	286.9	321.5	467.9	717.6	828.4
132.5°	297.5	332.1	465.6	690.3	788.4
135°	311.9	346.5	462.0	652.3	735.7
137.5°	327.5	358.9	460.3	618.7	688.9
140°	337.0	367.2	459.1	597.4	660.7
142.5°	346.4	374.3	457.9	580.6	633.6
145°	360.5	386.4	456.1	554.2	595.9
147.5°	376.4	398.5	454.7	533.4	566.2
150°	387.0	405.7	454.7	521.5	547.4
152.5°	395.2	411.6	453.5	510.8	532.1
155°	407.6	422.0	453.2	497.7	512.1
157.5°	419.6	430.9	453.2	488.8	499.7
160°	426.7	436.8	453.2	482.8	491.5
162.5°	433.8	441.5	454.4	478.1	484.4
165°	441.4	447.2	454.7	473.8	475.3
167.5°	449.4	452.2	456.1	468.8	470.0
170°	451.7	454.6	456.1	466.4	466.4
172.5°	454.1	455.8	456.1	464.1	464.1
175°	457.6	459.1	456.1	462.0	460.6
177.5°	458.8	458.8	455.3	459.9	457.6
180°	457.6	457.6	457.6	457.6	457.6

(END OF REPORT)