

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562774

Luminaire Tested: **SQ4-PC3-075U-125D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562774
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7913.1 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562774
CATALOG NUMBER: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562774

CATALOG NUMBER: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	73	86	79	73	69	69	65	62	61	57	55	52	50	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16627	16627	16627
5°	16751	16644	16582
10°	16711	16633	16586
15°	16623	16623	16607
20°	16513	16563	16563
25°	16357	16476	16425
30°	16158	16354	16283
35°	15918	16163	16050
40°	15655	15876	15715
45°	15370	15480	15240
50°	14969	14969	14729
55°	14493	14306	14091
60°	13793	13516	13300
65°	12749	12494	12385
70°	11163	11252	11208
75°	8983	9935	9992
80°	6381	8421	8512
85°	3885	7061	7061



TEST NUMBER: P562774

CATALOG NUMBER: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.5	2.2
10°-20°	489.4	6.2
20°-30°	741.2	9.4
30°-40°	888.6	11.2
40°-50°	906.0	11.4
50°-60°	790.9	10.0
60°-70°	566.2	7.2
70°-80°	291.6	3.7
80°-90°	74.9	0.9
90°-100°	216.8	2.7
100°-110°	596.3	7.5
110°-120°	615.5	7.8
120°-130°	493.1	6.2
130°-140°	387.3	4.9
140°-150°	296.8	3.8
150°-160°	213.4	2.7
160°-170°	130.5	1.6
170°-180°	44.0	0.6
0°-30°	1401.1	17.7
0°-40°	2289.7	28.9
0°-60°	3986.6	50.4
0°-90°	4919.4	62.2
90°-120°	1428.6	18.1
90°-150°	2605.9	32.9
90°-180°	2994.0	37.8
0°-180°	7913.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1802	1802	1802	1802	1802	
5°	1809	1791	1797	1792	1790	172
15°	1740	1726	1740	1740	1739	491
25°	1607	1595	1618	1614	1614	739
35°	1413	1410	1435	1425	1425	884
45°	1178	1175	1186	1171	1168	907
55°	901	890	889	876	876	803
65°	584	571	572	567	567	578
75°	252	263	279	280	280	272
85°	37	56	67	68	67	50
90°	1	4	7	9	9	4
95°	32	118	383	164	105	34
105°	107	164	657	1001	934	112
115°	189	230	527	1049	1191	186
125°	260	296	478	809	948	232
135°	314	348	464	654	740	242
145°	363	388	458	557	600	227
155°	411	424	455	501	515	189
165°	444	450	457	475	478	125
175°	460	460	458	463	462	44
180°	460	460	460	460	460	

TEST NUMBER: P562774

CATALOG NUMBER: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1802.1	1802.1	1802.1	1802.1	1802.1
2.5°	1812.7	1797.1	1802.1	1797.9	1791.4
5°	1808.7	1790.8	1797.1	1792.0	1790.4
7.5°	1795.7	1777.8	1786.0	1782.7	1781.0
10°	1783.7	1765.8	1775.4	1772.0	1770.4
12.5°	1767.7	1751.1	1762.0	1758.7	1758.3
15°	1740.3	1725.6	1740.3	1740.3	1738.7
17.5°	1706.0	1692.6	1708.3	1709.3	1708.3
20°	1681.9	1667.2	1686.9	1685.3	1686.9
22.5°	1652.6	1640.5	1661.6	1657.3	1658.9
25°	1606.8	1595.4	1618.5	1613.5	1613.5
27.5°	1552.8	1544.6	1569.8	1564.5	1564.5
30°	1516.7	1508.6	1535.1	1528.4	1528.4
32.5°	1476.7	1471.1	1496.4	1488.4	1488.4
35°	1413.3	1410.0	1435.0	1425.0	1425.0
37.5°	1347.9	1344.9	1367.6	1355.5	1351.5
40°	1299.8	1298.2	1318.2	1304.8	1304.8
42.5°	1251.8	1250.1	1267.5	1251.4	1251.4
45°	1178.0	1174.8	1186.4	1171.3	1168.0
47.5°	1097.6	1094.3	1101.6	1085.2	1083.6
50°	1042.9	1039.6	1042.9	1027.8	1026.2
52.5°	986.8	980.9	981.5	966.4	966.1
55°	901.0	889.6	889.4	876.0	876.0
57.5°	810.3	795.3	796.6	785.2	783.6
60°	747.5	731.2	732.5	722.5	720.8
62.5°	686.1	667.2	671.1	659.7	659.4
65°	584.0	571.0	572.3	567.3	567.3
67.5°	485.9	473.8	482.6	478.5	478.2
70°	413.8	405.6	417.1	417.1	415.5
72.5°	347.1	346.7	361.1	361.1	362.1
75°	252.0	263.4	278.7	280.3	280.3
77.5°	168.2	188.4	205.2	205.9	205.6
80°	120.1	143.0	158.5	161.8	160.2
82.5°	81.4	105.6	118.5	121.8	120.1
85°	36.7	56.3	66.7	68.4	66.7
87.5°	10.9	23.2	28.1	28.4	25.8
90°	1.0	3.8	6.8	8.8	8.8
92.5°	13.5	57.7	99.9	38.4	31.5
95°	32.3	118.3	383.3	163.9	104.6
97.5°	52.6	131.2	584.9	450.7	318.0
100°	67.5	139.2	648.3	654.3	533.9
102.5°	81.5	148.7	664.7	811.8	701.3
105°	106.6	163.9	657.1	1000.7	933.8
107.5°	130.4	182.8	619.7	1093.2	1113.1
110°	147.6	195.4	591.5	1116.2	1185.1

TEST NUMBER: P562774

CATALOG NUMBER: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	163.3	209.6	563.4	1101.4	1206.2
115°	188.7	229.8	527.0	1049.4	1190.9
117.5°	213.0	250.8	503.9	976.5	1136.6
120°	227.8	264.1	493.8	921.9	1087.3
122.5°	241.1	277.4	486.7	874.0	1031.0
125°	260.1	296.4	478.1	808.8	947.5
127.5°	278.1	312.7	472.5	754.5	876.1
130°	287.5	322.8	469.3	722.2	833.1
132.5°	298.4	333.8	467.0	693.8	793.9
135°	313.9	348.3	464.4	654.1	740.2
137.5°	328.3	360.3	462.3	622.1	693.0
140°	339.3	368.9	461.5	600.8	664.9
142.5°	348.7	376.0	459.9	581.8	636.7
145°	362.8	387.6	457.6	557.3	600.3
147.5°	377.8	399.2	456.4	535.6	570.0
150°	387.2	406.3	455.6	523.7	550.5
152.5°	395.8	413.4	454.9	513.4	535.6
155°	410.7	424.0	454.7	500.9	515.3
157.5°	421.4	432.3	454.7	490.7	500.6
160°	429.2	437.8	454.7	485.1	492.8
162.5°	435.5	442.6	455.4	480.4	486.5
165°	443.9	449.6	456.6	475.3	478.1
167.5°	449.8	454.2	457.6	470.9	471.7
170°	453.7	456.6	457.6	469.3	469.3
172.5°	456.8	458.2	457.6	467.0	466.2
175°	459.5	460.5	457.6	463.4	462.5
177.5°	460.3	460.3	457.2	461.9	460.3
180°	459.5	459.5	459.5	459.5	459.5

(END OF REPORT)