

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564407

Luminaire Tested: **SQ4-PR1-125U-125D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564407
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-125D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14765.9 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 117.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564407
CATALOG NUMBER: SQ4-PR1-125U-125D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564407

CATALOG NUMBER: SQ4-PR1-125U-125D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49				
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36				
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35	31				
4	75	64	56	51	69	60	53	47	51	46	41	43	39	36	35	32	30	26				
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23				
6	63	51	43	38	58	48	41	36	41	36	31	35	30	27	29	26	23	20				
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18				
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16				
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15				
10	47	35	28	23	44	33	27	22	29	23	20	25	20	18	21	18	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17873	17873	17873
5°	18034	17895	17802
10°	17977	17852	17758
15°	17898	17786	17691
20°	17808	17693	17562
25°	17683	17564	17360
30°	17492	17367	17119
35°	17233	17083	16839
40°	16841	16660	16358
45°	16154	15871	15544
50°	14945	14585	14298
55°	13044	12749	12480
60°	10991	10899	10684
65°	9507	9543	9470
70°	8733	8778	8778
75°	8387	8387	8446
80°	7892	7980	7892
85°	6359	7064	7064



TEST NUMBER: P564407

CATALOG NUMBER: SQ4-PR1-125U-125D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.8	1.9
10°-20°	786.2	5.3
20°-30°	1185.8	8.0
30°-40°	1412.9	9.6
40°-50°	1393.0	9.4
50°-60°	1064.6	7.2
60°-70°	658.8	4.5
70°-80°	374.2	2.5
80°-90°	116.6	0.8
90°-100°	543.4	3.7
100°-110°	1463.8	9.9
110°-120°	1536.2	10.4
120°-130°	1246.6	8.4
130°-140°	977.7	6.6
140°-150°	750.6	5.1
150°-160°	539.7	3.7
160°-170°	329.7	2.2
170°-180°	111.2	0.8
0°-30°	2246.8	15.2
0°-40°	3659.7	24.8
0°-60°	6117.4	41.4
0°-90°	7267.0	49.2
90°-120°	3543.5	24.0
90°-150°	6518.4	44.1
90°-180°	7499.0	50.8
0°-180°	14765.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2906	2906	2906	2906	2906	
5°	2921	2889	2898	2888	2883	277
15°	2811	2781	2793	2783	2778	793
25°	2606	2574	2588	2560	2558	1199
35°	2295	2268	2275	2245	2243	1432
45°	1857	1833	1825	1792	1787	1423
55°	1216	1197	1189	1169	1164	1090
65°	653	648	656	651	651	662
75°	353	353	353	355	355	373
85°	90	95	100	100	100	105
90°	3	9	18	19	19	9
95°	83	296	891	456	315	87
105°	271	421	1619	2422	2273	285
115°	478	585	1348	2605	2946	470
125°	653	750	1210	2046	2408	583
135°	786	877	1176	1650	1869	607
145°	909	980	1162	1411	1515	570
155°	1031	1069	1151	1266	1307	475
165°	1119	1132	1156	1202	1208	315
175°	1163	1162	1157	1173	1170	110
180°	1162	1162	1162	1162	1162	

TEST NUMBER: P564407

CATALOG NUMBER: SQ4-PR1-125U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2905.8	2905.8	2905.8	2905.8	2905.8
2.5°	2923.8	2898.4	2905.8	2899.5	2885.8
5°	2920.8	2889.0	2898.3	2888.2	2883.3
7.5°	2898.3	2867.0	2876.3	2866.2	2863.3
10°	2878.3	2848.9	2858.3	2848.1	2843.3
12.5°	2856.3	2824.9	2836.2	2824.1	2819.2
15°	2810.7	2781.3	2793.2	2783.1	2778.2
17.5°	2760.7	2729.3	2741.1	2729.5	2723.1
20°	2720.6	2691.2	2703.1	2685.5	2683.1
22.5°	2676.6	2647.2	2659.0	2635.5	2635.0
25°	2605.5	2573.7	2588.0	2560.4	2557.9
27.5°	2520.9	2491.5	2503.4	2475.3	2472.3
30°	2462.8	2433.4	2445.3	2415.2	2410.3
32.5°	2396.7	2369.3	2379.2	2349.1	2346.2
35°	2295.1	2268.2	2275.1	2245.0	2242.6
37.5°	2179.5	2155.0	2159.0	2125.9	2123.4
40°	2097.4	2072.9	2074.9	2039.8	2037.3
42.5°	2007.3	1982.8	1980.8	1945.7	1943.2
45°	1857.1	1832.7	1824.6	1791.9	1787.0
47.5°	1685.9	1661.5	1646.4	1619.8	1616.3
50°	1561.8	1537.3	1524.2	1501.6	1494.2
52.5°	1427.6	1403.2	1392.1	1371.4	1364.1
55°	1216.4	1196.8	1188.9	1168.7	1163.8
57.5°	1015.7	1002.4	1000.1	980.6	978.6
60°	893.5	886.2	886.0	868.5	868.5
62.5°	789.4	784.0	787.9	776.3	774.4
65°	653.2	648.4	655.7	650.7	650.7
67.5°	545.6	545.6	550.1	548.1	548.1
70°	485.6	485.6	488.1	488.1	488.1
72.5°	431.5	429.5	436.0	436.0	434.0
75°	352.9	352.9	352.9	355.4	355.4
77.5°	274.8	275.3	277.3	276.8	274.8
80°	222.8	225.2	225.3	222.8	222.8
82.5°	170.7	173.1	173.2	172.7	170.7
85°	90.1	95.0	100.1	100.1	100.1
87.5°	26.6	35.6	43.6	43.8	41.9
90°	3.0	8.7	17.8	19.2	19.2
92.5°	36.1	127.6	252.2	121.4	84.3
95°	82.9	295.6	890.8	455.5	315.2
97.5°	132.3	338.3	1397.2	1167.2	880.2
100°	170.2	355.4	1558.2	1630.3	1352.5
102.5°	206.9	379.3	1611.5	1977.1	1749.1
105°	270.8	421.3	1618.9	2422.0	2272.9
107.5°	331.2	465.4	1549.9	2650.6	2689.1
110°	371.4	498.8	1487.2	2721.5	2861.9



TEST NUMBER: P564407

CATALOG NUMBER: SQ4-PR1-125U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	414.0	532.1	1426.8	2705.8	2936.5
115°	478.0	585.0	1348.1	2604.8	2946.2
117.5°	536.3	636.7	1287.1	2443.5	2823.7
120°	574.2	671.1	1256.3	2327.7	2718.4
122.5°	607.3	703.1	1233.8	2209.3	2598.8
125°	652.6	749.5	1210.5	2045.9	2407.6
127.5°	696.1	791.6	1195.7	1901.8	2224.7
130°	722.1	817.6	1189.7	1819.2	2102.8
132.5°	748.2	842.5	1183.8	1746.4	2006.9
135°	785.8	876.9	1176.4	1650.5	1869.0
137.5°	821.6	909.0	1172.6	1569.1	1748.5
140°	846.4	930.4	1169.0	1519.0	1681.0
142.5°	872.5	950.6	1166.7	1472.2	1608.8
145°	908.6	979.5	1161.6	1411.1	1515.3
147.5°	947.7	1009.3	1156.6	1359.7	1441.6
150°	973.7	1027.2	1154.2	1327.4	1395.4
152.5°	997.4	1044.0	1153.0	1301.1	1356.4
155°	1031.4	1069.0	1151.3	1266.1	1306.6
157.5°	1061.3	1090.5	1151.6	1241.6	1268.8
160°	1080.2	1104.8	1152.7	1227.2	1247.5
162.5°	1096.8	1116.8	1153.9	1215.2	1229.7
165°	1118.7	1131.7	1155.7	1201.7	1207.5
167.5°	1136.5	1144.0	1157.2	1191.3	1193.6
170°	1148.3	1151.2	1157.2	1185.3	1185.3
172.5°	1155.4	1156.0	1158.4	1179.4	1179.4
175°	1163.1	1161.7	1157.2	1173.4	1170.5
177.5°	1166.4	1164.0	1158.1	1167.5	1165.2
180°	1161.6	1161.6	1161.6	1161.6	1161.6

(END OF REPORT)