

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563278

Luminaire Tested: **SQ4-PP3-050U-050D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563278
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-050D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3942.4 lumens
Efficiency: N/A
Efficacy: 138.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 28.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563278
CATALOG NUMBER: SQ4-PP3-050U-050D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563278

CATALOG NUMBER: SQ4-PP3-050U-050D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47				42	
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40				36	
3	82	72	65	59	75	67	61	55	57	52	48	48	44	41	39	36	34				30	
4	75	64	56	50	69	59	52	47	51	45	41	42	38	35	35	32	30				26	
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26				23	
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23				20	
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20				18	
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18				16	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16				14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7027	7027	7027
5°	7079	7035	7011
10°	7067	7016	6985
15°	7020	6981	6943
20°	6973	6934	6882
25°	6891	6843	6775
30°	6763	6728	6642
35°	6586	6540	6458
40°	6375	6335	6263
45°	6202	6157	6097
50°	5978	5941	5882
55°	5668	5594	5551
60°	5161	5014	4988
65°	4547	4357	4342
70°	3925	3763	3763
75°	3379	3333	3283
80°	2981	3013	2943
85°	2329	2541	2541



TEST NUMBER: P563278

CATALOG NUMBER: SQ4-PP3-050U-050D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.0	1.8
10°-20°	205.6	5.2
20°-30°	308.0	7.8
30°-40°	361.3	9.2
40°-50°	362.4	9.2
50°-60°	309.2	7.8
60°-70°	201.6	5.1
70°-80°	101.2	2.6
80°-90°	29.2	0.7
90°-100°	146.4	3.7
100°-110°	397.8	10.1
110°-120°	409.0	10.4
120°-130°	327.0	8.3
130°-140°	257.0	6.5
140°-150°	197.0	5.0
150°-160°	141.7	3.6
160°-170°	86.7	2.2
170°-180°	29.2	0.7
0°-30°	585.7	14.9
0°-40°	947.0	24.0
0°-60°	1618.6	41.1
0°-90°	1950.5	49.5
90°-120°	953.3	24.2
90°-150°	1734.4	44.0
90°-180°	1992.0	50.5
0°-180°	3942.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	762	762	762	762	762	
5°	764	757	760	757	757	73
15°	735	728	731	728	727	207
25°	677	669	672	666	666	311
35°	585	579	581	574	573	365
45°	475	472	472	467	467	366
55°	352	351	348	346	345	313
65°	208	204	200	198	199	208
75°	95	95	94	93	92	103
85°	22	24	24	24	24	26
90°	1	4	7	9	9	2
95°	22	80	255	111	75	23
105°	71	110	438	666	627	75
115°	126	152	350	697	794	124
125°	173	197	317	534	630	154
135°	208	231	308	435	490	161
145°	240	258	304	370	397	151
155°	272	281	302	332	341	125
165°	294	298	303	316	317	83
175°	305	306	304	308	307	29
180°	305	305	305	305	305	

TEST NUMBER: P563278

CATALOG NUMBER: SQ4-PP3-050U-050D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	761.6	761.6	761.6	761.6	761.6
2.5°	766.4	760.2	761.6	760.5	757.4
5°	764.3	757.1	759.6	757.0	757.0
7.5°	759.1	751.3	753.7	751.1	750.9
10°	754.3	746.5	748.9	746.3	745.6
12.5°	747.3	739.5	742.5	739.3	739.2
15°	734.9	727.7	730.9	728.2	726.9
17.5°	720.9	713.1	716.9	713.2	712.6
20°	710.2	702.4	706.2	700.9	700.9
22.5°	697.4	689.6	693.9	687.0	687.0
25°	676.9	669.0	672.2	666.2	665.5
27.5°	652.4	644.7	648.0	641.2	641.1
30°	634.8	627.6	631.5	624.1	623.5
32.5°	615.6	608.9	611.7	604.3	603.7
35°	584.7	578.9	580.7	574.0	573.4
37.5°	552.3	546.3	548.4	542.7	542.4
40°	529.3	525.4	526.0	521.3	520.0
42.5°	508.0	503.5	504.1	499.4	499.2
45°	475.3	472.0	471.9	467.3	467.3
47.5°	440.6	438.1	437.4	433.5	433.3
50°	416.5	414.6	413.9	410.5	409.8
52.5°	391.4	390.5	388.2	385.4	385.3
55°	352.4	351.1	347.8	345.8	345.1
57.5°	310.1	307.5	303.7	300.8	301.3
60°	279.7	277.1	271.7	270.3	270.3
62.5°	250.3	247.2	241.8	239.9	241.0
65°	208.3	204.3	199.6	198.3	198.9
67.5°	170.1	166.6	161.4	161.4	160.9
70°	145.5	143.6	139.5	139.5	139.5
72.5°	123.6	122.7	119.8	119.7	119.2
75°	94.8	94.8	93.5	92.8	92.1
77.5°	71.0	71.3	70.6	69.9	68.8
80°	56.1	57.4	56.7	56.1	55.4
82.5°	42.2	43.5	43.4	42.2	42.1
85°	22.0	24.0	24.0	24.0	24.0
87.5°	6.1	8.7	9.9	10.3	10.8
90°	1.0	3.9	6.9	8.8	8.8
92.5°	8.8	40.1	69.6	29.9	25.3
95°	21.6	80.1	255.0	111.0	74.6
97.5°	35.7	88.5	391.0	304.2	213.7
100°	45.1	94.0	432.6	438.5	354.1
102.5°	54.5	99.6	443.6	542.3	467.9
105°	70.6	110.0	437.5	666.1	626.8
107.5°	87.3	122.0	412.2	730.1	741.0
110°	99.1	130.7	393.4	742.7	789.7



TEST NUMBER: P563278

CATALOG NUMBER: SQ4-PP3-050U-050D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.3	139.4	374.5	732.2	803.0
115°	125.6	152.4	350.2	696.7	793.6
117.5°	140.9	166.6	334.7	646.4	755.5
120°	151.1	176.0	327.6	612.6	721.0
122.5°	159.7	184.6	322.9	578.8	683.3
125°	172.6	196.6	316.8	533.9	629.8
127.5°	184.2	208.0	313.5	499.8	582.1
130°	191.3	214.3	311.9	478.4	552.3
132.5°	198.3	221.4	310.4	460.2	525.6
135°	208.0	231.0	308.0	434.8	490.5
137.5°	218.4	239.3	306.8	412.5	459.3
140°	224.6	244.8	306.1	398.2	440.4
142.5°	230.9	249.5	305.3	387.1	422.4
145°	240.3	257.6	304.1	369.5	397.3
147.5°	250.9	265.7	303.1	355.6	377.5
150°	258.0	270.5	303.1	347.6	364.9
152.5°	263.5	274.4	302.3	340.5	354.7
155°	271.7	281.3	302.1	331.8	341.4
157.5°	279.8	287.2	302.1	325.8	333.1
160°	284.5	291.2	302.1	321.9	327.6
162.5°	289.2	294.4	302.9	318.7	322.9
165°	294.3	298.1	303.1	315.9	316.8
167.5°	299.6	301.5	304.1	312.5	313.3
170°	301.2	303.1	304.1	311.0	311.0
172.5°	302.7	303.9	304.1	309.4	309.4
175°	305.1	306.0	304.1	308.0	307.0
177.5°	305.9	305.9	303.5	306.6	305.1
180°	305.1	305.1	305.1	305.1	305.1

(END OF REPORT)