

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563350

Luminaire Tested: **SQ4-PP3-050U-125D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563350
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6864.7 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563350
CATALOG NUMBER: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563350

CATALOG NUMBER: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	60
2	94	86	80	75	89	82	76	72	74	69	66	66	63	60	59	57	55	51
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	50	47	43
4	79	68	59	53	74	64	57	51	58	52	48	53	48	44	47	44	40	37
5	72	60	52	46	68	58	50	44	52	46	41	47	42	38	43	39	35	33
6	67	54	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31	29
7	62	49	41	35	58	47	39	34	43	37	32	39	34	30	35	31	28	25
8	57	45	37	31	54	43	35	30	39	33	29	36	31	27	33	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	25	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17561	17561	17561
5°	17690	17582	17520
10°	17660	17535	17457
15°	17544	17448	17353
20°	17427	17328	17198
25°	17219	17101	16931
30°	16901	16812	16599
35°	16459	16346	16140
40°	15933	15832	15651
45°	15497	15389	15236
50°	14940	14846	14702
55°	14168	13980	13874
60°	12898	12529	12466
65°	11363	10889	10852
70°	9811	9406	9406
75°	8445	8324	8206
80°	7444	7534	7359
85°	5833	6362	6362



TEST NUMBER: P563350

CATALOG NUMBER: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.0	2.6
10°-20°	513.9	7.5
20°-30°	769.8	11.2
30°-40°	902.9	13.2
40°-50°	905.7	13.2
50°-60°	772.7	11.3
60°-70°	503.9	7.3
70°-80°	252.8	3.7
80°-90°	71.1	1.0
90°-100°	146.4	2.1
100°-110°	397.8	5.8
110°-120°	409.0	6.0
120°-130°	327.0	4.8
130°-140°	257.0	3.7
140°-150°	197.0	2.9
150°-160°	141.7	2.1
160°-170°	86.7	1.3
170°-180°	29.2	0.4
0°-30°	1463.7	21.3
0°-40°	2366.6	34.5
0°-60°	4045.0	58.9
0°-90°	4872.8	71.0
90°-120°	953.3	13.9
90°-150°	1734.4	25.3
90°-180°	1992.0	29.0
0°-180°	6864.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1910	1892	1898	1892	1892	181
15°	1837	1819	1827	1820	1817	518
25°	1692	1672	1680	1665	1663	778
35°	1461	1447	1451	1435	1433	913
45°	1188	1180	1179	1168	1168	915
55°	881	878	869	864	862	783
65°	520	511	499	496	497	519
75°	237	237	234	232	230	257
85°	55	60	60	60	60	65
90°	1	4	7	9	9	4
95°	22	80	255	111	75	23
105°	71	110	438	666	627	75
115°	126	152	350	697	794	124
125°	173	197	317	534	630	154
135°	208	231	308	435	490	161
145°	240	258	304	370	397	151
155°	272	281	302	332	341	125
165°	294	298	303	316	317	83
175°	305	306	304	308	307	29
180°	305	305	305	305	305	



TEST NUMBER: P563350

CATALOG NUMBER: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1903.4	1903.4	1903.4	1903.4	1903.4
2.5°	1915.4	1899.7	1903.4	1900.5	1892.7
5°	1910.1	1892.1	1898.4	1891.7	1891.7
7.5°	1897.1	1877.5	1883.7	1877.0	1876.7
10°	1885.0	1865.5	1871.7	1865.0	1863.4
12.5°	1867.7	1848.1	1855.7	1847.7	1847.3
15°	1836.7	1818.7	1826.7	1819.9	1816.7
17.5°	1801.6	1782.1	1791.6	1782.3	1781.0
20°	1774.9	1755.4	1764.9	1751.6	1751.6
22.5°	1742.9	1723.3	1734.2	1716.9	1716.9
25°	1691.5	1672.0	1679.9	1664.8	1663.2
27.5°	1630.5	1611.2	1619.5	1602.4	1602.1
30°	1586.4	1568.5	1578.1	1559.7	1558.1
32.5°	1538.4	1521.8	1528.7	1510.3	1508.7
35°	1461.3	1446.6	1451.3	1434.6	1433.0
37.5°	1380.3	1365.2	1370.6	1356.2	1355.6
40°	1322.9	1313.1	1314.5	1302.8	1299.5
42.5°	1269.5	1258.4	1259.8	1248.1	1247.5
45°	1187.7	1179.6	1179.4	1167.7	1167.7
47.5°	1101.0	1094.8	1093.0	1083.3	1083.0
50°	1040.9	1036.1	1034.3	1025.9	1024.3
52.5°	978.2	975.9	970.2	963.2	962.9
55°	880.8	877.5	869.1	864.1	862.5
57.5°	775.0	768.5	759.0	751.7	753.0
60°	699.0	692.4	679.0	675.6	675.6
62.5°	625.6	617.7	604.2	599.6	602.2
65°	520.5	510.7	498.8	495.5	497.1
67.5°	425.1	416.2	403.4	403.3	402.0
70°	363.7	358.8	348.7	348.7	348.7
72.5°	308.9	306.7	299.3	299.2	297.9
75°	236.9	236.9	233.5	231.8	230.2
77.5°	177.5	178.1	176.5	174.8	171.8
80°	140.1	143.4	141.8	140.1	138.5
82.5°	105.4	108.7	108.4	105.4	105.1
85°	55.1	59.9	60.1	60.1	60.1
87.5°	14.9	20.7	22.7	23.1	24.5
90°	1.0	3.9	6.9	8.8	8.8
92.5°	8.8	40.1	69.6	29.9	25.3
95°	21.6	80.1	255.0	111.0	74.6
97.5°	35.7	88.5	391.0	304.2	213.7
100°	45.1	94.0	432.6	438.5	354.1
102.5°	54.5	99.6	443.6	542.3	467.9
105°	70.6	110.0	437.5	666.1	626.8
107.5°	87.3	122.0	412.2	730.1	741.0
110°	99.1	130.7	393.4	742.7	789.7

TEST NUMBER: P563350

CATALOG NUMBER: SQ4-PP3-050U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.3	139.4	374.5	732.2	803.0
115°	125.6	152.4	350.2	696.7	793.6
117.5°	140.9	166.6	334.7	646.4	755.5
120°	151.1	176.0	327.6	612.6	721.0
122.5°	159.7	184.6	322.9	578.8	683.3
125°	172.6	196.6	316.8	533.9	629.8
127.5°	184.2	208.0	313.5	499.8	582.1
130°	191.3	214.3	311.9	478.4	552.3
132.5°	198.3	221.4	310.4	460.2	525.6
135°	208.0	231.0	308.0	434.8	490.5
137.5°	218.4	239.3	306.8	412.5	459.3
140°	224.6	244.8	306.1	398.2	440.4
142.5°	230.9	249.5	305.3	387.1	422.4
145°	240.3	257.6	304.1	369.5	397.3
147.5°	250.9	265.7	303.1	355.6	377.5
150°	258.0	270.5	303.1	347.6	364.9
152.5°	263.5	274.4	302.3	340.5	354.7
155°	271.7	281.3	302.1	331.8	341.4
157.5°	279.8	287.2	302.1	325.8	333.1
160°	284.5	291.2	302.1	321.9	327.6
162.5°	289.2	294.4	302.9	318.7	322.9
165°	294.3	298.1	303.1	315.9	316.8
167.5°	299.6	301.5	304.1	312.5	313.3
170°	301.2	303.1	304.1	311.0	311.0
172.5°	302.7	303.9	304.1	309.4	309.4
175°	305.1	306.0	304.1	308.0	307.0
177.5°	305.9	305.9	303.5	306.6	305.1
180°	305.1	305.1	305.1	305.1	305.1

(END OF REPORT)