

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565007

Luminaire Tested: **SQ4-PW1-125U-050D-835-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P565007  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-125U-050D-835-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10393.8 lumens  
Efficiency: N/A  
Efficacy: 140.1 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 74.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P565007  
CATALOG NUMBER: SQ4-PW1-125U-050D-835-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P565007

CATALOG NUMBER: SQ4-PW1-125U-050D-835-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	32	31	30	24
2	85	77	72	67	75	69	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22	17
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	53	46	40	58	48	41	36	38	33	30	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	18	16	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6992	6992	6992
5°	7037	6981	6950
10°	6981	6925	6887
15°	6906	6830	6805
20°	6824	6719	6706
25°	6729	6607	6586
30°	6587	6487	6445
35°	6400	6310	6272
40°	6200	6103	6079
45°	5959	5880	5854
50°	5712	5664	5626
55°	5445	5445	5359
60°	5113	5211	5026
65°	4679	4912	4563
70°	4124	4521	4016
75°	3522	4047	3427
80°	2731	3404	2766
85°	1764	2618	2329



TEST NUMBER: P565007

CATALOG NUMBER: SQ4-PW1-125U-050D-835-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	107.0	1.0
10°-20°	302.2	2.9
20°-30°	448.3	4.3
30°-40°	524.5	5.0
40°-50°	522.2	5.0
50°-60°	450.9	4.3
60°-70°	324.6	3.1
70°-80°	170.2	1.6
80°-90°	44.9	0.4
90°-100°	543.4	5.2
100°-110°	1463.8	14.1
110°-120°	1536.2	14.8
120°-130°	1246.6	12.0
130°-140°	977.7	9.4
140°-150°	750.6	7.2
150°-160°	539.7	5.2
160°-170°	329.7	3.2
170°-180°	111.2	1.1
0°-30°	857.5	8.3
0°-40°	1382.0	13.3
0°-60°	2355.1	22.7
0°-90°	2894.8	27.9
90°-120°	3543.5	34.1
90°-150°	6518.4	62.7
90°-180°	7499.0	72.1
0°-180°	10393.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1137	1137	1137	1137	1137	
5°	1140	1127	1131	1128	1126	108
15°	1085	1071	1073	1071	1069	306
25°	992	975	974	968	970	456
35°	852	840	840	832	835	533
45°	685	679	676	674	673	529
55°	508	507	508	501	500	453
65°	322	331	338	324	314	319
75°	148	162	170	159	144	159
85°	25	33	37	35	33	33
90°	3	9	18	19	19	7
95°	83	296	891	456	315	87
105°	271	421	1619	2422	2273	285
115°	478	585	1348	2605	2946	470
125°	653	750	1210	2046	2408	583
135°	786	877	1176	1650	1869	607
145°	909	980	1162	1411	1515	570
155°	1031	1069	1151	1266	1307	475
165°	1119	1132	1156	1202	1208	315
175°	1163	1162	1157	1173	1170	110
180°	1162	1162	1162	1162	1162	

TEST NUMBER: P565007

CATALOG NUMBER: SQ4-PW1-125U-050D-835-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1136.7	1136.7	1136.7	1136.7	1136.7
2.5°	1143.1	1133.7	1136.7	1134.2	1128.7
5°	1139.7	1127.0	1130.7	1127.6	1125.7
7.5°	1128.1	1116.3	1119.1	1115.8	1114.7
10°	1117.7	1105.9	1108.7	1104.6	1102.7
12.5°	1105.7	1093.1	1095.8	1091.8	1090.6
15°	1084.6	1070.9	1072.6	1070.6	1068.6
17.5°	1060.2	1046.3	1046.6	1043.4	1043.0
20°	1042.6	1027.9	1026.5	1022.6	1024.5
22.5°	1023.3	1007.9	1006.5	1001.0	1003.7
25°	991.5	974.8	973.5	967.5	970.5
27.5°	954.6	938.2	938.2	929.9	933.0
30°	927.4	911.7	913.4	903.4	907.4
32.5°	898.5	884.4	885.3	875.4	879.3
35°	852.3	840.5	840.3	832.3	835.3
37.5°	805.0	794.6	793.0	788.4	789.2
40°	772.2	763.3	760.1	757.1	757.1
42.5°	737.7	729.7	726.5	724.3	723.5
45°	685.0	679.2	676.0	674.0	673.0
47.5°	632.9	627.5	624.7	623.3	622.3
50°	596.9	593.0	591.9	588.9	587.9
52.5°	560.8	558.5	557.4	553.6	552.6
55°	507.8	506.8	507.8	500.7	499.7
57.5°	452.5	454.0	457.3	447.8	445.5
60°	415.6	419.5	423.6	412.5	408.6
62.5°	378.0	384.2	390.0	377.2	371.8
65°	321.5	331.3	337.5	324.2	313.5
67.5°	267.0	279.1	286.6	272.3	260.2
70°	229.3	243.1	251.4	237.0	223.3
72.5°	196.5	211.8	218.5	205.0	191.3
75°	148.2	161.9	170.3	158.9	144.2
77.5°	105.2	118.1	125.0	115.1	103.0
80°	77.1	90.8	96.1	87.9	78.1
82.5°	54.7	66.0	69.7	64.7	58.1
85°	25.0	32.9	37.1	35.0	33.0
87.5°	7.0	13.6	18.8	19.1	19.9
90°	3.0	8.7	17.8	19.2	19.2
92.5°	36.1	127.6	252.2	121.4	84.3
95°	82.9	295.6	890.8	455.5	315.2
97.5°	132.3	338.3	1397.2	1167.2	880.2
100°	170.2	355.4	1558.2	1630.3	1352.5
102.5°	206.9	379.3	1611.5	1977.1	1749.1
105°	270.8	421.3	1618.9	2422.0	2272.9
107.5°	331.2	465.4	1549.9	2650.6	2689.1
110°	371.4	498.8	1487.2	2721.5	2861.9



TEST NUMBER: P565007

CATALOG NUMBER: SQ4-PW1-125U-050D-835-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	414.0	532.1	1426.8	2705.8	2936.5
115°	478.0	585.0	1348.1	2604.8	2946.2
117.5°	536.3	636.7	1287.1	2443.5	2823.7
120°	574.2	671.1	1256.3	2327.7	2718.4
122.5°	607.3	703.1	1233.8	2209.3	2598.8
125°	652.6	749.5	1210.5	2045.9	2407.6
127.5°	696.1	791.6	1195.7	1901.8	2224.7
130°	722.1	817.6	1189.7	1819.2	2102.8
132.5°	748.2	842.5	1183.8	1746.4	2006.9
135°	785.8	876.9	1176.4	1650.5	1869.0
137.5°	821.6	909.0	1172.6	1569.1	1748.5
140°	846.4	930.4	1169.0	1519.0	1681.0
142.5°	872.5	950.6	1166.7	1472.2	1608.8
145°	908.6	979.5	1161.6	1411.1	1515.3
147.5°	947.7	1009.3	1156.6	1359.7	1441.6
150°	973.7	1027.2	1154.2	1327.4	1395.4
152.5°	997.4	1044.0	1153.0	1301.1	1356.4
155°	1031.4	1069.0	1151.3	1266.1	1306.6
157.5°	1061.3	1090.5	1151.6	1241.6	1268.8
160°	1080.2	1104.8	1152.7	1227.2	1247.5
162.5°	1096.8	1116.8	1153.9	1215.2	1229.7
165°	1118.7	1131.7	1155.7	1201.7	1207.5
167.5°	1136.5	1144.0	1157.2	1191.3	1193.6
170°	1148.3	1151.2	1157.2	1185.3	1185.3
172.5°	1155.4	1156.0	1158.4	1179.4	1179.4
175°	1163.1	1161.7	1157.2	1173.4	1170.5
177.5°	1166.4	1164.0	1158.1	1167.5	1165.2
180°	1161.6	1161.6	1161.6	1161.6	1161.6

(END OF REPORT)