

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519193

Luminaire Tested: **SQ4-WB-075U-075D-835-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519193
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-075U-075D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8232.6 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 68
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519193
CATALOG NUMBER: SQ4-WB-075U-075D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519193

CATALOG NUMBER: SQ4-WB-075U-075D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	98	94	90	87	90	86	83	81	72	70	68	59	58	57	47	47	46	40
2	90	83	78	73	82	77	72	68	65	61	58	53	51	49	43	42	40	36
3	83	74	67	62	76	69	63	58	58	54	50	48	45	43	39	37	36	31
4	76	66	59	54	70	61	55	50	52	48	44	44	40	38	36	34	32	28
5	70	60	52	47	65	55	49	44	47	42	39	40	36	33	33	30	28	25
6	65	54	47	41	60	50	44	39	43	38	34	36	33	30	30	28	26	23
7	61	49	42	37	56	46	39	35	39	34	31	34	30	27	28	25	23	21
8	56	45	38	33	52	42	36	31	36	31	28	31	27	24	26	23	21	19
9	53	41	34	29	49	39	32	28	34	29	25	29	25	22	24	21	19	17
10	49	38	31	27	46	36	30	25	31	26	23	27	23	20	23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15787	15787	15787
5°	15590	15535	15625
10°	14729	14863	15208
15°	13597	13913	14537
20°	12348	12812	13660
25°	11075	11679	12726
30°	9903	10551	11759
35°	8660	9285	10613
40°	7288	7867	9187
45°	6015	6534	7670
50°	5022	5474	6391
55°	4264	4698	5278
60°	3644	4073	4212
65°	2901	3426	2722
70°	2572	2674	1662
75°	2381	2167	1017
80°	2193	1994	878
85°	1990	1828	713



TEST NUMBER: P519193

CATALOG NUMBER: SQ4-WB-075U-075D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.4	2.9
10°-20°	612.3	7.4
20°-30°	793.2	9.6
30°-40°	776.7	9.4
40°-50°	594.5	7.2
50°-60°	396.2	4.8
60°-70°	216.2	2.6
70°-80°	90.1	1.1
80°-90°	27.3	0.3
90°-100°	325.1	3.9
100°-110°	894.5	10.9
110°-120°	923.3	11.2
120°-130°	739.7	9.0
130°-140°	581.0	7.1
140°-150°	445.2	5.4
150°-160°	320.1	3.9
160°-170°	195.7	2.4
170°-180°	66.0	0.8
0°-30°	1640.9	19.9
0°-40°	2417.7	29.4
0°-60°	3408.4	41.4
0°-90°	3741.9	45.5
90°-120°	2142.9	26.0
90°-150°	3908.8	47.5
90°-180°	4491.0	54.6
0°-180°	8232.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2567	2567	2567	2567	2567	
5°	2525	2500	2516	2522	2531	235
15°	2135	2128	2185	2244	2283	596
25°	1632	1636	1721	1796	1875	750
35°	1153	1159	1237	1320	1413	717
45°	692	705	751	808	882	539
55°	398	414	438	455	492	360
65°	199	216	235	206	187	207
75°	100	100	91	63	43	107
85°	28	28	26	17	10	31
90°	2	6	10	13	13	5
95°	48	178	575	246	157	51
105°	160	246	986	1501	1401	169
115°	283	345	790	1574	1786	279
125°	390	445	717	1213	1421	348
135°	471	522	697	981	1110	363
145°	544	581	686	836	900	341
155°	616	636	682	751	773	283
165°	666	674	685	713	717	188
175°	689	691	686	695	694	65
180°	689	689	689	689	689	

TEST NUMBER: P519193

CATALOG NUMBER: SQ4-WB-075U-075D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2566.7	2566.7	2566.7	2566.7	2566.7
2.5°	2573.0	2550.1	2555.9	2555.7	2548.7
5°	2525.0	2499.7	2516.0	2521.8	2530.6
7.5°	2431.3	2412.1	2441.9	2463.9	2481.8
10°	2358.3	2341.8	2379.7	2411.8	2434.9
12.5°	2273.6	2259.8	2306.7	2349.8	2379.9
15°	2135.3	2127.6	2184.9	2244.3	2282.9
17.5°	1987.3	1983.6	2049.3	2118.7	2168.0
20°	1886.4	1885.3	1957.4	2029.6	2086.9
22.5°	1784.6	1787.0	1862.8	1937.9	2003.1
25°	1631.9	1636.3	1720.9	1795.9	1875.2
27.5°	1490.7	1492.7	1580.1	1659.3	1743.9
30°	1394.3	1399.8	1485.5	1567.5	1655.6
32.5°	1297.9	1304.3	1388.2	1472.9	1562.8
35°	1153.3	1158.8	1236.6	1319.8	1413.4
37.5°	1004.1	1011.6	1080.7	1159.4	1251.5
40°	907.7	918.8	979.8	1053.9	1144.2
42.5°	814.9	828.6	885.2	955.5	1037.0
45°	691.5	704.7	751.2	808.1	881.8
47.5°	585.2	600.4	636.1	685.1	748.0
50°	524.8	539.1	572.1	608.4	667.9
52.5°	471.7	486.0	515.4	543.3	594.0
55°	397.6	414.1	438.1	454.7	492.2
57.5°	336.7	352.6	371.7	379.2	401.8
60°	296.2	313.8	331.1	330.3	342.4
62.5°	259.3	274.2	291.5	279.5	280.2
65°	199.3	215.9	235.4	205.7	187.0
67.5°	161.1	164.6	184.7	143.4	121.2
70°	143.0	143.0	148.7	111.1	92.4
72.5°	125.9	125.9	120.7	90.3	70.7
75°	100.2	100.2	91.2	62.6	42.8
77.5°	77.3	76.4	69.8	46.7	31.1
80°	61.9	61.9	56.3	36.9	24.8
82.5°	48.4	48.4	43.7	28.8	18.5
85°	28.2	28.2	25.9	16.7	10.1
87.5°	10.2	11.1	11.1	8.0	7.1
90°	1.5	5.8	10.3	13.2	13.2
92.5°	20.2	86.5	149.9	57.6	47.2
95°	48.4	177.5	574.9	245.8	156.9
97.5°	78.9	196.8	877.3	676.0	477.0
100°	101.2	208.8	972.4	981.5	800.8
102.5°	122.3	223.0	997.0	1217.7	1051.9
105°	159.9	245.9	985.6	1501.0	1400.6
107.5°	195.7	274.2	929.6	1639.8	1669.6
110°	221.5	293.2	887.3	1674.3	1777.6

TEST NUMBER: P519193

CATALOG NUMBER: SQ4-WB-075U-075D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	244.9	314.3	845.1	1652.1	1809.3
115°	283.1	344.7	790.5	1574.1	1786.4
117.5°	319.4	376.2	755.9	1464.8	1704.8
120°	341.7	396.2	740.7	1382.8	1630.9
122.5°	361.7	416.2	730.1	1311.0	1546.4
125°	390.1	444.6	717.2	1213.2	1421.2
127.5°	417.1	469.0	708.7	1131.7	1314.1
130°	431.2	484.3	704.0	1083.2	1249.6
132.5°	447.6	500.7	700.5	1040.6	1190.9
135°	470.8	522.4	696.7	981.2	1110.3
137.5°	492.5	540.4	693.4	933.2	1039.6
140°	508.9	553.4	692.3	901.2	997.3
142.5°	523.0	564.0	689.9	872.8	955.1
145°	544.1	581.4	686.4	836.0	900.5
147.5°	566.7	598.8	684.6	803.4	855.1
150°	580.8	609.5	683.5	785.6	825.7
152.5°	593.7	620.1	682.3	770.2	803.4
155°	616.0	636.1	682.0	751.4	772.9
157.5°	632.1	648.5	682.0	736.0	750.9
160°	643.9	656.8	682.0	727.7	739.2
162.5°	653.2	663.9	683.2	720.6	729.8
165°	665.9	674.5	684.9	712.9	717.2
167.5°	674.7	681.3	686.4	706.4	707.5
170°	680.5	684.8	686.4	704.0	704.0
172.5°	685.2	687.2	686.4	700.4	699.3
175°	689.3	690.8	686.4	695.2	693.7
177.5°	690.5	690.5	685.8	692.8	690.5
180°	689.3	689.3	689.3	689.3	689.3

(END OF REPORT)