

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563782

Luminaire Tested: **SQ4-PP3-150U-075D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563782
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-075D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8899.0 lumens
Efficiency: N/A
Efficacy: 140.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 63.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563782
CATALOG NUMBER: SQ4-PP3-150U-075D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563782

CATALOG NUMBER: SQ4-PP3-150U-075D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	25	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10356	10356	10356
5°	10433	10369	10333
10°	10415	10342	10295
15°	10346	10290	10234
20°	10278	10220	10142
25°	10156	10085	9986
30°	9967	9915	9790
35°	9707	9640	9518
40°	9397	9338	9230
45°	9140	9076	8986
50°	8812	8756	8671
55°	8356	8245	8181
60°	7606	7388	7353
65°	6702	6423	6401
70°	5786	5546	5546
75°	4980	4909	4841
80°	4389	4442	4341
85°	3440	3747	3747



TEST NUMBER: P563782

CATALOG NUMBER: SQ4-PP3-150U-075D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.1	1.2
10°-20°	303.1	3.4
20°-30°	454.0	5.1
30°-40°	532.5	6.0
40°-50°	534.2	6.0
50°-60°	455.7	5.1
60°-70°	297.2	3.3
70°-80°	149.1	1.7
80°-90°	43.2	0.5
90°-100°	434.2	4.9
100°-110°	1174.0	13.2
110°-120°	1234.3	13.9
120°-130°	1002.6	11.3
130°-140°	786.5	8.8
140°-150°	603.6	6.8
150°-160°	434.1	4.9
160°-170°	265.2	3.0
170°-180°	89.4	1.0
0°-30°	863.2	9.7
0°-40°	1395.7	15.7
0°-60°	2385.6	26.8
0°-90°	2875.1	32.3
90°-120°	2842.6	31.9
90°-150°	5235.3	58.8
90°-180°	6024.0	67.7
0°-180°	8899.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1122	1122	1122	1122	1122	
5°	1126	1116	1120	1116	1116	107
15°	1083	1073	1077	1073	1071	306
25°	998	986	991	982	981	459
35°	862	853	856	846	845	538
45°	700	696	696	689	689	539
55°	520	518	513	510	509	462
65°	307	301	294	292	293	306
75°	140	140	138	137	136	152
85°	32	35	35	35	35	38
90°	2	6	13	14	13	6
95°	67	236	722	374	222	71
105°	218	337	1302	1921	1842	230
115°	384	470	1080	2091	2360	379
125°	526	603	974	1643	1930	469
135°	631	705	947	1326	1502	487
145°	733	788	934	1135	1222	459
155°	828	860	926	1019	1052	382
165°	901	910	930	967	972	254
175°	935	934	931	943	941	89
180°	934	934	934	934	934	

TEST NUMBER: P563782

CATALOG NUMBER: SQ4-PP3-150U-075D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1122.5	1122.5	1122.5	1122.5	1122.5
2.5°	1129.6	1120.4	1122.5	1120.9	1116.3
5°	1126.5	1115.9	1119.6	1115.7	1115.7
7.5°	1118.8	1107.3	1110.9	1107.0	1106.8
10°	1111.7	1100.2	1103.9	1099.9	1098.9
12.5°	1101.5	1090.0	1094.4	1089.7	1089.5
15°	1083.2	1072.6	1077.3	1073.3	1071.4
17.5°	1062.5	1051.0	1056.6	1051.1	1050.3
20°	1046.8	1035.3	1040.9	1033.0	1033.0
22.5°	1027.9	1016.4	1022.8	1012.6	1012.6
25°	997.6	986.1	990.7	981.8	980.9
27.5°	961.6	950.2	955.1	945.1	944.9
30°	935.6	925.0	930.7	919.9	918.9
32.5°	907.3	897.5	901.6	890.7	889.8
35°	861.8	853.2	855.9	846.1	845.1
37.5°	814.0	805.2	808.3	799.8	799.5
40°	780.2	774.4	775.3	768.3	766.4
42.5°	748.7	742.2	743.0	736.1	735.7
45°	700.5	695.7	695.6	688.7	688.7
47.5°	649.3	645.7	644.6	638.9	638.7
50°	613.9	611.0	610.0	605.0	604.1
52.5°	576.9	575.6	572.2	568.1	567.9
55°	519.5	517.5	512.6	509.6	508.6
57.5°	457.1	453.2	447.6	443.3	444.1
60°	412.2	408.4	400.4	398.5	398.5
62.5°	368.9	364.3	356.3	353.6	355.2
65°	307.0	301.2	294.2	292.2	293.2
67.5°	250.7	245.5	237.9	237.9	237.1
70°	214.5	211.6	205.6	205.6	205.6
72.5°	182.2	180.9	176.5	176.5	175.7
75°	139.7	139.7	137.7	136.7	135.8
77.5°	104.7	105.1	104.1	103.1	101.3
80°	82.6	84.6	83.6	82.6	81.7
82.5°	62.2	64.1	63.9	62.2	62.0
85°	32.5	35.4	35.4	35.4	35.4
87.5°	9.1	12.9	15.2	15.4	16.0
90°	2.0	5.9	13.1	14.1	13.1
92.5°	28.6	104.1	205.4	89.2	64.6
95°	67.4	236.5	722.1	373.7	222.3
97.5°	108.2	271.3	1125.6	931.5	684.1
100°	138.8	285.3	1251.1	1304.8	1055.0
102.5°	167.0	304.8	1295.4	1587.8	1401.0
105°	218.2	337.2	1302.4	1921.2	1842.5
107.5°	265.7	374.3	1245.5	2129.1	2155.3
110°	302.7	401.1	1194.8	2185.0	2296.1



TEST NUMBER: P563782

CATALOG NUMBER: SQ4-PP3-150U-075D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	335.7	427.8	1148.1	2173.8	2360.5
115°	384.2	469.7	1080.2	2091.0	2360.5
117.5°	431.7	511.9	1035.3	1964.5	2269.9
120°	460.6	539.3	1008.8	1873.7	2185.5
122.5°	488.0	565.1	992.7	1776.4	2090.5
125°	526.0	602.7	973.6	1642.9	1930.0
127.5°	561.0	636.3	962.3	1533.9	1786.4
130°	580.3	658.0	957.5	1466.5	1694.7
132.5°	600.4	677.3	952.6	1405.8	1615.8
135°	630.6	705.3	947.4	1326.5	1501.6
137.5°	661.0	731.6	943.0	1262.2	1404.8
140°	681.9	747.8	941.4	1220.8	1347.7
142.5°	702.0	764.0	938.1	1183.5	1294.6
145°	733.2	788.2	934.3	1135.4	1222.0
147.5°	761.5	810.3	929.9	1091.9	1158.4
150°	782.5	825.7	928.3	1068.3	1121.4
152.5°	801.8	839.5	927.5	1046.4	1090.0
155°	827.7	860.2	926.3	1018.6	1052.0
157.5°	854.7	877.3	926.5	999.2	1021.2
160°	870.0	888.6	927.3	987.0	1002.7
162.5°	882.0	897.6	928.1	977.2	989.0
165°	901.1	910.0	930.3	966.6	971.5
167.5°	914.2	920.3	930.5	957.5	959.9
170°	922.3	925.2	931.3	953.4	953.4
172.5°	928.7	929.3	931.3	948.6	947.8
175°	935.3	934.3	931.3	943.3	941.4
177.5°	937.5	935.2	931.1	939.1	936.7
180°	934.3	934.3	934.3	934.3	934.3

(END OF REPORT)