

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564022

Luminaire Tested: **SQ4-PR1-050U-125D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564022
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6835.9 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564022
CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564022

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	75	75	75	71	
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	64	64	64	60	
2	94	87	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55	55	55	55	51	
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	47	47	47	44	
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	41	41	41	38	
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	36	36	36	33	
6	67	55	47	41	63	52	45	39	48	41	37	43	38	34	39	35	32	32	32	32	29	
7	62	50	42	36	59	48	40	35	43	37	33	40	34	30	36	32	28	28	28	28	26	
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	25	25	25	25	23	
9	54	41	34	29	51	40	33	28	37	30	26	33	28	25	31	26	23	23	23	23	21	
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	21	21	21	19	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17873	17873	17873
5°	18034	17895	17802
10°	17977	17852	17758
15°	17898	17786	17691
20°	17807	17694	17562
25°	17683	17564	17360
30°	17492	17367	17118
35°	17234	17083	16838
40°	16841	16659	16358
45°	16155	15871	15545
50°	14945	14586	14297
55°	13044	12749	12481
60°	10992	10900	10684
65°	9507	9545	9470
70°	8732	8778	8778
75°	8388	8388	8445
80°	7890	7980	7890
85°	6362	7061	7061



TEST NUMBER: P564022

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.2	2.7
10°-20°	524.1	7.7
20°-30°	790.6	11.6
30°-40°	941.9	13.8
40°-50°	928.7	13.6
50°-60°	709.8	10.4
60°-70°	439.2	6.4
70°-80°	249.5	3.6
80°-90°	77.0	1.1
90°-100°	146.4	2.1
100°-110°	397.8	5.8
110°-120°	409.0	6.0
120°-130°	327.0	4.8
130°-140°	257.0	3.8
140°-150°	197.0	2.9
150°-160°	141.7	2.1
160°-170°	86.7	1.3
170°-180°	29.2	0.4
0°-30°	1497.9	21.9
0°-40°	2439.8	35.7
0°-60°	4078.3	59.7
0°-90°	4844.0	70.9
90°-120°	953.3	13.9
90°-150°	1734.4	25.4
90°-180°	1992.0	29.1
0°-180°	6835.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1937	1937	1937	1937	1937	
5°	1947	1926	1932	1926	1922	185
15°	1874	1854	1862	1855	1852	529
25°	1737	1716	1725	1707	1705	799
35°	1530	1512	1517	1497	1495	955
45°	1238	1222	1216	1195	1191	949
55°	811	798	793	779	776	727
65°	436	432	437	434	434	441
75°	235	235	235	237	237	248
85°	60	63	67	67	67	70
90°	1	4	7	9	9	4
95°	22	80	255	111	75	23
105°	71	110	438	666	627	75
115°	126	152	350	697	794	124
125°	173	197	317	534	630	154
135°	208	231	308	435	490	161
145°	240	258	304	370	397	151
155°	272	281	302	332	341	125
165°	294	298	303	316	317	83
175°	305	306	304	308	307	29
180°	305	305	305	305	305	



TEST NUMBER: P564022

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1937.2	1937.2	1937.2	1937.2	1937.2
2.5°	1949.2	1932.3	1937.2	1933.0	1923.9
5°	1947.2	1926.0	1932.2	1925.5	1922.2
7.5°	1932.2	1911.3	1917.5	1910.8	1908.8
10°	1918.9	1899.3	1905.5	1898.8	1895.5
12.5°	1904.2	1883.3	1890.8	1882.7	1879.5
15°	1873.8	1854.2	1862.1	1855.4	1852.1
17.5°	1840.4	1819.6	1827.4	1819.7	1815.4
20°	1813.7	1794.2	1802.1	1790.3	1788.7
22.5°	1784.4	1764.8	1772.7	1757.0	1756.7
25°	1737.0	1715.8	1725.3	1706.9	1705.3
27.5°	1680.6	1661.0	1668.9	1650.2	1648.2
30°	1641.9	1622.3	1630.2	1610.1	1606.8
32.5°	1597.8	1579.6	1586.1	1566.1	1564.1
35°	1530.1	1512.1	1516.7	1496.7	1495.0
37.5°	1453.0	1436.7	1439.3	1417.3	1415.6
40°	1398.3	1382.0	1383.2	1359.9	1358.2
42.5°	1338.2	1321.9	1320.5	1297.1	1295.5
45°	1238.1	1221.8	1216.4	1194.6	1191.4
47.5°	1124.0	1107.6	1097.6	1079.8	1077.6
50°	1041.2	1024.9	1016.2	1001.0	996.1
52.5°	951.8	935.4	928.1	914.3	909.4
55°	810.9	797.9	792.6	779.2	775.9
57.5°	677.1	668.3	666.8	653.7	652.4
60°	595.7	590.8	590.7	579.0	579.0
62.5°	526.3	522.7	525.3	517.6	516.3
65°	435.5	432.2	437.2	433.8	433.8
67.5°	363.7	363.7	366.8	365.4	365.4
70°	323.7	323.7	325.4	325.4	325.4
72.5°	287.7	286.4	290.7	290.6	289.3
75°	235.3	235.3	235.3	236.9	236.9
77.5°	183.2	183.5	184.9	184.5	183.2
80°	148.5	150.1	150.2	148.5	148.5
82.5°	113.8	115.4	115.5	115.1	113.8
85°	60.1	63.3	66.7	66.7	66.7
87.5°	17.5	23.3	28.1	28.4	27.1
90°	1.0	3.9	6.9	8.8	8.8
92.5°	8.8	40.1	69.6	29.9	25.3
95°	21.6	80.1	255.0	111.0	74.6
97.5°	35.7	88.5	391.0	304.2	213.7
100°	45.1	94.0	432.6	438.5	354.1
102.5°	54.5	99.6	443.6	542.3	467.9
105°	70.6	110.0	437.5	666.1	626.8
107.5°	87.3	122.0	412.2	730.1	741.0
110°	99.1	130.7	393.4	742.7	789.7



TEST NUMBER: P564022

CATALOG NUMBER: SQ4-PR1-050U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.3	139.4	374.5	732.2	803.0
115°	125.6	152.4	350.2	696.7	793.6
117.5°	140.9	166.6	334.7	646.4	755.5
120°	151.1	176.0	327.6	612.6	721.0
122.5°	159.7	184.6	322.9	578.8	683.3
125°	172.6	196.6	316.8	533.9	629.8
127.5°	184.2	208.0	313.5	499.8	582.1
130°	191.3	214.3	311.9	478.4	552.3
132.5°	198.3	221.4	310.4	460.2	525.6
135°	208.0	231.0	308.0	434.8	490.5
137.5°	218.4	239.3	306.8	412.5	459.3
140°	224.6	244.8	306.1	398.2	440.4
142.5°	230.9	249.5	305.3	387.1	422.4
145°	240.3	257.6	304.1	369.5	397.3
147.5°	250.9	265.7	303.1	355.6	377.5
150°	258.0	270.5	303.1	347.6	364.9
152.5°	263.5	274.4	302.3	340.5	354.7
155°	271.7	281.3	302.1	331.8	341.4
157.5°	279.8	287.2	302.1	325.8	333.1
160°	284.5	291.2	302.1	321.9	327.6
162.5°	289.2	294.4	302.9	318.7	322.9
165°	294.3	298.1	303.1	315.9	316.8
167.5°	299.6	301.5	304.1	312.5	313.3
170°	301.2	303.1	304.1	311.0	311.0
172.5°	302.7	303.9	304.1	309.4	309.4
175°	305.1	306.0	304.1	308.0	307.0
177.5°	305.9	305.9	303.5	306.6	305.1
180°	305.1	305.1	305.1	305.1	305.1

(END OF REPORT)