

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519529

Luminaire Tested: **SQ4-WB-125U-125D-835-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519529
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-125D-835-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13659.1 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 117.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519529
CATALOG NUMBER: SQ4-WB-125U-125D-835-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519529

CATALOG NUMBER: SQ4-WB-125U-125D-835-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	98	94	90	87	90	86	83	81	72	70	68	59	58	57	47	46	46	40
2	90	83	78	73	82	77	72	68	64	61	58	53	51	49	43	41	40	35
3	83	74	67	62	76	68	63	58	58	54	50	48	45	43	39	37	35	31
4	76	66	59	54	70	61	55	50	52	47	44	44	40	38	36	33	31	28
5	70	60	52	47	65	55	49	44	47	42	39	40	36	33	33	30	28	25
6	65	54	46	41	60	50	44	39	43	38	34	36	33	30	30	27	25	23
7	61	49	42	36	56	46	39	34	39	34	31	33	30	27	28	25	23	20
8	56	45	38	33	52	42	35	31	36	31	28	31	27	24	26	23	21	19
9	53	41	34	29	49	39	32	28	33	28	25	29	25	22	24	21	19	17
10	49	38	31	27	46	36	29	25	31	26	23	27	23	20	22	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25991	25991	25991
5°	25667	25575	25723
10°	24250	24469	25036
15°	22385	22905	23932
20°	20329	21093	22489
25°	18233	19227	20951
30°	16303	17369	19358
35°	14256	15286	17472
40°	11999	12952	15126
45°	9902	10757	12629
50°	8268	9013	10521
55°	7019	7735	8689
60°	5998	6706	6934
65°	4777	5640	4480
70°	4235	4401	2734
75°	3921	3569	1675
80°	3613	3284	1445
85°	3275	3006	1179



TEST NUMBER: P519529

CATALOG NUMBER: SQ4-WB-125U-125D-835-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.6	2.8
10°-20°	1008.1	7.4
20°-30°	1305.8	9.6
30°-40°	1278.7	9.4
40°-50°	978.8	7.2
50°-60°	652.2	4.8
60°-70°	355.9	2.6
70°-80°	148.3	1.1
80°-90°	44.7	0.3
90°-100°	543.4	4.0
100°-110°	1463.8	10.7
110°-120°	1536.2	11.2
120°-130°	1246.6	9.1
130°-140°	977.7	7.2
140°-150°	750.6	5.5
150°-160°	539.7	4.0
160°-170°	329.7	2.4
170°-180°	111.2	0.8
0°-30°	2701.5	19.8
0°-40°	3980.2	29.1
0°-60°	5611.2	41.1
0°-90°	6160.1	45.1
90°-120°	3543.5	25.9
90°-150°	6518.4	47.7
90°-180°	7499.0	54.9
0°-180°	13659.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4226	4226	4226	4226	4226	
5°	4157	4115	4142	4152	4166	387
15°	3515	3503	3597	3695	3758	982
25°	2687	2694	2833	2957	3087	1236
35°	1899	1908	2036	2173	2327	1180
45°	1138	1160	1237	1330	1452	888
55°	654	682	721	749	810	593
65°	328	355	388	339	308	341
75°	165	165	150	103	70	176
85°	46	46	43	28	17	50
90°	3	9	18	19	19	8
95°	83	296	891	456	315	87
105°	271	421	1619	2422	2273	285
115°	478	585	1348	2605	2946	470
125°	653	750	1210	2046	2408	583
135°	786	877	1176	1650	1869	607
145°	909	980	1162	1411	1515	570
155°	1031	1069	1151	1266	1307	475
165°	1119	1132	1156	1202	1208	315
175°	1163	1162	1157	1173	1170	110
180°	1162	1162	1162	1162	1162	

TEST NUMBER: P519529

CATALOG NUMBER: SQ4-WB-125U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4225.6	4225.6	4225.6	4225.6	4225.6
2.5°	4236.0	4198.2	4207.8	4207.5	4195.9
5°	4157.0	4115.3	4142.1	4151.7	4166.2
7.5°	4002.7	3971.2	4020.1	4056.4	4085.8
10°	3882.6	3855.4	3917.8	3970.6	4008.6
12.5°	3743.1	3720.3	3797.6	3868.5	3918.2
15°	3515.4	3502.7	3597.0	3694.9	3758.3
17.5°	3271.8	3265.6	3373.8	3488.0	3569.2
20°	3105.7	3103.9	3222.5	3341.4	3435.7
22.5°	2938.1	2942.0	3066.7	3190.4	3297.8
25°	2686.6	2693.9	2833.1	2956.6	3087.1
27.5°	2454.1	2457.4	2601.3	2731.7	2870.9
30°	2295.4	2304.5	2445.6	2580.5	2725.6
32.5°	2136.7	2147.2	2285.4	2424.9	2572.8
35°	1898.6	1907.7	2035.8	2172.8	2326.9
37.5°	1653.1	1665.5	1779.2	1908.8	2060.3
40°	1494.4	1512.6	1613.1	1735.1	1883.8
42.5°	1341.7	1364.1	1457.3	1573.1	1707.3
45°	1138.4	1160.2	1236.7	1330.3	1451.8
47.5°	963.4	988.4	1047.2	1127.8	1231.5
50°	864.0	887.6	941.9	1001.6	1099.5
52.5°	776.5	800.1	848.5	894.5	977.9
55°	654.5	681.7	721.3	748.6	810.3
57.5°	554.4	580.5	611.9	624.2	661.6
60°	487.6	516.6	545.1	543.7	563.7
62.5°	426.8	451.5	479.8	460.2	461.3
65°	328.2	355.4	387.5	338.6	307.8
67.5°	265.1	270.9	304.1	236.1	199.5
70°	235.5	235.5	244.7	182.9	152.0
72.5°	207.3	207.3	198.8	148.7	116.4
75°	165.0	165.0	150.2	103.1	70.5
77.5°	127.2	125.7	115.0	76.9	51.2
80°	102.0	102.0	92.7	60.7	40.8
82.5°	79.7	79.7	71.9	47.4	30.4
85°	46.4	46.4	42.6	27.6	16.7
87.5°	16.9	18.1	18.4	12.7	11.3
90°	3.0	8.7	17.8	19.2	19.2
92.5°	36.1	127.6	252.2	121.4	84.3
95°	82.9	295.6	890.8	455.5	315.2
97.5°	132.3	338.3	1397.2	1167.2	880.2
100°	170.2	355.4	1558.2	1630.3	1352.5
102.5°	206.9	379.3	1611.5	1977.1	1749.1
105°	270.8	421.3	1618.9	2422.0	2272.9
107.5°	331.2	465.4	1549.9	2650.6	2689.1
110°	371.4	498.8	1487.2	2721.5	2861.9

TEST NUMBER: P519529

CATALOG NUMBER: SQ4-WB-125U-125D-835-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	414.0	532.1	1426.8	2705.8	2936.5
115°	478.0	585.0	1348.1	2604.8	2946.2
117.5°	536.3	636.7	1287.1	2443.5	2823.7
120°	574.2	671.1	1256.3	2327.7	2718.4
122.5°	607.3	703.1	1233.8	2209.3	2598.8
125°	652.6	749.5	1210.5	2045.9	2407.6
127.5°	696.1	791.6	1195.7	1901.8	2224.7
130°	722.1	817.6	1189.7	1819.2	2102.8
132.5°	748.2	842.5	1183.8	1746.4	2006.9
135°	785.8	876.9	1176.4	1650.5	1869.0
137.5°	821.6	909.0	1172.6	1569.1	1748.5
140°	846.4	930.4	1169.0	1519.0	1681.0
142.5°	872.5	950.6	1166.7	1472.2	1608.8
145°	908.6	979.5	1161.6	1411.1	1515.3
147.5°	947.7	1009.3	1156.6	1359.7	1441.6
150°	973.7	1027.2	1154.2	1327.4	1395.4
152.5°	997.4	1044.0	1153.0	1301.1	1356.4
155°	1031.4	1069.0	1151.3	1266.1	1306.6
157.5°	1061.3	1090.5	1151.6	1241.6	1268.8
160°	1080.2	1104.8	1152.7	1227.2	1247.5
162.5°	1096.8	1116.8	1153.9	1215.2	1229.7
165°	1118.7	1131.7	1155.7	1201.7	1207.5
167.5°	1136.5	1144.0	1157.2	1191.3	1193.6
170°	1148.3	1151.2	1157.2	1185.3	1185.3
172.5°	1155.4	1156.0	1158.4	1179.4	1179.4
175°	1163.1	1161.7	1157.2	1173.4	1170.5
177.5°	1166.4	1164.0	1158.1	1167.5	1165.2
180°	1161.6	1161.6	1161.6	1161.6	1161.6

(END OF REPORT)