

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564046

Luminaire Tested: **SQ4-PR1-075U-050D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564046  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-075U-050D-835-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4932.8 lumens  
Efficiency: N/A  
Efficacy: 142.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 34.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564046  
CATALOG NUMBER: SQ4-PR1-075U-050D-835-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564046

CATALOG NUMBER: SQ4-PR1-075U-050D-835-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	28
3	80	71	63	58	72	64	58	53	53	49	45	42	39	37	33	31	29	24
4	73	63	55	49	66	57	51	45	47	42	38	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	22	18	22	18	15	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7152	7152	7152
5°	7217	7161	7123
10°	7193	7144	7106
15°	7162	7117	7079
20°	7126	7080	7027
25°	7075	7028	6947
30°	6999	6949	6850
35°	6895	6836	6738
40°	6739	6666	6546
45°	6464	6350	6220
50°	5980	5836	5721
55°	5220	5101	4995
60°	4399	4362	4275
65°	3805	3818	3790
70°	3493	3512	3512
75°	3354	3354	3379
80°	3156	3193	3156
85°	2541	2826	2826



TEST NUMBER: P564046

CATALOG NUMBER: SQ4-PR1-075U-050D-835-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.3	1.5
10°-20°	209.7	4.3
20°-30°	316.3	6.4
30°-40°	376.9	7.6
40°-50°	371.6	7.5
50°-60°	284.0	5.8
60°-70°	175.8	3.6
70°-80°	99.8	2.0
80°-90°	31.5	0.6
90°-100°	216.8	4.4
100°-110°	596.3	12.1
110°-120°	615.5	12.5
120°-130°	493.1	10.0
130°-140°	387.3	7.9
140°-150°	296.8	6.0
150°-160°	213.4	4.3
160°-170°	130.5	2.6
170°-180°	44.0	0.9
0°-30°	599.4	12.2
0°-40°	976.3	19.8
0°-60°	1631.9	33.1
0°-90°	1939.0	39.3
90°-120°	1428.6	29.0
90°-150°	2605.9	52.8
90°-180°	2994.0	60.7
0°-180°	4932.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	775	775	775	775	775	
5°	779	771	773	770	769	74
15°	750	742	745	742	741	212
25°	695	687	690	683	682	320
35°	612	605	607	599	598	382
45°	495	489	487	478	477	380
55°	324	319	317	312	310	291
65°	174	173	175	174	174	177
75°	94	94	94	95	95	99
85°	24	25	27	27	27	28
90°	1	4	7	9	9	3
95°	32	118	383	164	105	34
105°	107	164	657	1001	934	112
115°	189	230	527	1049	1191	186
125°	260	296	478	809	948	232
135°	314	348	464	654	740	242
145°	363	388	458	557	600	227
155°	411	424	455	501	515	189
165°	444	450	457	475	478	125
175°	460	460	458	463	462	44
180°	460	460	460	460	460	

TEST NUMBER: P564046

CATALOG NUMBER: SQ4-PR1-075U-050D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	775.2	775.2	775.2	775.2	775.2
2.5°	780.0	773.2	775.2	773.5	769.8
5°	779.2	770.7	773.2	770.5	769.1
7.5°	773.2	764.8	767.3	764.6	763.8
10°	767.8	760.0	762.5	759.8	758.5
12.5°	761.9	753.6	756.6	753.4	752.1
15°	749.8	742.0	745.1	742.4	741.1
17.5°	736.4	728.1	731.2	728.1	726.4
20°	725.8	717.9	721.1	716.4	715.7
22.5°	714.0	706.2	709.3	703.0	702.9
25°	695.0	686.6	690.4	683.0	682.4
27.5°	672.5	664.6	667.8	660.3	659.5
30°	657.0	649.1	652.3	644.3	643.0
32.5°	639.4	632.0	634.7	626.7	625.9
35°	612.2	605.1	606.9	598.9	598.2
37.5°	581.4	574.9	575.9	567.1	566.4
40°	559.5	553.0	553.5	544.1	543.5
42.5°	535.5	528.9	528.4	519.0	518.4
45°	495.4	488.9	486.7	478.0	476.7
47.5°	449.7	443.2	439.2	432.1	431.2
50°	416.6	410.1	406.6	400.6	398.6
52.5°	380.8	374.3	371.4	365.8	363.9
55°	324.5	319.3	317.1	311.8	310.5
57.5°	270.9	267.4	266.8	261.6	261.1
60°	238.4	236.4	236.4	231.7	231.7
62.5°	210.6	209.1	210.2	207.1	206.6
65°	174.3	173.0	174.9	173.6	173.6
67.5°	145.6	145.6	146.8	146.2	146.2
70°	129.5	129.5	130.2	130.2	130.2
72.5°	115.1	114.6	116.3	116.3	115.8
75°	94.1	94.1	94.1	94.8	94.8
77.5°	73.3	73.4	74.0	73.8	73.3
80°	59.4	60.1	60.1	59.4	59.4
82.5°	45.5	46.2	46.2	46.1	45.5
85°	24.0	25.3	26.7	26.7	26.7
87.5°	7.1	9.8	12.1	12.4	11.9
90°	1.0	3.8	6.8	8.8	8.8
92.5°	13.5	57.7	99.9	38.4	31.5
95°	32.3	118.3	383.3	163.9	104.6
97.5°	52.6	131.2	584.9	450.7	318.0
100°	67.5	139.2	648.3	654.3	533.9
102.5°	81.5	148.7	664.7	811.8	701.3
105°	106.6	163.9	657.1	1000.7	933.8
107.5°	130.4	182.8	619.7	1093.2	1113.1
110°	147.6	195.4	591.5	1116.2	1185.1



TEST NUMBER: P564046

CATALOG NUMBER: SQ4-PR1-075U-050D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	163.3	209.6	563.4	1101.4	1206.2
115°	188.7	229.8	527.0	1049.4	1190.9
117.5°	213.0	250.8	503.9	976.5	1136.6
120°	227.8	264.1	493.8	921.9	1087.3
122.5°	241.1	277.4	486.7	874.0	1031.0
125°	260.1	296.4	478.1	808.8	947.5
127.5°	278.1	312.7	472.5	754.5	876.1
130°	287.5	322.8	469.3	722.2	833.1
132.5°	298.4	333.8	467.0	693.8	793.9
135°	313.9	348.3	464.4	654.1	740.2
137.5°	328.3	360.3	462.3	622.1	693.0
140°	339.3	368.9	461.5	600.8	664.9
142.5°	348.7	376.0	459.9	581.8	636.7
145°	362.8	387.6	457.6	557.3	600.3
147.5°	377.8	399.2	456.4	535.6	570.0
150°	387.2	406.3	455.6	523.7	550.5
152.5°	395.8	413.4	454.9	513.4	535.6
155°	410.7	424.0	454.7	500.9	515.3
157.5°	421.4	432.3	454.7	490.7	500.6
160°	429.2	437.8	454.7	485.1	492.8
162.5°	435.5	442.6	455.4	480.4	486.5
165°	443.9	449.6	456.6	475.3	478.1
167.5°	449.8	454.2	457.6	470.9	471.7
170°	453.7	456.6	457.6	469.3	469.3
172.5°	456.8	458.2	457.6	467.0	466.2
175°	459.5	460.5	457.6	463.4	462.5
177.5°	460.3	460.3	457.2	461.9	460.3
180°	459.5	459.5	459.5	459.5	459.5

(END OF REPORT)