

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564190

Luminaire Tested: **SQ4-PR1-0U-100D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564190
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-0U-100D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3794.9 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564190
CATALOG NUMBER: SQ4-PR1-0U-100D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564190

CATALOG NUMBER: SQ4-PR1-0U-100D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85			85																
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72			72																
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62			62																
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54			54																
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47			47																
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41			41																
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37			37																
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33			33																
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30			30																
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27			27																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14005	14005	14005
5°	14132	14023	13951
10°	14087	13989	13915
15°	14025	13938	13863
20°	13955	13864	13762
25°	13856	13763	13604
30°	13707	13610	13414
35°	13504	13386	13195
40°	13197	13054	12818
45°	12659	12437	12181
50°	11711	11430	11204
55°	10222	9991	9780
60°	8614	8542	8372
65°	7451	7479	7423
70°	6844	6879	6879
75°	6573	6573	6620
80°	6185	6254	6185
85°	4986	5536	5536



TEST NUMBER: P564190

CATALOG NUMBER: SQ4-PR1-0U-100D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.6	3.8
10°-20°	410.7	10.8
20°-30°	619.5	16.3
30°-40°	738.1	19.5
40°-50°	727.7	19.2
50°-60°	556.2	14.7
60°-70°	344.2	9.1
70°-80°	195.5	5.2
80°-90°	59.5	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1173.8	30.9
0°-40°	1911.9	50.4
0°-60°	3195.8	84.2
0°-90°	3794.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3794.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1518	1518	1518	1518	1518	
5°	1526	1509	1514	1509	1506	145
15°	1468	1453	1459	1454	1451	414
25°	1361	1344	1352	1338	1336	626
35°	1199	1185	1188	1173	1172	748
45°	970	957	953	936	934	743
55°	636	625	621	611	608	569
65°	341	339	343	340	340	346
75°	184	184	184	186	186	195
85°	47	50	52	52	52	57
90°	0	0	0	0	0	



TEST NUMBER: P564190

CATALOG NUMBER: SQ4-PR1-0U-100D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1518.0	1518.0	1518.0	1518.0	1518.0
2.5°	1527.4	1514.2	1518.0	1514.7	1507.6
5°	1525.9	1509.3	1514.1	1508.8	1506.3
7.5°	1514.1	1497.7	1502.6	1497.3	1495.8
10°	1503.7	1488.3	1493.2	1487.9	1485.3
12.5°	1492.1	1475.8	1481.7	1475.4	1472.8
15°	1468.3	1453.0	1459.2	1453.9	1451.4
17.5°	1442.2	1425.8	1432.0	1425.9	1422.6
20°	1421.3	1405.9	1412.1	1402.9	1401.7
22.5°	1398.3	1382.9	1389.1	1376.8	1376.6
25°	1361.1	1344.5	1352.0	1337.6	1336.3
27.5°	1316.9	1301.6	1307.8	1293.1	1291.6
30°	1286.6	1271.3	1277.5	1261.7	1259.1
32.5°	1252.1	1237.8	1242.9	1227.2	1225.7
35°	1199.0	1184.9	1188.5	1172.8	1171.5
37.5°	1138.6	1125.8	1127.9	1110.6	1109.3
40°	1095.7	1082.9	1083.9	1065.6	1064.3
42.5°	1048.6	1035.8	1034.8	1016.4	1015.2
45°	970.2	957.4	953.2	936.1	933.6
47.5°	880.7	868.0	860.1	846.2	844.4
50°	815.9	803.1	796.3	784.4	780.6
52.5°	745.8	733.0	727.2	716.4	712.6
55°	635.5	625.2	621.1	610.6	608.0
57.5°	530.6	523.7	522.5	512.3	511.2
60°	466.8	463.0	462.9	453.7	453.7
62.5°	412.4	409.6	411.6	405.6	404.5
65°	341.3	338.7	342.6	340.0	340.0
67.5°	285.0	285.0	287.4	286.3	286.3
70°	253.7	253.7	255.0	255.0	255.0
72.5°	225.4	224.4	227.8	227.7	226.7
75°	184.4	184.4	184.4	185.7	185.7
77.5°	143.6	143.8	144.9	144.6	143.6
80°	116.4	117.6	117.7	116.4	116.4
82.5°	89.2	90.5	90.5	90.2	89.2
85°	47.1	49.6	52.3	52.3	52.3
87.5°	13.6	17.7	20.9	20.9	19.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)