

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564694

Luminaire Tested: **SQ4-PW1-050U-125D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564694
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-050U-125D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6811.5 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564694
CATALOG NUMBER: SQ4-PW1-050U-125D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564694

CATALOG NUMBER: SQ4-PW1-050U-125D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	98	94	91	97	93	90	86	84	81	78	75	73	71	67	65	64	60
2	94	86	80	74	88	82	76	71	73	69	65	66	62	59	59	56	54	50
3	85	76	68	62	81	72	65	60	65	59	55	58	54	50	52	49	46	43
4	78	67	59	53	74	64	56	51	58	52	47	52	47	43	47	43	40	37
5	72	60	52	45	68	57	49	44	52	45	41	47	42	38	42	38	35	32
6	66	54	46	40	63	51	44	38	47	40	36	42	37	33	38	34	31	28
7	61	49	41	35	58	47	39	34	42	36	32	39	33	29	35	31	27	25
8	57	44	36	31	54	43	35	30	39	33	28	35	30	26	32	28	24	22
9	53	41	33	28	50	39	32	27	36	30	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17473	17473	17473
5°	17586	17447	17370
10°	17445	17305	17211
15°	17261	17069	17006
20°	17054	16792	16760
25°	16816	16511	16460
30°	16461	16211	16105
35°	15994	15767	15674
40°	15495	15254	15192
45°	14891	14696	14631
50°	14274	14154	14059
55°	13608	13608	13393
60°	12778	13024	12562
65°	11693	12276	11402
70°	10307	11297	10038
75°	8801	10113	8566
80°	6827	8512	6912
85°	4414	6531	5833



TEST NUMBER: P564694

CATALOG NUMBER: SQ4-PW1-050U-125D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.3	2.6
10°-20°	503.5	7.4
20°-30°	746.8	11.0
30°-40°	873.9	12.8
40°-50°	870.0	12.8
50°-60°	751.3	11.0
60°-70°	540.8	7.9
70°-80°	283.6	4.2
80°-90°	71.5	1.0
90°-100°	146.4	2.2
100°-110°	397.8	5.8
110°-120°	409.0	6.0
120°-130°	327.0	4.8
130°-140°	257.0	3.8
140°-150°	197.0	2.9
150°-160°	141.7	2.1
160°-170°	86.7	1.3
170°-180°	29.2	0.4
0°-30°	1428.7	21.0
0°-40°	2302.5	33.8
0°-60°	3923.8	57.6
0°-90°	4819.6	70.8
90°-120°	953.3	14.0
90°-150°	1734.4	25.5
90°-180°	1992.0	29.2
0°-180°	6811.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1894	1894	1894	1894	1894	
5°	1899	1878	1884	1879	1876	180
15°	1807	1784	1787	1784	1780	509
25°	1652	1624	1622	1612	1617	760
35°	1420	1400	1400	1387	1392	888
45°	1141	1132	1126	1123	1121	881
55°	846	844	846	834	833	755
65°	536	552	562	540	522	531
75°	247	270	284	265	240	265
85°	42	55	62	58	55	55
90°	1	4	7	9	9	3
95°	22	80	255	111	75	23
105°	71	110	438	666	627	75
115°	126	152	350	697	794	124
125°	173	197	317	534	630	154
135°	208	231	308	435	490	161
145°	240	258	304	370	397	151
155°	272	281	302	332	341	125
165°	294	298	303	316	317	83
175°	305	306	304	308	307	29
180°	305	305	305	305	305	



TEST NUMBER: P564694

CATALOG NUMBER: SQ4-PW1-050U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1893.8	1893.8	1893.8	1893.8	1893.8
2.5°	1904.5	1888.9	1893.8	1889.6	1880.5
5°	1898.8	1877.6	1883.8	1878.7	1875.5
7.5°	1879.5	1859.9	1864.5	1859.1	1857.1
10°	1862.1	1842.6	1847.1	1840.4	1837.1
12.5°	1842.1	1821.2	1825.8	1819.0	1817.1
15°	1807.1	1784.2	1787.0	1783.6	1780.4
17.5°	1766.4	1743.2	1743.7	1738.3	1737.7
20°	1737.0	1712.5	1710.3	1703.7	1707.0
22.5°	1705.0	1679.2	1676.9	1667.7	1672.3
25°	1651.9	1624.2	1621.9	1612.0	1616.9
27.5°	1590.5	1563.1	1563.1	1549.2	1554.4
30°	1545.1	1519.0	1521.7	1505.2	1511.7
32.5°	1497.0	1473.6	1475.0	1458.5	1465.0
35°	1420.0	1400.4	1399.9	1386.7	1391.6
37.5°	1341.2	1323.9	1321.2	1313.5	1314.8
40°	1286.5	1271.8	1266.5	1261.4	1261.4
42.5°	1229.1	1215.7	1210.4	1206.7	1205.4
45°	1141.3	1131.5	1126.3	1122.9	1121.3
47.5°	1054.5	1045.4	1040.9	1038.5	1036.9
50°	994.5	987.9	986.1	981.1	979.5
52.5°	934.4	930.5	928.7	922.4	920.7
55°	846.0	844.3	846.0	834.3	832.6
57.5°	753.9	756.5	761.9	746.1	742.2
60°	692.5	699.0	705.8	687.3	680.8
62.5°	629.7	640.2	649.7	628.5	619.4
65°	535.6	551.9	562.3	540.2	522.3
67.5°	444.8	465.1	477.5	453.7	433.5
70°	382.1	404.9	418.8	394.9	372.1
72.5°	327.4	352.8	364.1	341.5	318.7
75°	246.9	269.8	283.7	264.7	240.3
77.5°	175.2	196.7	208.2	191.8	171.5
80°	128.5	151.3	160.2	146.5	130.1
82.5°	91.1	110.0	116.1	107.9	96.8
85°	41.7	54.8	61.7	58.3	55.1
87.5°	10.9	20.6	26.7	27.2	28.5
90°	1.0	3.9	6.9	8.8	8.8
92.5°	8.8	40.1	69.6	29.9	25.3
95°	21.6	80.1	255.0	111.0	74.6
97.5°	35.7	88.5	391.0	304.2	213.7
100°	45.1	94.0	432.6	438.5	354.1
102.5°	54.5	99.6	443.6	542.3	467.9
105°	70.6	110.0	437.5	666.1	626.8
107.5°	87.3	122.0	412.2	730.1	741.0
110°	99.1	130.7	393.4	742.7	789.7

TEST NUMBER: P564694

CATALOG NUMBER: SQ4-PW1-050U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.3	139.4	374.5	732.2	803.0
115°	125.6	152.4	350.2	696.7	793.6
117.5°	140.9	166.6	334.7	646.4	755.5
120°	151.1	176.0	327.6	612.6	721.0
122.5°	159.7	184.6	322.9	578.8	683.3
125°	172.6	196.6	316.8	533.9	629.8
127.5°	184.2	208.0	313.5	499.8	582.1
130°	191.3	214.3	311.9	478.4	552.3
132.5°	198.3	221.4	310.4	460.2	525.6
135°	208.0	231.0	308.0	434.8	490.5
137.5°	218.4	239.3	306.8	412.5	459.3
140°	224.6	244.8	306.1	398.2	440.4
142.5°	230.9	249.5	305.3	387.1	422.4
145°	240.3	257.6	304.1	369.5	397.3
147.5°	250.9	265.7	303.1	355.6	377.5
150°	258.0	270.5	303.1	347.6	364.9
152.5°	263.5	274.4	302.3	340.5	354.7
155°	271.7	281.3	302.1	331.8	341.4
157.5°	279.8	287.2	302.1	325.8	333.1
160°	284.5	291.2	302.1	321.9	327.6
162.5°	289.2	294.4	302.9	318.7	322.9
165°	294.3	298.1	303.1	315.9	316.8
167.5°	299.6	301.5	304.1	312.5	313.3
170°	301.2	303.1	304.1	311.0	311.0
172.5°	302.7	303.9	304.1	309.4	309.4
175°	305.1	306.0	304.1	308.0	307.0
177.5°	305.9	305.9	303.5	306.6	305.1
180°	305.1	305.1	305.1	305.1	305.1

(END OF REPORT)