

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518498

Luminaire Tested: **SQ4-BB-075U-050D-835-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518498
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-075U-050D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8496.7 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 71.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518498
CATALOG NUMBER: SQ4-BB-075U-050D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P518498

CATALOG NUMBER: SQ4-BB-075U-050D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	30				
1	94	90	87	84	84	81	79	76	64	63	61	49	48	47	35	34	33	27				
2	87	80	75	70	78	72	68	64	58	55	52	44	42	41	32	31	30	24				
3	80	71	65	60	72	65	59	55	52	48	45	40	38	36	29	28	27	22				
4	73	64	57	52	66	58	52	47	47	43	39	36	34	32	27	25	24	20				
5	68	57	50	45	61	52	46	41	42	38	35	33	30	28	25	23	22	18				
6	63	52	45	39	56	47	41	36	39	34	31	30	27	25	23	21	20	16				
7	58	47	40	35	52	43	37	32	35	31	27	28	25	23	21	19	18	15				
8	54	43	36	31	49	39	33	29	32	28	25	26	23	21	20	18	16	14				
9	51	39	33	28	46	36	30	26	30	25	22	24	21	19	18	16	15	13				
10	47	36	30	25	43	33	27	24	28	23	20	22	19	17	17	15	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9694	9694	9694
5°	9538	9515	9586
10°	8925	9044	9296
15°	8114	8371	8837
20°	7202	7576	8240
25°	6272	6769	7571
30°	5372	5963	6938
35°	4455	5061	6172
40°	3422	4047	5259
45°	2474	3064	4231
50°	1686	2284	3357
55°	1095	1652	2608
60°	628	1163	1886
65°	167	711	954
70°	82	220	274
75°	36	18	0
80°	27	0	0
85°	0	0	0



TEST NUMBER: P518498

CATALOG NUMBER: SQ4-BB-075U-050D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	2.3
10°-20°	490.4	5.8
20°-30°	614.0	7.2
30°-40°	567.1	6.7
40°-50°	381.1	4.5
50°-60°	196.8	2.3
60°-70°	61.7	0.7
70°-80°	3.9	0.0
80°-90°	2.4	0.0
90°-100°	433.5	5.1
100°-110°	1192.6	14.0
110°-120°	1231.0	14.5
120°-130°	986.3	11.6
130°-140°	774.7	9.1
140°-150°	593.7	7.0
150°-160°	426.8	5.0
160°-170°	261.0	3.1
170°-180°	88.0	1.0
0°-30°	1296.2	15.3
0°-40°	1863.3	21.9
0°-60°	2441.3	28.7
0°-90°	2509.2	29.5
90°-120°	2857.1	33.6
90°-150°	5211.7	61.3
90°-180°	5988.0	70.5
0°-180°	8496.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2102	2102	2102	2102	2102	
5°	2060	2039	2055	2062	2070	191
15°	1699	1693	1753	1812	1850	473
25°	1232	1242	1330	1421	1487	565
35°	791	811	899	1004	1096	490
45°	379	402	470	561	649	298
55°	136	159	205	264	324	127
65°	15	29	65	78	87	26
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	2	8	14	18	18	4
95°	64	237	767	328	209	68
105°	213	328	1314	2001	1868	225
115°	377	460	1054	2099	2382	372
125°	520	593	956	1618	1895	464
135°	628	697	929	1308	1480	484
145°	726	775	915	1115	1201	455
155°	821	848	909	1002	1031	377
165°	888	899	913	950	956	250
175°	919	921	915	927	925	87
180°	919	919	919	919	919	

TEST NUMBER: P518498

CATALOG NUMBER: SQ4-BB-075U-050D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2101.5	2101.5	2101.5	2101.5	2101.5
2.5°	2106.4	2086.5	2091.7	2091.6	2086.0
5°	2059.8	2038.9	2054.7	2062.0	2070.0
7.5°	1972.8	1956.5	1986.8	2009.5	2026.0
10°	1905.3	1891.3	1930.7	1961.7	1984.6
12.5°	1827.2	1816.4	1864.0	1906.5	1935.8
15°	1698.9	1692.9	1752.8	1811.6	1850.4
17.5°	1561.4	1561.2	1629.5	1702.6	1749.3
20°	1467.1	1470.0	1543.3	1623.9	1678.5
22.5°	1372.7	1379.7	1457.9	1541.9	1604.5
25°	1232.2	1242.2	1329.8	1420.8	1487.4
27.5°	1097.2	1111.7	1203.9	1298.5	1379.6
30°	1008.5	1025.4	1119.4	1218.9	1302.4
32.5°	921.5	941.6	1033.1	1138.4	1223.5
35°	791.0	810.9	898.7	1004.5	1096.0
37.5°	656.2	675.6	761.5	865.6	964.4
40°	568.3	590.2	672.0	772.9	873.3
42.5°	488.6	510.5	587.4	686.6	781.4
45°	379.2	402.1	469.7	561.2	648.6
47.5°	288.5	313.4	372.7	455.5	535.2
50°	234.9	259.7	318.2	391.1	467.7
52.5°	191.7	215.8	268.6	337.3	407.5
55°	136.2	159.1	205.4	263.7	324.3
57.5°	94.1	113.8	155.3	204.0	251.5
60°	68.1	87.0	126.1	165.6	204.4
62.5°	45.3	62.6	100.9	131.1	157.2
65°	15.3	29.2	65.1	78.5	87.4
67.5°	7.7	9.3	34.2	36.1	39.0
70°	6.1	6.1	16.3	17.4	20.3
72.5°	4.5	4.5	6.5	8.4	8.9
75°	2.0	2.0	1.0	0.0	0.0
77.5°	1.0	1.0	0.8	0.0	0.0
80°	1.0	1.0	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.4	1.5	2.7	3.5	3.5
90°	2.0	7.7	13.7	17.6	17.6
92.5°	27.0	115.3	199.9	76.7	63.0
95°	64.5	236.6	766.6	327.8	209.2
97.5°	105.2	262.4	1169.8	901.3	635.9
100°	134.9	278.3	1296.5	1308.6	1067.7
102.5°	163.1	297.3	1329.4	1623.5	1402.5
105°	213.2	327.9	1314.1	2001.4	1867.5
107.5°	260.9	365.6	1239.4	2186.4	2226.2
110°	295.3	390.9	1183.1	2232.4	2370.1



TEST NUMBER: P518498

CATALOG NUMBER: SQ4-BB-075U-050D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	326.6	419.1	1126.8	2202.8	2412.3
115°	377.4	459.6	1054.0	2098.8	2381.8
117.5°	425.9	501.6	1007.9	1953.0	2273.1
120°	455.6	528.3	987.5	1843.8	2174.6
122.5°	482.2	554.9	973.5	1747.9	2061.9
125°	520.2	592.8	956.3	1617.7	1894.9
127.5°	556.2	625.4	944.9	1508.9	1752.2
130°	574.9	645.7	938.7	1444.3	1666.1
132.5°	596.8	667.6	934.0	1387.5	1587.9
135°	627.7	696.6	928.9	1308.3	1480.3
137.5°	656.7	720.5	924.6	1244.2	1386.1
140°	678.6	737.8	923.0	1201.7	1329.8
142.5°	697.3	752.0	919.9	1163.7	1273.4
145°	725.5	775.2	915.2	1114.7	1200.7
147.5°	755.6	798.4	912.8	1071.2	1140.1
150°	774.4	812.6	911.3	1047.4	1101.0
152.5°	791.6	826.8	909.7	1026.9	1071.2
155°	821.3	848.1	909.3	1001.9	1030.6
157.5°	842.8	864.6	909.3	981.3	1001.2
160°	858.5	875.7	909.3	970.3	985.6
162.5°	871.0	885.1	910.9	960.8	973.1
165°	887.8	899.3	913.2	950.5	956.3
167.5°	899.5	908.3	915.2	941.8	943.3
170°	907.4	913.1	915.2	938.7	938.7
172.5°	913.6	916.3	915.2	933.9	932.4
175°	919.1	921.0	915.2	926.9	925.0
177.5°	920.7	920.7	914.4	923.7	920.7
180°	919.1	919.1	919.1	919.1	919.1

(END OF REPORT)