

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564718

Luminaire Tested: **SQ4-PW1-075U-050D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564718  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-075U-050D-835-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4923.0 lumens  
Efficiency: N/A  
Efficacy: 141.9 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 34.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564718  
CATALOG NUMBER: SQ4-PW1-075U-050D-835-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564718

CATALOG NUMBER: SQ4-PW1-075U-050D-835-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	55	47	41	60	50	44	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	27	24	21	21	19	17	14
8	52	40	33	28	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6992	6992	6992
5°	7037	6981	6951
10°	6980	6924	6887
15°	6907	6830	6805
20°	6824	6720	6706
25°	6729	6607	6586
30°	6587	6487	6444
35°	6400	6310	6271
40°	6200	6104	6080
45°	5959	5881	5855
50°	5711	5664	5625
55°	5445	5445	5360
60°	5113	5211	5026
65°	4678	4912	4563
70°	4125	4521	4017
75°	3522	4046	3426
80°	2731	3406	2768
85°	1768	2615	2329



TEST NUMBER: P564718

CATALOG NUMBER: SQ4-PW1-075U-050D-835-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.4	1.4
10°-20°	201.5	4.1
20°-30°	298.8	6.1
30°-40°	349.7	7.1
40°-50°	348.1	7.1
50°-60°	300.6	6.1
60°-70°	216.4	4.4
70°-80°	113.5	2.3
80°-90°	29.3	0.6
90°-100°	216.8	4.4
100°-110°	596.3	12.1
110°-120°	615.5	12.5
120°-130°	493.1	10.0
130°-140°	387.3	7.9
140°-150°	296.8	6.0
150°-160°	213.4	4.3
160°-170°	130.5	2.7
170°-180°	44.0	0.9
0°-30°	571.7	11.6
0°-40°	921.3	18.7
0°-60°	1570.1	31.9
0°-90°	1929.2	39.2
90°-120°	1428.6	29.0
90°-150°	2605.9	52.9
90°-180°	2994.0	60.8
0°-180°	4923.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	758	758	758	758	758	
5°	760	751	754	752	750	72
15°	723	714	715	714	712	204
25°	661	650	649	645	647	304
35°	568	560	560	555	557	355
45°	457	453	451	449	449	352
55°	338	338	338	334	333	302
65°	214	221	225	216	209	212
75°	99	108	114	106	96	106
85°	17	22	25	23	22	22
90°	1	4	7	9	9	3
95°	32	118	383	164	105	34
105°	107	164	657	1001	934	112
115°	189	230	527	1049	1191	186
125°	260	296	478	809	948	232
135°	314	348	464	654	740	242
145°	363	388	458	557	600	227
155°	411	424	455	501	515	189
165°	444	450	457	475	478	125
175°	460	460	458	463	462	44
180°	460	460	460	460	460	

TEST NUMBER: P564718

CATALOG NUMBER: SQ4-PW1-075U-050D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	757.8	757.8	757.8	757.8	757.8
2.5°	762.1	755.8	757.8	756.1	752.5
5°	759.8	751.3	753.8	751.8	750.5
7.5°	752.1	744.2	746.1	743.9	743.1
10°	745.1	737.3	739.1	736.4	735.1
12.5°	737.1	728.7	730.6	727.9	727.1
15°	723.1	713.9	715.1	713.7	712.4
17.5°	706.8	697.5	697.7	695.6	695.3
20°	695.0	685.2	684.4	681.7	683.0
22.5°	682.2	671.9	671.0	667.3	669.1
25°	661.0	649.9	649.0	645.0	647.0
27.5°	636.4	625.5	625.5	619.9	622.0
30°	618.3	607.8	608.9	602.3	604.9
32.5°	599.0	589.6	590.2	583.6	586.2
35°	568.2	560.4	560.2	554.9	556.8
37.5°	536.7	529.8	528.7	525.6	526.1
40°	514.8	508.9	506.8	504.8	504.8
42.5°	491.8	486.4	484.3	482.8	482.3
45°	456.7	452.8	450.7	449.3	448.7
47.5°	422.0	418.3	416.5	415.5	414.9
50°	397.9	395.3	394.6	392.6	391.9
52.5°	373.9	372.3	371.6	369.1	368.4
55°	338.5	337.9	338.5	333.8	333.2
57.5°	301.7	302.7	304.9	298.5	297.0
60°	277.1	279.7	282.4	275.0	272.4
62.5°	252.0	256.2	260.0	251.5	247.8
65°	214.3	220.8	225.0	216.2	209.0
67.5°	178.0	186.1	191.1	181.6	173.5
70°	152.9	162.0	167.6	158.0	148.9
72.5°	131.0	141.2	145.7	136.7	127.5
75°	98.8	108.0	113.5	105.9	96.1
77.5°	70.1	78.7	83.3	76.7	68.6
80°	51.4	60.5	64.1	58.6	52.1
82.5°	36.5	44.0	46.5	43.2	38.7
85°	16.7	21.9	24.7	23.3	22.0
87.5°	4.5	8.7	11.5	11.9	12.4
90°	1.0	3.8	6.8	8.8	8.8
92.5°	13.5	57.7	99.9	38.4	31.5
95°	32.3	118.3	383.3	163.9	104.6
97.5°	52.6	131.2	584.9	450.7	318.0
100°	67.5	139.2	648.3	654.3	533.9
102.5°	81.5	148.7	664.7	811.8	701.3
105°	106.6	163.9	657.1	1000.7	933.8
107.5°	130.4	182.8	619.7	1093.2	1113.1
110°	147.6	195.4	591.5	1116.2	1185.1



TEST NUMBER: P564718

CATALOG NUMBER: SQ4-PW1-075U-050D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	163.3	209.6	563.4	1101.4	1206.2
115°	188.7	229.8	527.0	1049.4	1190.9
117.5°	213.0	250.8	503.9	976.5	1136.6
120°	227.8	264.1	493.8	921.9	1087.3
122.5°	241.1	277.4	486.7	874.0	1031.0
125°	260.1	296.4	478.1	808.8	947.5
127.5°	278.1	312.7	472.5	754.5	876.1
130°	287.5	322.8	469.3	722.2	833.1
132.5°	298.4	333.8	467.0	693.8	793.9
135°	313.9	348.3	464.4	654.1	740.2
137.5°	328.3	360.3	462.3	622.1	693.0
140°	339.3	368.9	461.5	600.8	664.9
142.5°	348.7	376.0	459.9	581.8	636.7
145°	362.8	387.6	457.6	557.3	600.3
147.5°	377.8	399.2	456.4	535.6	570.0
150°	387.2	406.3	455.6	523.7	550.5
152.5°	395.8	413.4	454.9	513.4	535.6
155°	410.7	424.0	454.7	500.9	515.3
157.5°	421.4	432.3	454.7	490.7	500.6
160°	429.2	437.8	454.7	485.1	492.8
162.5°	435.5	442.6	455.4	480.4	486.5
165°	443.9	449.6	456.6	475.3	478.1
167.5°	449.8	454.2	457.6	470.9	471.7
170°	453.7	456.6	457.6	469.3	469.3
172.5°	456.8	458.2	457.6	467.0	466.2
175°	459.5	460.5	457.6	463.4	462.5
177.5°	460.3	460.3	457.2	461.9	460.3
180°	459.5	459.5	459.5	459.5	459.5

(END OF REPORT)