

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562584

Luminaire Tested: **SQ4-PC3-025U-125D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562584
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11769.8 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 101.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562584
CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562584

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	115	115	115	115	111	111	111	111	102	102	102	94	94	94	87	87	87	84				
1	105	101	97	93	101	97	93	90	90	87	84	83	81	79	77	75	74	71				
2	96	88	82	76	92	85	79	74	79	74	70	73	69	66	68	65	62	59				
3	88	78	70	64	84	75	68	62	70	64	59	65	60	56	60	56	53	50				
4	80	69	60	54	77	66	59	53	62	55	50	58	52	48	54	49	46	43				
5	74	61	53	46	71	59	51	45	55	49	43	52	46	42	48	44	40	37				
6	68	55	47	40	65	53	45	40	50	43	38	47	41	36	44	39	35	33				
7	63	50	42	36	60	48	41	35	45	39	34	43	37	32	40	35	31	29				
8	59	46	37	32	56	44	37	31	42	35	30	39	33	29	37	32	28	26				
9	55	42	34	28	53	41	33	28	38	32	27	36	30	26	34	29	25	23				
10	51	38	31	26	49	37	30	25	35	29	24	33	28	24	31	26	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16626	16626	16626
5°	16752	16643	16582
10°	16711	16632	16586
15°	16623	16623	16607
20°	16514	16563	16563
25°	16358	16476	16425
30°	16159	16354	16283
35°	15918	16163	16049
40°	15655	15876	15716
45°	15370	15479	15240
50°	14968	14968	14729
55°	14494	14306	14091
60°	13793	13516	13301
65°	12749	12494	12385
70°	11163	11253	11208
75°	8981	9933	9992
80°	6384	8421	8512
85°	3885	7066	7066



TEST NUMBER: P562584

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	341.1	2.9
10°-20°	978.8	8.3
20°-30°	1482.3	12.6
30°-40°	1777.1	15.1
40°-50°	1812.0	15.4
50°-60°	1581.8	13.4
60°-70°	1132.4	9.6
70°-80°	583.3	5.0
80°-90°	149.1	1.3
90°-100°	145.3	1.2
100°-110°	381.9	3.2
110°-120°	396.0	3.4
120°-130°	317.6	2.7
130°-140°	249.2	2.1
140°-150°	191.3	1.6
150°-160°	137.8	1.2
160°-170°	84.3	0.7
170°-180°	28.5	0.2
0°-30°	2802.2	23.8
0°-40°	4579.4	38.9
0°-60°	7973.2	67.7
0°-90°	9837.9	83.6
90°-120°	923.2	7.8
90°-150°	1681.3	14.3
90°-180°	1932.0	16.4
0°-180°	11769.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3604	3604	3604	3604	3604	
5°	3618	3582	3594	3584	3581	343
15°	3481	3451	3481	3481	3477	981
25°	3214	3191	3237	3227	3227	1479
35°	2827	2820	2870	2850	2850	1768
45°	2356	2350	2373	2342	2336	1814
55°	1802	1779	1779	1752	1752	1606
65°	1168	1142	1145	1135	1135	1155
75°	504	527	557	561	561	545
85°	73	113	134	137	134	100
90°	2	6	15	8	8	5
95°	19	75	250	129	88	21
105°	69	104	422	641	598	73
115°	122	148	338	675	770	121
125°	170	191	308	520	613	151
135°	202	223	298	420	476	157
145°	235	250	294	358	386	147
155°	266	273	294	323	332	122
165°	287	290	294	306	310	81
175°	298	298	296	300	300	28
180°	298	298	298	298	298	



TEST NUMBER: P562584

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3604.1	3604.1	3604.1	3604.1	3604.1
2.5°	3625.5	3594.2	3604.1	3595.8	3582.8
5°	3617.5	3581.6	3594.1	3584.0	3580.8
7.5°	3591.4	3555.6	3572.1	3565.3	3562.1
10°	3567.4	3531.5	3550.7	3544.0	3540.7
12.5°	3535.4	3502.1	3524.0	3517.3	3516.7
15°	3480.7	3451.3	3480.7	3480.6	3477.3
17.5°	3411.9	3385.2	3416.6	3418.5	3416.6
20°	3363.9	3334.5	3373.9	3370.6	3373.9
22.5°	3305.1	3281.0	3323.1	3314.5	3317.8
25°	3213.7	3190.8	3237.0	3227.0	3227.0
27.5°	3105.6	3089.2	3139.6	3128.9	3128.9
30°	3033.5	3017.2	3070.2	3056.8	3056.8
32.5°	2953.4	2942.3	2992.8	2976.7	2976.7
35°	2826.6	2820.0	2870.0	2849.9	2849.9
37.5°	2695.8	2689.9	2735.1	2710.9	2703.1
40°	2599.6	2596.4	2636.4	2609.7	2609.7
42.5°	2503.5	2500.3	2534.9	2502.9	2502.9
45°	2356.0	2349.5	2372.7	2342.5	2336.0
47.5°	2195.2	2188.7	2203.2	2170.4	2167.1
50°	2085.7	2079.2	2085.7	2055.6	2052.4
52.5°	1973.6	1961.8	1962.9	1932.9	1932.2
55°	1802.1	1779.2	1778.7	1752.0	1752.0
57.5°	1620.5	1590.5	1593.2	1570.4	1567.1
60°	1495.0	1462.4	1465.0	1444.9	1441.7
62.5°	1372.2	1334.4	1342.2	1319.5	1318.8
65°	1168.0	1141.9	1144.6	1134.6	1134.6
67.5°	971.8	947.6	965.1	957.1	956.4
70°	827.6	811.3	834.3	834.2	831.0
72.5°	694.1	693.5	722.2	722.2	724.2
75°	503.9	526.8	557.3	560.6	560.6
77.5°	336.4	376.8	410.5	411.8	411.1
80°	240.3	286.0	317.0	323.6	320.4
82.5°	162.9	211.1	236.9	243.5	240.3
85°	73.4	112.6	133.5	136.7	133.5
87.5°	21.7	46.0	56.5	54.8	49.6
90°	1.9	5.6	15.3	7.6	7.6
92.5°	8.0	38.7	85.6	37.9	24.5
95°	19.1	75.1	250.3	129.0	87.9
97.5°	33.2	82.6	374.5	297.8	219.3
100°	43.9	88.8	412.7	418.2	324.8
102.5°	53.1	95.0	423.4	520.9	441.0
105°	68.8	104.3	422.2	641.0	598.0
107.5°	84.8	117.7	398.2	703.3	713.8
110°	95.5	125.4	378.3	719.4	764.2

TEST NUMBER: P562584

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	106.2	134.6	360.0	709.2	778.0
115°	122.3	148.4	338.2	674.7	770.0
117.5°	137.9	161.9	323.3	626.8	732.5
120°	147.1	169.5	317.2	594.6	697.4
122.5°	156.3	178.7	312.6	562.5	663.7
125°	170.0	190.6	307.6	519.9	613.3
127.5°	181.1	202.0	303.4	485.5	564.4
130°	187.2	209.7	301.9	464.0	536.9
132.5°	193.4	215.8	300.3	445.5	510.9
135°	202.5	223.1	298.0	419.7	475.7
137.5°	212.1	232.2	297.7	400.4	446.3
140°	219.7	238.4	296.1	385.0	428.0
142.5°	225.8	243.0	296.1	374.2	411.2
145°	235.0	249.9	294.2	357.9	385.9
147.5°	244.2	258.7	294.2	344.4	367.6
150°	250.3	263.4	294.2	336.7	355.4
152.5°	256.4	266.5	294.2	330.5	344.7
155°	265.6	273.0	294.2	323.1	332.4
157.5°	272.4	279.5	294.2	316.5	323.3
160°	277.0	282.6	294.2	313.4	317.2
162.5°	281.6	285.7	294.2	310.4	314.1
165°	286.6	290.3	294.2	305.8	309.5
167.5°	291.2	293.0	296.1	303.8	305.3
170°	294.2	296.1	296.1	303.8	303.8
172.5°	295.8	296.1	296.1	302.2	300.7
175°	298.0	298.0	296.1	300.0	300.0
177.5°	298.0	298.0	296.5	299.5	298.0
180°	298.0	298.0	298.0	298.0	298.0

(END OF REPORT)