

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565078

Luminaire Tested: **SQ4-PW1-125U-125D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565078
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-125D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9819.6 lumens
Efficiency: N/A
Efficacy: 130.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565078
CATALOG NUMBER: SQ4-PW1-125U-125D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P565078

CATALOG NUMBER: SQ4-PW1-125U-125D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49				49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47				42	
2	89	82	76	70	82	75	70	66	64	60	57	53	50	48	43	41	40				35	
3	81	72	65	59	75	66	60	55	56	52	48	47	44	41	38	36	34				30	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	45	40	45	39	35	38	33	30	31	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22				19	
7	58	46	38	32	53	43	36	31	37	31	27	31	27	23	26	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18				15	
9	50	38	31	25	46	35	29	24	31	25	21	26	22	19	22	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17473	17473	17473
5°	17586	17447	17370
10°	17445	17305	17211
15°	17261	17069	17006
20°	17054	16792	16760
25°	16816	16511	16460
30°	16461	16211	16105
35°	15994	15767	15674
40°	15495	15254	15192
45°	14891	14696	14631
50°	14274	14154	14059
55°	13608	13608	13393
60°	12778	13024	12562
65°	11693	12276	11402
70°	10307	11297	10038
75°	8801	10113	8566
80°	6827	8512	6912
85°	4414	6531	5833



TEST NUMBER: P565078

CATALOG NUMBER: SQ4-PW1-125U-125D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.3	1.8
10°-20°	503.5	5.1
20°-30°	746.8	7.6
30°-40°	873.9	8.9
40°-50°	870.0	8.9
50°-60°	751.3	7.7
60°-70°	540.8	5.5
70°-80°	283.6	2.9
80°-90°	72.1	0.7
90°-100°	362.3	3.7
100°-110°	975.9	9.9
110°-120°	1024.2	10.4
120°-130°	831.1	8.5
130°-140°	651.8	6.6
140°-150°	500.4	5.1
150°-160°	359.8	3.7
160°-170°	219.8	2.2
170°-180°	74.1	0.8
0°-30°	1428.7	14.5
0°-40°	2302.5	23.4
0°-60°	3923.8	40.0
0°-90°	4820.2	49.1
90°-120°	2362.3	24.1
90°-150°	4345.6	44.3
90°-180°	4999.0	50.9
0°-180°	9819.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1894	1894	1894	1894	1894	
5°	1899	1878	1884	1879	1876	180
15°	1807	1784	1787	1784	1780	509
25°	1652	1624	1622	1612	1617	760
35°	1420	1400	1400	1387	1392	888
45°	1141	1132	1126	1123	1121	881
55°	846	844	846	834	833	755
65°	536	552	562	540	522	531
75°	247	270	284	265	240	265
85°	42	55	62	58	55	55
90°	2	6	12	13	13	5
95°	55	197	594	304	210	58
105°	180	281	1079	1615	1515	190
115°	319	390	899	1736	1964	314
125°	435	500	807	1364	1605	389
135°	524	585	784	1100	1246	404
145°	606	653	774	941	1010	380
155°	688	713	768	844	871	317
165°	746	754	770	801	805	210
175°	775	774	772	782	780	74
180°	774	774	774	774	774	

TEST NUMBER: P565078

CATALOG NUMBER: SQ4-PW1-125U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1893.8	1893.8	1893.8	1893.8	1893.8
2.5°	1904.5	1888.9	1893.8	1889.6	1880.5
5°	1898.8	1877.6	1883.8	1878.7	1875.5
7.5°	1879.5	1859.9	1864.5	1859.1	1857.1
10°	1862.1	1842.6	1847.1	1840.4	1837.1
12.5°	1842.1	1821.2	1825.8	1819.0	1817.1
15°	1807.1	1784.2	1787.0	1783.6	1780.4
17.5°	1766.4	1743.2	1743.7	1738.3	1737.7
20°	1737.0	1712.5	1710.3	1703.7	1707.0
22.5°	1705.0	1679.2	1676.9	1667.7	1672.3
25°	1651.9	1624.2	1621.9	1612.0	1616.9
27.5°	1590.5	1563.1	1563.1	1549.2	1554.4
30°	1545.1	1519.0	1521.7	1505.2	1511.7
32.5°	1497.0	1473.6	1475.0	1458.5	1465.0
35°	1420.0	1400.4	1399.9	1386.7	1391.6
37.5°	1341.2	1323.9	1321.2	1313.5	1314.8
40°	1286.5	1271.8	1266.5	1261.4	1261.4
42.5°	1229.1	1215.7	1210.4	1206.7	1205.4
45°	1141.3	1131.5	1126.3	1122.9	1121.3
47.5°	1054.5	1045.4	1040.9	1038.5	1036.9
50°	994.5	987.9	986.1	981.1	979.5
52.5°	934.4	930.5	928.7	922.4	920.7
55°	846.0	844.3	846.0	834.3	832.6
57.5°	753.9	756.5	761.9	746.1	742.2
60°	692.5	699.0	705.8	687.3	680.8
62.5°	629.7	640.2	649.7	628.5	619.4
65°	535.6	551.9	562.3	540.2	522.3
67.5°	444.8	465.1	477.5	453.7	433.5
70°	382.1	404.9	418.8	394.9	372.1
72.5°	327.4	352.8	364.1	341.5	318.7
75°	246.9	269.8	283.7	264.7	240.3
77.5°	175.2	196.7	208.2	191.8	171.5
80°	128.5	151.3	160.2	146.5	130.1
82.5°	91.1	110.0	116.1	107.9	96.8
85°	41.7	54.8	61.7	58.3	55.1
87.5°	11.1	21.0	27.7	28.0	29.3
90°	2.0	5.8	11.8	12.8	12.8
92.5°	24.1	85.0	168.1	80.9	56.2
95°	55.2	197.0	593.9	303.7	210.1
97.5°	88.2	225.6	931.5	778.2	586.8
100°	113.4	236.9	1038.8	1086.9	901.7
102.5°	137.9	252.9	1074.3	1318.1	1166.1
105°	180.5	280.9	1079.3	1614.6	1515.3
107.5°	220.8	310.3	1033.3	1767.0	1792.7
110°	247.6	332.5	991.5	1814.4	1907.9



TEST NUMBER: P565078

CATALOG NUMBER: SQ4-PW1-125U-125D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	276.0	354.7	951.2	1803.9	1957.7
115°	318.6	390.0	898.7	1736.5	1964.2
117.5°	357.5	424.5	858.1	1629.0	1882.5
120°	382.8	447.4	837.6	1551.8	1812.2
122.5°	404.9	468.7	822.6	1472.9	1732.5
125°	435.1	499.7	807.0	1363.9	1605.1
127.5°	464.1	527.7	797.1	1267.8	1483.1
130°	481.4	545.1	793.2	1212.8	1401.8
132.5°	498.8	561.7	789.2	1164.3	1337.9
135°	523.8	584.6	784.3	1100.3	1246.0
137.5°	547.7	606.0	781.7	1046.1	1165.7
140°	564.3	620.2	779.4	1012.7	1120.7
142.5°	581.7	633.7	777.8	981.5	1072.5
145°	605.7	653.0	774.4	940.7	1010.2
147.5°	631.8	672.9	771.1	906.5	961.1
150°	649.1	684.8	769.5	885.0	930.3
152.5°	664.9	696.0	768.7	867.4	904.2
155°	687.6	712.7	767.5	844.1	871.1
157.5°	707.5	727.0	767.7	827.7	845.8
160°	720.2	736.6	768.5	818.1	831.6
162.5°	731.2	744.5	769.3	810.2	819.8
165°	745.8	754.5	770.5	801.1	805.0
167.5°	757.6	762.7	771.5	794.2	795.7
170°	765.5	767.5	771.5	790.2	790.2
172.5°	770.3	770.7	772.2	786.3	786.3
175°	775.4	774.4	771.5	782.3	780.3
177.5°	777.6	776.0	772.1	778.3	776.8
180°	774.4	774.4	774.4	774.4	774.4

(END OF REPORT)