

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P562632

Luminaire Tested: **SQ4-PC3-050U-075D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562632
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-075D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9787.3 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 78.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562632
CATALOG NUMBER: SQ4-PC3-050U-075D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562632

CATALOG NUMBER: SQ4-PC3-050U-075D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	57	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	37	34	30
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9806	9806	9806
5°	9879	9816	9779
10°	9855	9809	9782
15°	9804	9804	9794
20°	9739	9768	9768
25°	9647	9717	9687
30°	9530	9645	9603
35°	9388	9532	9466
40°	9233	9363	9268
45°	9065	9129	8988
50°	8828	8828	8687
55°	8548	8437	8311
60°	8135	7971	7844
65°	7519	7369	7305
70°	6583	6636	6610
75°	5297	5859	5893
80°	3764	4968	5018
85°	2292	4166	4166



TEST NUMBER: P562632

CATALOG NUMBER: SQ4-PC3-050U-075D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.2	2.1
10°-20°	577.3	5.9
20°-30°	874.2	8.9
30°-40°	1048.1	10.7
40°-50°	1068.7	10.9
50°-60°	932.9	9.5
60°-70°	667.9	6.8
70°-80°	344.0	3.5
80°-90°	89.3	0.9
90°-100°	292.9	3.0
100°-110°	795.7	8.1
110°-120°	818.1	8.4
120°-130°	654.1	6.7
130°-140°	513.9	5.3
140°-150°	394.1	4.0
150°-160°	283.4	2.9
160°-170°	173.3	1.8
170°-180°	58.4	0.6
0°-30°	1652.7	16.9
0°-40°	2700.7	27.6
0°-60°	4702.3	48.0
0°-90°	5803.5	59.3
90°-120°	1906.7	19.5
90°-150°	3468.7	35.4
90°-180°	3984.0	40.7
0°-180°	9787.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2126	2126	2126	2126	2126	
5°	2133	2112	2120	2114	2112	203
15°	2053	2035	2053	2053	2051	579
25°	1895	1882	1909	1903	1903	872
35°	1667	1663	1693	1681	1681	1043
45°	1390	1386	1399	1382	1378	1070
55°	1063	1049	1049	1033	1033	947
65°	689	673	675	669	669	681
75°	297	311	329	331	331	321
85°	43	66	79	81	79	59
90°	2	8	14	18	18	5
95°	43	160	510	222	149	46
105°	141	220	875	1332	1254	150
115°	251	305	700	1393	1587	248
125°	345	393	634	1068	1260	308
135°	416	462	616	870	981	322
145°	481	515	608	739	795	302
155°	543	563	604	664	683	251
165°	589	596	606	632	634	166
175°	610	612	608	616	614	58
180°	610	610	610	610	610	

TEST NUMBER: P562632

CATALOG NUMBER: SQ4-PC3-050U-075D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2125.6	2125.6	2125.6	2125.6	2125.6
2.5°	2138.2	2119.7	2125.6	2120.7	2113.0
5°	2133.4	2112.3	2119.7	2113.7	2111.8
7.5°	2118.1	2096.9	2106.7	2102.7	2100.8
10°	2103.9	2082.8	2094.1	2090.1	2088.2
12.5°	2085.0	2065.4	2078.3	2074.4	2074.0
15°	2052.8	2035.4	2052.8	2052.7	2050.8
17.5°	2012.2	1996.4	2015.0	2016.1	2015.0
20°	1983.9	1966.5	1989.8	1987.8	1989.8
22.5°	1949.2	1935.0	1959.9	1954.8	1956.7
25°	1895.3	1881.8	1909.1	1903.2	1903.2
27.5°	1831.5	1821.9	1851.6	1845.3	1845.3
30°	1789.0	1779.4	1810.7	1802.8	1802.8
32.5°	1741.8	1735.2	1765.0	1755.6	1755.6
35°	1667.0	1663.2	1692.6	1680.8	1680.8
37.5°	1589.9	1586.4	1613.1	1598.8	1594.2
40°	1533.2	1531.2	1554.8	1539.1	1539.1
42.5°	1476.5	1474.6	1495.0	1476.1	1476.1
45°	1389.5	1385.6	1399.3	1381.5	1377.7
47.5°	1294.6	1290.8	1299.4	1280.0	1278.1
50°	1230.1	1226.2	1230.1	1212.3	1210.4
52.5°	1163.9	1157.0	1157.7	1139.9	1139.5
55°	1062.8	1049.3	1049.0	1033.3	1033.3
57.5°	955.7	938.0	939.6	926.2	924.2
60°	881.7	862.5	864.0	852.2	850.2
62.5°	809.3	787.0	791.6	778.2	777.8
65°	688.8	673.4	675.1	669.2	669.2
67.5°	573.1	558.9	569.2	564.4	564.1
70°	488.1	478.5	492.0	492.0	490.1
72.5°	409.4	409.0	425.9	425.9	427.1
75°	297.2	310.7	328.7	330.6	330.6
77.5°	198.4	222.2	242.1	242.9	242.5
80°	141.7	168.6	187.0	190.9	188.9
82.5°	96.0	124.5	139.7	143.6	141.7
85°	43.3	66.4	78.7	80.6	78.7
87.5°	13.0	28.0	34.2	35.0	31.9
90°	2.0	7.7	13.7	17.7	17.7
92.5°	17.7	80.2	139.3	59.8	50.6
95°	43.2	160.2	510.1	222.0	149.1
97.5°	71.4	176.9	782.0	608.4	427.3
100°	90.2	188.1	865.2	877.1	708.2
102.5°	109.1	199.2	887.2	1084.7	935.8
105°	141.3	219.9	875.0	1332.3	1253.6
107.5°	174.6	244.1	824.4	1460.1	1482.0
110°	198.2	261.5	786.7	1485.3	1579.3

TEST NUMBER: P562632

CATALOG NUMBER: SQ4-PC3-050U-075D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	218.6	278.8	749.1	1464.4	1606.0
115°	251.1	304.8	700.4	1393.4	1587.2
117.5°	281.7	333.1	669.4	1292.7	1511.0
120°	302.1	352.0	655.3	1225.2	1442.0
122.5°	319.4	369.3	645.9	1157.6	1366.7
125°	345.3	393.3	633.7	1067.7	1259.5
127.5°	368.4	416.0	627.0	999.6	1164.2
130°	382.6	428.6	623.9	956.8	1104.5
132.5°	396.7	442.7	620.7	920.4	1051.2
135°	415.9	462.0	616.0	869.7	980.9
137.5°	436.7	478.5	613.7	824.9	918.6
140°	449.3	489.6	612.1	796.5	880.9
142.5°	461.8	499.0	610.5	774.2	844.8
145°	480.7	515.2	608.2	738.9	794.6
147.5°	501.9	531.4	606.2	711.2	754.9
150°	516.0	540.9	606.2	695.3	729.8
152.5°	527.0	548.8	604.7	681.0	709.4
155°	543.4	562.6	604.3	663.6	682.7
157.5°	559.5	574.5	604.3	651.7	666.3
160°	568.9	582.4	604.3	643.8	655.3
162.5°	578.4	588.7	605.8	637.4	645.9
165°	588.6	596.2	606.2	631.8	633.7
167.5°	599.2	603.0	608.2	625.1	626.6
170°	602.3	606.1	608.2	621.9	621.9
172.5°	605.4	607.7	608.2	618.8	618.8
175°	610.1	612.1	608.2	616.0	614.1
177.5°	611.7	611.7	607.0	613.2	610.1
180°	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)