

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519192

Luminaire Tested: **SQ4-WB-075U-075D-835-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519192
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-075U-075D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5488.4 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 42.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519192
CATALOG NUMBER: SQ4-WB-075U-075D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519192

CATALOG NUMBER: SQ4-WB-075U-075D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	98	94	90	87	90	86	83	81	72	70	68	59	58	57	47	47	46	40
2	90	83	78	73	82	77	72	68	65	61	58	53	51	49	43	42	40	36
3	83	74	67	62	76	69	63	58	58	54	50	48	45	43	39	37	36	31
4	76	66	59	54	70	61	55	50	52	48	44	44	40	38	36	34	32	28
5	70	60	52	47	65	55	49	44	47	42	39	40	36	33	33	30	28	25
6	65	54	47	41	60	50	44	39	43	38	34	36	33	30	30	28	26	23
7	61	49	42	37	56	46	39	35	39	34	31	34	30	27	28	25	23	21
8	56	45	38	33	52	42	36	31	36	31	28	31	27	24	26	23	21	19
9	53	41	34	29	49	39	32	28	34	29	25	29	25	22	24	21	19	17
10	49	38	31	27	46	36	30	25	31	26	23	27	23	20	23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15787	15787	15787
5°	15590	15534	15625
10°	14729	14863	15208
15°	13598	13913	14537
20°	12348	12812	13660
25°	11075	11680	12726
30°	9902	10550	11758
35°	8659	9285	10613
40°	7289	7867	9187
45°	6015	6534	7671
50°	5022	5474	6390
55°	4263	4699	5278
60°	3644	4072	4211
65°	2901	3425	2720
70°	2573	2673	1662
75°	2381	2167	1016
80°	2194	1992	877
85°	1990	1831	720



TEST NUMBER: P519192

CATALOG NUMBER: SQ4-WB-075U-075D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.0	2.9
10°-20°	408.2	7.4
20°-30°	528.8	9.6
30°-40°	517.8	9.4
40°-50°	396.3	7.2
50°-60°	264.1	4.8
60°-70°	144.1	2.6
70°-80°	60.0	1.1
80°-90°	18.2	0.3
90°-100°	216.8	3.9
100°-110°	596.3	10.9
110°-120°	615.5	11.2
120°-130°	493.1	9.0
130°-140°	387.3	7.1
140°-150°	296.8	5.4
150°-160°	213.4	3.9
160°-170°	130.5	2.4
170°-180°	44.0	0.8
0°-30°	1094.0	19.9
0°-40°	1611.8	29.4
0°-60°	2272.2	41.4
0°-90°	2494.6	45.5
90°-120°	1428.6	26.0
90°-150°	2605.9	47.5
90°-180°	2994.0	54.6
0°-180°	5488.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1711	1711	1711	1711	1711	
5°	1683	1666	1677	1681	1687	157
15°	1424	1418	1457	1496	1522	398
25°	1088	1091	1147	1197	1250	500
35°	769	772	824	880	942	478
45°	461	470	501	539	588	360
55°	265	276	292	303	328	240
65°	133	144	157	137	125	138
75°	67	67	61	42	28	71
85°	19	19	17	11	7	20
90°	1	4	7	9	9	3
95°	32	118	383	164	105	34
105°	107	164	657	1001	934	112
115°	189	230	527	1049	1191	186
125°	260	296	478	809	948	232
135°	314	348	464	654	740	242
145°	363	388	458	557	600	227
155°	411	424	455	501	515	189
165°	444	450	457	475	478	125
175°	460	460	458	463	462	44
180°	460	460	460	460	460	

TEST NUMBER: P519192

CATALOG NUMBER: SQ4-WB-075U-075D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1711.1	1711.1	1711.1	1711.1	1711.1
2.5°	1715.3	1700.0	1703.9	1703.8	1699.1
5°	1683.3	1666.4	1677.3	1681.2	1687.1
7.5°	1620.9	1608.1	1627.9	1642.6	1654.5
10°	1572.2	1561.2	1586.5	1607.9	1623.3
12.5°	1515.8	1506.5	1537.8	1566.5	1586.6
15°	1423.6	1418.4	1456.6	1496.2	1521.9
17.5°	1324.9	1322.4	1366.2	1412.4	1445.3
20°	1257.6	1256.9	1304.9	1353.1	1391.3
22.5°	1189.7	1191.4	1241.9	1291.9	1335.4
25°	1087.9	1090.9	1147.3	1197.3	1250.1
27.5°	993.8	995.1	1053.4	1106.2	1162.6
30°	929.5	933.2	990.3	1045.0	1103.7
32.5°	865.2	869.5	925.5	981.9	1041.8
35°	768.8	772.5	824.4	879.9	942.3
37.5°	669.4	674.4	720.5	772.9	834.3
40°	605.2	612.5	653.2	702.6	762.8
42.5°	543.3	552.4	590.1	637.0	691.4
45°	461.0	469.8	500.8	538.7	587.9
47.5°	390.1	400.3	424.1	456.7	498.7
50°	349.9	359.4	381.4	405.6	445.2
52.5°	314.4	324.0	343.6	362.2	396.0
55°	265.0	276.1	292.1	303.1	328.1
57.5°	224.5	235.1	247.8	252.8	267.9
60°	197.5	209.2	220.7	220.2	228.2
62.5°	172.8	182.8	194.3	186.4	186.8
65°	132.9	143.9	156.9	137.1	124.6
67.5°	107.4	109.7	123.1	95.6	80.8
70°	95.4	95.4	99.1	74.0	61.6
72.5°	83.9	83.9	80.5	60.2	47.2
75°	66.8	66.8	60.8	41.7	28.5
77.5°	51.5	50.9	46.6	31.1	20.7
80°	41.3	41.3	37.5	24.6	16.5
82.5°	32.3	32.3	29.1	19.2	12.3
85°	18.8	18.8	17.3	11.2	6.8
87.5°	6.8	7.4	7.4	5.4	4.8
90°	1.0	3.8	6.8	8.8	8.8
92.5°	13.5	57.7	99.9	38.4	31.5
95°	32.3	118.3	383.3	163.9	104.6
97.5°	52.6	131.2	584.9	450.7	318.0
100°	67.5	139.2	648.3	654.3	533.9
102.5°	81.5	148.7	664.7	811.8	701.3
105°	106.6	163.9	657.1	1000.7	933.8
107.5°	130.4	182.8	619.7	1093.2	1113.1
110°	147.6	195.4	591.5	1116.2	1185.1



TEST NUMBER: P519192

CATALOG NUMBER: SQ4-WB-075U-075D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	163.3	209.6	563.4	1101.4	1206.2
115°	188.7	229.8	527.0	1049.4	1190.9
117.5°	213.0	250.8	503.9	976.5	1136.6
120°	227.8	264.1	493.8	921.9	1087.3
122.5°	241.1	277.4	486.7	874.0	1031.0
125°	260.1	296.4	478.1	808.8	947.5
127.5°	278.1	312.7	472.5	754.5	876.1
130°	287.5	322.8	469.3	722.2	833.1
132.5°	298.4	333.8	467.0	693.8	793.9
135°	313.9	348.3	464.4	654.1	740.2
137.5°	328.3	360.3	462.3	622.1	693.0
140°	339.3	368.9	461.5	600.8	664.9
142.5°	348.7	376.0	459.9	581.8	636.7
145°	362.8	387.6	457.6	557.3	600.3
147.5°	377.8	399.2	456.4	535.6	570.0
150°	387.2	406.3	455.6	523.7	550.5
152.5°	395.8	413.4	454.9	513.4	535.6
155°	410.7	424.0	454.7	500.9	515.3
157.5°	421.4	432.3	454.7	490.7	500.6
160°	429.2	437.8	454.7	485.1	492.8
162.5°	435.5	442.6	455.4	480.4	486.5
165°	443.9	449.6	456.6	475.3	478.1
167.5°	449.8	454.2	457.6	470.9	471.7
170°	453.7	456.6	457.6	469.3	469.3
172.5°	456.8	458.2	457.6	467.0	466.2
175°	459.5	460.5	457.6	463.4	462.5
177.5°	460.3	460.3	457.2	461.9	460.3
180°	459.5	459.5	459.5	459.5	459.5

(END OF REPORT)