

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563568

Luminaire Tested: **SQ4-PP3-100U-050D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563568
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-050D-835-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11933.9 lumens
Efficiency: N/A
Efficacy: 140.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563568
CATALOG NUMBER: SQ4-PP3-100U-050D-835-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563568

CATALOG NUMBER: SQ4-PP3-100U-050D-835-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	32	30	29	23
3	78	69	62	56	70	63	57	52	50	46	42	39	36	33	28	26	25	20
4	71	61	53	48	64	55	49	44	45	40	36	34	31	29	25	23	21	17
5	66	54	47	41	59	49	43	37	40	35	31	31	27	25	23	20	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	22	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	15	12
8	52	40	32	27	46	36	30	25	29	24	21	23	20	17	17	15	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7027	7027	7027
5°	7079	7035	7010
10°	7067	7017	6985
15°	7020	6981	6943
20°	6973	6934	6882
25°	6890	6843	6775
30°	6763	6727	6642
35°	6586	6541	6458
40°	6375	6335	6263
45°	6201	6158	6097
50°	5978	5940	5883
55°	5669	5594	5551
60°	5161	5014	4989
65°	4546	4357	4342
70°	3925	3763	3763
75°	3379	3331	3283
80°	2978	3015	2943
85°	2334	2546	2546



TEST NUMBER: P563568

CATALOG NUMBER: SQ4-PP3-100U-050D-835-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.0	1.2
10°-20°	411.3	3.4
20°-30°	616.0	5.2
30°-40°	722.6	6.1
40°-50°	724.8	6.1
50°-60°	618.3	5.2
60°-70°	403.3	3.4
70°-80°	202.3	1.7
80°-90°	58.6	0.5
90°-100°	579.0	4.9
100°-110°	1598.3	13.4
110°-120°	1648.4	13.8
120°-130°	1324.6	11.1
130°-140°	1041.0	8.7
140°-150°	798.4	6.7
150°-160°	573.8	4.8
160°-170°	350.9	2.9
170°-180°	118.3	1.0
0°-30°	1171.3	9.8
0°-40°	1893.9	15.9
0°-60°	3237.1	27.1
0°-90°	3901.2	32.7
90°-120°	3825.6	32.1
90°-150°	6989.6	58.6
90°-180°	8033.0	67.3
0°-180°	11933.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1523	1523	1523	1523	1523	
5°	1529	1514	1519	1514	1514	145
15°	1470	1456	1462	1456	1454	415
25°	1354	1338	1344	1332	1331	622
35°	1170	1158	1162	1148	1147	731
45°	950	944	944	934	934	732
55°	705	702	696	692	690	626
65°	416	409	399	396	398	416
75°	190	190	187	186	184	206
85°	44	48	48	48	48	52
90°	4	8	16	18	20	8
95°	85	313	1050	432	281	91
105°	285	440	1758	2685	2528	303
115°	510	617	1416	2804	3189	501
125°	700	797	1284	2172	2550	623
135°	843	934	1248	1760	1984	652
145°	977	1045	1232	1498	1612	612
155°	1102	1138	1222	1344	1387	508
165°	1193	1208	1228	1276	1286	336
175°	1236	1238	1230	1248	1244	117
180°	1236	1236	1236	1236	1236	

TEST NUMBER: P563568

CATALOG NUMBER: SQ4-PP3-100U-050D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1523.3	1523.3	1523.3	1523.3	1523.3
2.5°	1532.9	1520.3	1523.3	1521.0	1514.7
5°	1528.6	1514.2	1519.2	1513.9	1513.9
7.5°	1518.2	1502.5	1507.5	1502.2	1501.9
10°	1508.6	1492.9	1497.9	1492.5	1491.2
12.5°	1494.7	1479.0	1485.1	1478.7	1478.4
15°	1469.9	1455.5	1461.8	1456.4	1453.8
17.5°	1441.8	1426.2	1433.8	1426.3	1425.3
20°	1420.5	1404.8	1412.4	1401.8	1401.8
22.5°	1394.8	1379.2	1387.9	1374.0	1374.0
25°	1353.7	1338.0	1344.4	1332.3	1331.0
27.5°	1304.8	1289.4	1296.0	1282.4	1282.1
30°	1269.6	1255.2	1262.9	1248.2	1246.9
32.5°	1231.2	1217.8	1223.4	1208.7	1207.4
35°	1169.5	1157.7	1161.5	1148.1	1146.8
37.5°	1104.6	1092.6	1096.8	1085.4	1084.8
40°	1058.7	1050.8	1052.0	1042.6	1040.0
42.5°	1015.9	1007.1	1008.2	998.8	998.3
45°	950.5	944.0	943.9	934.5	934.5
47.5°	881.1	876.1	874.7	867.0	866.7
50°	833.0	829.1	827.7	821.0	819.7
52.5°	782.9	781.0	776.4	770.8	770.6
55°	704.9	702.3	695.5	691.5	690.2
57.5°	620.2	615.0	607.4	601.6	602.6
60°	559.4	554.2	543.4	540.7	540.7
62.5°	500.6	494.4	483.5	479.9	481.9
65°	416.5	408.7	399.2	396.5	397.8
67.5°	340.2	333.1	322.8	322.8	321.7
70°	291.0	287.1	279.0	279.0	279.0
72.5°	247.2	245.4	239.5	239.5	238.4
75°	189.6	189.6	186.9	185.5	184.2
77.5°	142.0	142.6	141.2	139.9	137.5
80°	112.1	114.8	113.5	112.1	110.8
82.5°	84.4	87.0	86.8	84.4	84.1
85°	44.1	48.0	48.1	48.1	48.1
87.5°	12.5	17.5	20.3	20.7	22.1
90°	4.0	7.8	15.8	17.8	19.8
92.5°	35.6	147.8	264.3	96.4	75.2
95°	85.1	313.3	1050.3	431.7	280.9
97.5°	140.8	350.9	1555.9	1197.9	867.6
100°	182.0	373.5	1742.6	1755.0	1426.2
102.5°	221.5	399.1	1779.0	2168.4	1856.6
105°	284.8	439.6	1758.5	2684.6	2527.9
107.5°	352.1	489.8	1660.4	2933.5	2990.8
110°	399.6	523.3	1584.4	2987.1	3172.8



TEST NUMBER: P563568

CATALOG NUMBER: SQ4-PP3-100U-050D-835-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	442.3	561.4	1513.2	2944.8	3218.7
115°	510.3	616.7	1416.3	2803.7	3188.6
117.5°	569.7	675.7	1352.6	2605.1	3043.0
120°	609.2	713.7	1327.3	2470.7	2911.7
122.5°	647.2	747.0	1306.7	2345.2	2762.9
125°	700.2	796.9	1283.7	2172.5	2549.7
127.5°	745.3	842.0	1270.3	2026.6	2351.9
130°	775.4	872.1	1264.0	1937.3	2233.2
132.5°	803.9	895.9	1257.6	1862.3	2130.3
135°	842.6	933.5	1248.1	1759.6	1984.0
137.5°	886.2	968.9	1243.4	1673.4	1864.9
140°	909.9	991.1	1240.2	1615.9	1784.2
142.5°	936.8	1011.8	1237.1	1564.8	1713.0
145°	977.1	1044.8	1232.3	1498.0	1612.1
147.5°	1015.9	1075.1	1228.0	1441.6	1530.2
150°	1044.4	1092.8	1226.4	1408.0	1479.6
152.5°	1066.6	1111.8	1224.8	1379.2	1438.4
155°	1101.8	1138.5	1222.4	1344.1	1386.6
157.5°	1134.2	1162.4	1222.8	1318.4	1347.4
160°	1153.2	1178.3	1224.4	1304.0	1325.3
162.5°	1169.0	1191.1	1226.0	1291.2	1307.9
165°	1192.8	1208.2	1228.4	1276.1	1285.7
167.5°	1211.0	1220.2	1230.3	1266.8	1269.9
170°	1220.4	1228.2	1230.3	1262.0	1262.0
172.5°	1228.4	1233.0	1230.3	1255.6	1254.1
175°	1236.3	1238.2	1230.3	1248.1	1244.2
177.5°	1239.4	1237.9	1229.9	1240.9	1237.9
180°	1236.3	1236.3	1236.3	1236.3	1236.3

(END OF REPORT)