

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P519673

Luminaire Tested: **SQ4-050U-0D-835-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519673  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-050U-0D-835-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2987.9 lumens  
Efficiency: N/A  
Efficacy: 165.1 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Indirect

Input Watts (W): 18.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519673  
CATALOG NUMBER: SQ4-050U-0D-835-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P519673

CATALOG NUMBER: SQ4-050U-0D-835-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	2287	27001	7890
100°	2398	22985	18816
105°	2517	15597	22344
110°	2672	10610	21302
115°	2741	7645	17325
120°	2788	6046	13304
125°	2777	5097	10131
130°	2745	4477	7927
135°	2713	4019	6400
140°	2706	3686	5305
145°	2707	3425	4474
150°	2749	3229	3888
155°	2766	3076	3475
160°	2793	2966	3217
165°	2811	2895	3027
170°	2821	2849	2913
175°	2825	2816	2844



TEST NUMBER: P519673

CATALOG NUMBER: SQ4-050U-0D-835-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	219.7	7.4
100°-110°	596.8	20.0
110°-120°	613.6	20.5
120°-130°	490.6	16.4
130°-140°	385.5	12.9
140°-150°	295.6	9.9
150°-160°	212.5	7.1
160°-170°	130.0	4.4
170°-180°	43.8	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1430.0	47.9
90°-150°	2601.6	87.1
90°-180°	2988.0	100.0
0°-180°	2987.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	6	10	13	13	
95°	32	120	383	166	112	36
105°	106	165	656	999	940	113
115°	188	229	525	1045	1190	186
125°	259	295	475	801	945	231
135°	312	346	462	652	736	241
145°	360	386	456	554	596	226
155°	408	422	453	498	512	188
165°	441	447	455	474	475	125
175°	458	459	456	462	461	43
180°	458	458	458	458	458	



TEST NUMBER: P519673

CATALOG NUMBER: SQ4-050U-0D-835-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	1.5	5.8	10.3	13.2	13.2
92.5°	13.2	60.1	104.5	44.9	38.0
95°	32.4	120.1	382.6	166.5	111.8
97.5°	53.6	132.7	586.5	456.3	320.5
100°	67.7	141.1	648.9	657.8	531.2
102.5°	81.8	149.4	665.4	813.5	701.9
105°	105.9	164.9	656.3	999.2	940.2
107.5°	131.0	183.0	618.3	1095.1	1111.5
110°	148.6	196.1	590.0	1114.0	1184.5
112.5°	163.9	209.1	561.8	1098.3	1204.5
115°	188.3	228.6	525.3	1045.1	1190.4
117.5°	211.3	249.9	502.0	969.6	1133.3
120°	226.6	264.0	491.5	918.9	1081.5
122.5°	239.5	277.0	484.4	868.2	1025.0
125°	259.0	294.9	475.3	800.8	944.7
127.5°	276.3	312.0	470.3	749.7	873.1
130°	286.9	321.5	467.9	717.6	828.4
132.5°	297.5	332.1	465.6	690.3	788.4
135°	311.9	346.5	462.0	652.3	735.7
137.5°	327.5	358.9	460.3	618.7	688.9
140°	337.0	367.2	459.1	597.4	660.7
142.5°	346.4	374.3	457.9	580.6	633.6
145°	360.5	386.4	456.1	554.2	595.9
147.5°	376.4	398.5	454.7	533.4	566.2
150°	387.0	405.7	454.7	521.5	547.4
152.5°	395.2	411.6	453.5	510.8	532.1
155°	407.6	422.0	453.2	497.7	512.1
157.5°	419.6	430.9	453.2	488.8	499.7
160°	426.7	436.8	453.2	482.8	491.5
162.5°	433.8	441.5	454.4	478.1	484.4
165°	441.4	447.2	454.7	473.8	475.3
167.5°	449.4	452.2	456.1	468.8	470.0
170°	451.7	454.6	456.1	466.4	466.4
172.5°	454.1	455.8	456.1	464.1	464.1
175°	457.6	459.1	456.1	462.0	460.6
177.5°	458.8	458.8	455.3	459.9	457.6
180°	457.6	457.6	457.6	457.6	457.6

(END OF REPORT)